

NXP 204-MHz, 32-bit Cortex-M4/ Cortex-M0 MCU LPC4300 series

# Cortex-M4 MCUs with Cortex-M0 coprocessor, HS USB, and more

Multiple cores and a unique set of configurable peripherals make it easy to develop advanced applications within a single architecture and development environment.

#### **KEY FEATURES**

- ▶ 204 MHz, 32-bit ARM Cortex-M4 with FPU
- ▶ 204 MHz, 32-bit ARM Cortex-M0 coprocessor
- ▶ Up to 1 MB dual-bank Flash
- ▶ Up to 282 KB SRAM
- ▶ Up to 16 KB EEPROM
- ▶ Memory Protection Unit (MPU)
- Two high-speed USB 2.0 interfaces, with on-chip high-speed PHY
- ▶ 10/100T Ethernet MAC with MII and RMII interfaces
- ▶ LCD controller with 1024 x 768 pixel display resolution
- Innovative Quad SPI Flash Interface (SPIFI)
- ▶ State Configurable Timer with up to 16 PWMs
- ▶ Configurable Serial GPIO
- ▶ Two CAN 2.0B
- ▶ Up to 164 GPIO
- ▶ Pin-compatible with the LPC1800 series

# **ADDITIONAL FEATURES**

- ▶ 8-channel GPDMA controller
- ▶ Two 8-channel, 400 Ksps 10-bit ADCs and one 10-bit DAC, the optional 12-bit 80Msps ADC
- ▶ Motor Control PWM and Quadrature Encoder Interface
- ▶ Four UARTs, smart card interface
- ▶ Two Fast-mode I<sup>2</sup>C, two I<sup>2</sup>S, three SSP/SPI
- ▶ Extended temperature range: -45 to +105 °C

# **KEY APPLICATIONS**

- ▶ Industrial automation
- ▶ Instrumentation
- ▶ Embedded audio
- ▶ Automotive accessories
- ▶ Robotics
- ▶ Medical

The NXP LPC4300 series combines industry leading microcontroller performance and advanced peripheral functionality to deliver superior integration for the most challenging embedded applications. The LPC4300 architecture uses multiple cores – a sophisticated Cortex-M4 processor with a floating-point unit (FPU), plus one or two Cortex-M0 coprocessor cores. The multi-core approach makes it easy to partition a design for maximum efficiency, letting the powerful Cortex-M4 core crunch numbers and letting the Cortex-M0 coprocessor(s) manage data movement and I/O handling.




The multi-core approach also reduces time-to-market, since design and debug take place in a single development environment. The processor cores are supported by a long list of high-performance peripherals, integrated interrupt control, and low-power modes that give embedded engineers new ways to solve complex design problems.

Depending on their application needs, designers can choose an LPC4300 device with or without on-chip Flash. There are also options for extended temperature range.

Several LPC4300 features are unique to NXP. The SCT subsystem, consisting of a timer array with a state machine, makes it easy to configure complex PWM and timer functions. The SPIFI peripheral provides a seamless interface to SPI and quad-SPI memories, and the Serial GPIO expand the options for serial interfaces like I<sup>2</sup>C and I<sup>2</sup>S.

The LPC4300 series is also equipped with an extensive list of connectivity interfaces and analog functions. Options include two HS USB controllers, an on-chip HS PHY, a 10/100T Ethernet controller with hardware-enabled TCP/IP checksum calculation, and a high-resolution color LCD controller.

Analog functionality includes two 8-channel, 10-bit ADCs running at 400 Ksps or a 6-channel, 12-bit ADC running at 80 Msps, and a 10-bit DAC.



\*The LPC4370 adds an 80Msps 12-bit ADC and a subsystem with a second Cortex-M0 peripheral handler.

Туре	Memory							Serial	External	<b>Temperature</b>	
	Flash	Ram	M4F/M0	LCD	Ethernet	USB	SCT	GPIO	bus interface	range	Package Package
LPC4310		168 KB	•				•	•	8-16	-40 to +85 °C	LQFP144, TBGA100
LPC4312	512	104 KB	•				•	•	8-16	-40 to +105 °C	LQFP144, TBGA100
LPC4313	256x2	104 KB	•				•	•	8-16	-40 to +105 °C	LQFP144, TBGA100
LPC4315	768	136 KB	•				•	•	8-16	-40 to +105 °C	LQFP144, TBGA100
LPC4317	1024	136 KB	•				•	•	8-16	-40 to +105 °C	LQFP144, TBGA100
LPC4320		200 KB	•			1	•	•	8-16	-40 to +85 °C	LQFP144, TBGA100
LPC4322	512	104 KB	•			1	•	•	8-16	-40 to +105 °C	LQFP144, TBGA100
LPC4323	256x2	104 KB	•			1	•	•	8-16	-40 to +105 °C	LQFP144, TBGA100
LPC4325	768	136 KB	•			1	•	•	8-16	-40 to +105 °C	LQFP144, TBGA100
LPC4327	1024	136 KB	•			1	•	•	8-16	-40 to +105 °C	LQFP144, TBGA100
LPC4330		264 KB	•		•	2	•	•	16-32	-40 to +85 °C	BGA256, BGA180, LQFP144, BGA100
LPC4333	512	136 KB	•		•	2	•	•	16-32	-40 to +105 °C	BGA256, BGA180, LQFP144, BGA100
LPC4337	1024	136 KB	•		•	2	•	•	16-32	-40 to +105 °C	BGA256, BGA180, LQFP144, BGA100
LPC4350		264 KB	•	•	•	2	•	•	16-32	-40 to +85 °C	BGA256, LQFP208, BGA180
LPC4353	512	136 KB	•	•	•	2	•	•	16-32	-40 to +105 °C	BGA256, LQFP208, BGA180
LPC4357	1024 (2x512)	136 KB	•	•	•	2	•	•	16-32	-40 to +105 °C	BGA256, LQFP208, BGA180
LPC4370		282 KB	•	•	•	2	•	•	8-32	-40 to +85 °C	BGA256, BGA100

Note: LPC4370 combines a Cortex-M4 with two Cortex-M0 cores

www.nxp.com/microcontrollers

### www.nxp.com

#### © 2013 NXP Semiconductors N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.