



FRDM Automotive S32K312 Development Board for General Purpose

FRDM-A-S32K312 UPDATED

Active

Last Updated: Mar 10, 2026


S32K312MINI#EVB Renamed to FRDM#A#S32K312: Now part of the FRDM Automotive Ecosystem under its new name, the board keeps the same hardware and adds full ecosystem compatibility for flexible, scalable development.

The FRDM-A-S32K312 is a development board for general-purpose industrial and automotive applications.

Based on the 32-bit Arm® Cortex®-M7 S32K3 microcontroller unit (MCU) in a 172 High Density Quad Flat Package (HDQFP) package, the FRDM-A-S32K312 offers a single-core mode, Hardware Security Engine (HSE), over-the-air (OTA) support, advanced connectivity and low-power.

The FRDM-A-S32K312 offers a standard-based form factor compatible with the Arduino® UNO pin layout, providing a broad range of expansion board options for quick application prototyping and demonstration.

FRDM-A-S32K312 Development Board Block Diagram



S32K3 Family Block Diagram

K311	K312	K314	Common Features	K322	K324	K341	K342	K344	K328	K338	K348	K358	
1 x Arm® Cortex-M7 @120 MHz		1x Cortex-M7 @240MHz	AEC-Q100, 125 °C, 3,3/5 V	2 x Cortex-M7 @240 MHz		1 Lockstep Cortex-M7 @ 240 MHz			2 x Cortex-M7 @ 240 MHz	3 x Cortex-M7 @ 240 MHz	1 LS Cortex-M7 @ 240 MHz	1 LS Cortex-M7 + 1 Cortex-M7 @ 240 MHz	
1 MB Flash	2 MB Flash	4 MB Flash	HSE-B Crypto Security Engine	2 MB Flash	4 MB Flash	1 MB Flash	2 MB Flash	4 MB Flash	8 MB Flash				
128 K SRAM	192 K SRAM	512 K SRAM	FOTA (Firmware Over-the-Air)	256 k SRAM	512 k SRAM	256 k SRAM	256 k SRAM	512 k SRAM	1152 KB SRAM	1152 KB SRAM	1152 KB SRAM	1152 KB SRAM	
up to 84 I/Os	up to 143 I/Os	up to 218 I/Os	Low-Power Operating Modes and Peripherals (LP UART, FlexIO)	up to 143 I/Os	up to 218 I/Os	up to 143 I/Os	up to 143 I/Os	up to 218 I/Os	up to 218 I/Os				
16-ch, eDMA		32-ch, eDMA	ASIL B/D Safety: (ECC Memories, MPU, CRC, Watchdogs)	32-ch, eDMA					32-ch, eDMA				
3 x CAN (3 x FD)	6 x CAN (6 x FD)		100 Mbit/s Ethernet (TSN)	4 x CAN (4 x FD)	6 x CAN (6 x FD)	4 x CAN (4 x FD)	4 x CAN (4 x FD)	6 x CAN (6 x FD)	8 x CAN (8 x FD)	8 x CAN (8 x FD)	8 x CAN (8 x FD)	8 x CAN (8 x FD)	
			100 Mbit/s Ethernet (TSN)	100 Mbit/s Ethernet (TSN)					1 Gbit/s Ethernet (TSN)				
2 x I2C	2 x I2C	2 x I2C	eMIOS Timers, Analogue Comparator, Logic Control Unit, Body Cross Triggering Unit, Trigger Mux	2 x I2C	2 x I2C	2 x I2C	2 x I2C	2 x I2C	2 x I2C				
4 x SPI*		6 x SPI*	JTAG	4 x SPI*	6 x SPI*	4 x SPI*	4 x SPI*	6 x SPI*	6 x SPI*				
2 x 24-ch, 12-bit ADC		3 x 24-ch, 12-bit ADC	S32 Design Studio IDE	2 x 24-ch, 12-bit ADC	3 x 24-ch, 12-bit ADC	2 x 24-ch, 12-bit ADC	2 x 24-ch, 12-bit ADC	3 x 24-ch, 12-bit ADC	3 x 24-ch, 12-bit ADC				
			2 x SAI (FS)	2 x SAI (FS)					2 x SAI (FS)				
			Quad SPI	Quad SPI					Quad SPI + SDHC (SDIO)				
LOFP-48	HDQFP-172		Real-Time Drivers (AUTOSAR® and Non-AUTOSAR)	HDQFP-172				HDQFP-172					
HDQFP-100				HDQFP-100		HDQFP-100	HDQFP-100						
		MAPBGA-257	Security FW Safety Software Framework Application Software	MAPBGA-257			MAPBGA-257		MAPBGA-289				

View additional information for [FRDM Automotive S32K312 Development Board for General Purpose](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2026 NXP B.V.