

Mask Set Errata

MSE908JL8_2L39J 7/2003

Mask Set Errata for 908JL8, Mask 2L39J





Introduction

This mask set errata applies to this 908JL8 MCU mask set:

2L39J

MCU Device Mask Set Identification

The mask set is identified by a 5-character code consisting of a version number, a letter, two numerical digits, and a letter, for example 2L39J. All standard devices are marked with a mask set number and a date code.

MCU Device Date Codes

Device markings indicate the week of manufacture and the mask set used. The date is coded as four numerical digits where the first two digits indicate the year and the last two digits indicate the work week. For instance, the date code "0301" indicates the first week of the year 2003.

MCU Device Part Number Prefixes

Some MCU samples and devices are marked with an SC, PC, or XC prefix. An SC prefix denotes special/custom device. A PC prefix indicates a prototype device which has undergone basic testing only. An XC prefix denotes that the device is tested but is not fully characterized or qualified over the full range of normal manufacturing process variations. After full characterization and qualification, devices will be marked with the MC or SC prefix.



I/O Port Function on OSC2/RCCLK/PTA6/KBI6 Pin

SE65-IO PORT

An anomaly has been found with the OSC2/RCCLK/PTA6/KBI6 pin when:

 RC oscillator option is selected (OSCSEL = 0) and the pin is selected as PTA6 (PTA6EN = 1).

Under this condition, the PTA6 pin can only function as an output pin; not an input/output pin as stated in the device data sheet.

Because PTA6 is output only:

- The DDRA6 bit has no effect on PTA6.
- The PTAPUE6 bit must not be set to logic 1 to avoid possible current drain if DDRA6 is logic 0.
- The KBIE6 bit has no effect, as keyboard interrupt, KBI6, is not available.

To maintain compatibility with future silicon, the DDRA6 bit should be set to a logic 1 if PTA6 is used as an output port pin.

Minimum Crystal Frequency

SE66-CRYSTAL

A longer than normal start-up time has been identified when the crystal oscillator option is selected (OSCSEL = 1).

When a less than 4-MHz crystal is used, the time from V_{DD} applied to the MCU to crystal frequency stabilization is longer than the 4096 ICLK cycles stated in the data sheet. This crystal stabilization time also depends on the crystal being used, as crystal start-up times vary depending on manufacturers (consult the crystal manufacturers data sheet).

Although this longer start-up time does not cause any known anomaly to the MCU, it is recommended that if a less than 4-MHz crystal is used, the reset pin, RST, should be held low for a longer period to allow for the crystal to stabilize.





HOW TO REACH US:

USA/EUROPE/LOCATIONS NOT LISTED:

Motorola Literature Distribution; P.O. Box 5405, Denver, Colorado 80217 1-303-675-2140 or 1-800-441-2447

JAPAN:

Motorola Japan Ltd.; SPS, Technical Information Center, 3-20-1, Minami-Azabu Minato-ku, Tokyo 106-8573 Japan 81-3-3440-3569

ASIA/PACIFIC:

Motorola Semiconductors H.K. Ltd.; Silicon Harbour Centre, 2 Dai King Street, Tai Po Industrial Estate, Tai Po, N.T., Hong Kong 852-26668334

TECHNICAL INFORMATION CENTER:

1-800-521-6274

HOME PAGE:

http://www.motorola.com/semiconductors

Information in this document is provided solely to enable system and software implementers to use Motorola products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Motorola data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights nor the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part.



Motorola and the Stylized M Logo are registered in the U.S. Patent and Trademark Office. digital dna is a trademark of Motorola, Inc. All other product or service names are the property of their respective owners. Motorola, Inc. is an Equal Opportunity/Affirmative Action Employer.

© Motorola, Inc. 2003