

# SOT1677-1

HVQFN12, plastic, thermal enhanced very thin quad flatpack; no leads; 12 terminals; 0.5 mm pitch; 3 mm x 3 mm x 0.85 mm body

**21 December 2017** 

Package information

## 1. Package summary

Terminal position code Q (quad)

Package type descriptive code HVQFN12

Package style descriptive code HVQFN (thermal enhanced very thin quad

flatpack; no leads)

Package body material type P (plastic)

Mounting method type S (surface mount)

Issue date11-6-2017Manufacturer package code98ASA00227D


#### **Table 1. Package summary**

Symbol	Parameter		Min	Тур	Nom	Max	Unit		
D	package length		_	-	3	-	mm		
Е	package width		_	-	3	-	mm		
A <sub>2</sub>	package height		-	-	0.85	-	mm		
е	nominal pitch		-	-	0.5	-	mm		
n <sub>2</sub>	actual quantity of termination		_	_	12	-	A/A		




HVQFN12, plastic, thermal enhanced very thin quad flatpack; no leads; 12 terminals; 0.5 mm pitch; 3 mm x 3 mm x 0.85 mm body

# 2. Package outline



SOT1677-1

HVQFN12, plastic, thermal enhanced very thin quad flatpack; no leads; 12 terminals; 0.5 mm pitch; 3 mm x 3 mm x 0.85 mm body



SOT1677-1

HVQFN12, plastic, thermal enhanced very thin quad flatpack; no leads; 12 terminals; 0.5 mm pitch; 3 mm x 3 mm x 0.85 mm body

#### NOTE:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. DIMENSIONING & TOLERANCING PER ASME Y14.5 2009.

 $\stackrel{\frown}{3}$  this dimension applies to plated terminal and is measured between 0.15 and 0.30 mm from terminal tip.

THIS DIMENSION APPLIED ONLY FOR TERMINALS.

© NXP SEMICONDUCTORS N. V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE		PRINT VERSIO	N NOT TO SCALE
FLAT NON-LEADED PACKAGE (QFN)		DOCUMENT NO: 98ASA00227D REV: A		
		STANDARD: NON-JEDEC		
12 TERMINAL, 0.5 PITCH (	(3X3XU.85)	S0T1677	7-1	30 NOV 2017

Fig. 3. Package outline note HVQFN12 (SOT1677-1)

HVQFN12, plastic, thermal enhanced very thin quad flatpack; no leads; 12 terminals; 0.5 mm pitch; 3 mm x 3 mm x 0.85 mm body

### 3. Legal information

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

HVQFN12, plastic, thermal enhanced very thin quad flatpack; no leads; 12 terminals; 0.5 mm pitch; 3 mm x 3 mm x 0.85 mm body

### 4. Contents

1.	Package summary	1
2.	Package outline	2
3.	Legal information	5
© <b>N</b>	NXP B.V. 2017. All rights reserved	
For For	more information, please visit: http://www.nxp.com sales office addresses, please send an email to: salesaddresses@nxp.com te of release: 21 December 2017	