

# Freescale Announces Two New Cellular Base Station Drivers AFT27S006N and AFT27S010N

**December 2013** 





Freescale and the Freescale logo are trademarks of Freescale Semiconductor, Inc., Reg. U.S. Pat. & Tm. Off. Airfast is a trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. © 2013 Freescale Semiconductor, Inc.



## A Global Leader in

## Microcontrollers and Digital Networking Processors



- > 50 Year Legacy
- > **5,500** Engineers
- > 6,000 Patent Families

**Four** Primary **Five** Core Product Markets Groups Microcontrollers **Automotive Digital Networking** Networking **Automotive MCU** Industrial Analog & Sensors Consumer RF







Maintain RF's leadership market share position in cellular infrastructure PAs and leverage market position to grow revenue in adjacent spaces for RF



## **RF Cellular**

 Continue strong position with Airfast technology and MMIC portfolio expansion




## **RF Industrial**

 Continue strong position in current markets while expanding into additional RF Industrial applications



## **RF's Mission & Charter**





## **KF Market Focus**

## Performance Leadership with Airfast RF Power Solutions

## Markets & Applications

#### Super Macro

High Power RF LDMOS, LDMOS ICs

#### Macro

High Power RF LDMOS, LDMOS ICs

#### Micro

Medium Power LDMOS, LDMOS ICs

#### Pico

LDMOS ICs, MMICs

## RF Power Products Growth

## Markets & Applications

## Industrial, Scientific, Medical

- CO2 Lasers
- Plasma Generation
- MRI

#### Broadcast

- UHF & VHF Television
- FM Radio
- · Shortwave Radio

#### Aerospace

- · Distance Measuring
- Weather Radar
- · Air Traffic Mgmt

#### Military/Defense

- · Long Range Radar
- HF, VHF, UHF Comms
- Radio Navigation

#### Land Mobile Radio

- · Public Safety
- Marine
- Dispatch

## GaAs MMIC Solutions Expansion

## Markets & Applications

#### Wireless Infrastructure

ADAM, GPA, LNA, MMIC PA Driver

#### Small Cell

MMIC PA, LNA

#### Smart Energy

MMIC PA, LNA

#### Land Mobile Radio

MMIC PA Driver, LNA, ATT



# Technology & Service Differentiation

- Freescale RF maintains a clear #1 position for cellular infrastructure
  - More than 2x market share of next largest supplier\*
- Freescale's latest Airfast performance puts us in best-in-class at all frequency bands and power levels
- Our unparalleled worldwide applications support and most reliable supply chain gives us an undisputed market leadership position
- We are creating further differentiation in our product offerings to continue to grow our cellular market share

\*Source: ABI Research, December 2012





## **Customers Facing...**

- Skyrocketing data rates
- Multiple wireless standards
- Increasing network complexity
- Stringent power requirements
- Worldwide rise in IP traffic

# **Mobile Broadband for Evolving Cellular Market**

- Enable increased capacity requirements on cellular networks
- Support for 4G data rates and beyond
- Reduced energy consumption
- Shrinking equipment footprint
- Reduced time-to-market for new designs

## Past

**Product Portfolio** 

## **RF Power**

Macrocells

## **Signal Bandwidth**

20-35 MHz

## **RF Bandwidth**

Single Tx band

## **RF PA Size and Cost**

- Mix of single and two-stage final stage device
- Air cavity devices (above 1 GHz)

## **RF Performance**

- Class AB and symmetric Doherty
- 30 –40% lineup efficiency

# **Current**Solutions

## **RF Power**

Covering femto to macrocells

## **Signal Bandwidth**

Support for full bands/broad range of frequencies

## **RF Bandwidth**

- Single Tx to Multi Tx band
- Linearization and filtering/ out-of-band emissions considerations

## **RF PA Size and Cost**

- Plastic packaging
- Package uniformity over range of Tx bands
- Additional integration
- · Reduction in board space

## **RF Performance**

- Advanced high efficiency PAs
- 45%+ lineup efficiency (multiple bands)



# Airfast Goals

RF Power Solutions: Fast Forward to the Future

Develop innovative RF solutions that meet and exceed market needs for performance, bandwidth and cost efficiency.

Airfast Delivers Multi-Generational Performance Improvements

- ☑ 5 points higher drain efficiency over prior generation.
- ☑ 25% higher power density
- ☑ Significantly improved linearity
- ✓ Industry leading instantaneous bandwidth, up to 160 MHz
- ☑ Second generation over-molded plastic packaging: most technically advanced and cost-effective packages available for high power RF transistors

Beyond components - System Level Solutions


☑ DPD validated reference circuit designs for the full PA lineup to shorten customer's development time and cost





# wo New Airfast Drivers for Cellular Base Stations

- Building on the success of the MW6S004N, the industries workhorse, Freescale introduces two new drivers:
- AFT27S006N, AFT27S010N
  - Covering the full cellular infrastructure frequency range from 700 to 2700 MHz
  - Excellent 20 to 24 dB gain performance across the entire frequency range
  - Ultra small footprint (PLD-1.5W)
  - Two power options (6 W and 10 W) are ideally suited for MIMO applications rated between 20 to 40 W average power







## AF [27S006N Key Product Features



Designed as a driver for 20 to 40 W cellular base station MIMO applications across all bands

## Availability:

• In Production

## Airfast RF Power Solutions 28 V LDMOS

- Designed for cellular operation from 728 to 2700 MHz
- PLD-1.5W package

## AFT27S006N Class AB Performance

At an average power of 28.8 dBm:

- · 2600 MHz
- Gain: 22.0 dB, Drain Efficiency: 21.2%
- · 2350 MHz
- Gain: 23.5 dB, Drain Efficiency: 21.5%
- 2140 MHz
- Gain: 22.8 dB, Drain Efficiency: 19.8%
- 748 MHz
- Gain: 24.4 dB, Drain Efficiency: 19.9%





## AF [27S010N Key Product Features



Designed as a driver for 20 to 40 W cellular base station MIMO applications across all bands

## Availability:

In Production

## Airfast RF Power Solutions 28 V LDMOS

- Designed for cellular operation from 728 to 2700 MHz
- PLD-1.5W package

## **AFT27S010N Class AB Performance**

At an average power of 1.26 W:

- · 2600 MHz
- Gain: 21.0 dB, Drain Efficiency: 22.7%
- 2350 MHz
- Gain: 21.6 dB, Drain Efficiency: 22.6%
- · 2140 MHz
- Gain: 21.8 dB, Drain Efficiency: 23.0%
- 748 MHz
- Gain: 24.3 dB, Drain Efficiency: 24.7%





