

# Kinetis SDK v.2.0.0 Release Notes Supporting MKE1xZ7 Devices

## Contents

## 1 Overview

The Kinetis Software Development Kit (KSDK) 2.0.0 is a collection of software enablement for KE1xZ devices that includes peripheral drivers and integrated RTOS support for FreeRTOS OS and  $\mu$ C/OS. In addition to the base enablement, the KSDK is augmented with demo applications and driver example projects, and API documentation to help the customers quickly leverage the support of the Kinetis SDK.

For the latest version of this and other Kinetis SDK documents, see the Kinetis SDK homepage [KINETIS-SDK: Software Development Kit for Kinetis MCUs](#).

## 2 KSDK 2.0.0

KSDK 2.0.0 is the evolution of KSDK 1.x into a more optimized software solution. KSDK 2.0.0 eliminates the need for a separate HAL and Peripheral Driver, replacing these two layers with a single driver for each peripheral. The single driver provides both the low-level functionality of the HAL and the non-blocking interrupt-based functionality of the Peripheral Driver, enabling customers to select the right level of abstraction for their solution. Peripheral drivers in KSDK 2.0.0 also eliminate external software dependencies. The Operating System Abstraction, Power Manager, and Clock Manager are no longer required by the KSDK 2.0.0 drivers.

1	Overview.....	1
2	KSDK 2.0.0.....	1
3	Development Tools.....	2
4	Supported Development Systems.....	2
5	Release Contents.....	2
6	Kinetis SDK Release Package.....	3
7	MISRA Compliance.....	4
8	Known Issues.....	5
9	Driver Log.....	6
10	Middleware Log.....	13
11	RTOS Log.....	13
12	Revision history.....	14



## Development Tools

At the middleware level, RTCS and MFS have been removed, and the USB stack has been replaced with a BSD licensed solution. KSDK 2.0.0 has also aligned with ARM® architecture through the integration of mbed TLS with our accelerated cryptography drivers. This integration ensures the highest level of performance from our on-chip security peripherals.

The existing MQX™ RTOS support has been deprecated to focus on support of FreeRTOS OS and µC/OS-II and µC/OS-III.

The Real Time Control Embedded Software Library (RTCESL) and motor control examples for PMSM and BLDC are added to the middleware layer.

## 3 Development Tools

The Kinetis SDK v2.0.0 was compiled and tested with these development tools:

- IAR Embedded Workbench for ARM® version 7.70.1
- MDK-ARM Microcontroller Development Kit (Keil)® 5.20
- Kinetis Design Studio IDE v3.2.0
- Makefiles support with GCC revision 5-2015-q4-update from ARM Embedded
- Atollic® TrueSTUDIO® 5.5.2

## 4 Supported Development Systems

This release supports boards and devices listed in this table. Boards and devices in boldface were tested in this release:

**Table 1. Supported MCU devices and development boards**

Development boards	Kinetis MCU devices
FRDM-KE15Z (MKE15Z256VLL7)	MKE14Z128VLL7, MKE14Z128VLH7, MKE14Z256VLL7, MKE14Z256VLH7, MKE15Z128VLL7, MKE15Z128VLH7, <b>MKE15Z256VLL7</b> , MKE15Z256VLH7

## 5 Release Contents

This table describes the release contents.

**Table 2. Release contents**

Deliverable	Location
Boards	<install_dir>/boards
Demo applications	<install_dir>/boards/<board_name>/demo_apps
Driver examples	<install_dir>/boards/<board_name>/driver_examples
RTOS examples	<install_dir>/boards/<board_name>/rtos_examples
Documentation	<install_dir>/docs
DMA manager	<install_dir>/middleware/dma_manager_<version>
Motor Control libraries	<install_dir>/middleware/motor_control_<version>

*Table continues on the next page...*

**Table 2. Release contents (continued)**

RTCESL libraries	<install_dir>/middleware/rtcesl_<version>
Driver, SoC header and feature header files, utilities	<install_dir>/devices/<device_name>
Cortex Microcontroller Software Interface Standard (CMSIS) ARM Cortex®-M header files, DSP library source	<install_dir>/CMSIS
Peripheral Drivers	<install_dir>/devices/<device_name>/drivers
Utilities such as debug console	<install_dir>/devices/<device_name>/utilities
RTOS Kernel code	<install_dir>/rtos
Tools	<install_dir>/tools

## 6 Kinetis SDK Release Package

The KSDK 2.0.0 release package contents are aligned with the silicon subfamily it supports. This includes the boards, CMSIS, devices, documentation, middleware, and RTOS support.

### 6.1 Kinetis device support

The device folder contains all available software enablement for the specific SoC subfamily. This folder includes clock-specific implementation, device register header file, device register feature header file, CMSIS-derived device SVD, and the system configuration source files. Included with the standard SoC support are folders containing peripheral drivers, toolchain support, and a simple debug console.

The device-specific header files provide a direct access to the Kinetis MCU peripheral registers. The device header file provides an overall System-on-Chip (SoC) memory mapped register definition. In addition to the overall device memory mapped header file, the Kinetis SDK also includes the feature header file for each peripheral instantiated on the SoC.

The toolchain folder contains the startup code and linker files for each supported toolchain. The startup code is a CMSIS-compliant startup that efficiently transfers the code execution to the main() function.

#### 6.1.1 Kinetis board support

The boards folder provides the board-specific demo applications, driver examples, RTOS, and middleware examples.

#### 6.1.2 Demo applications and other examples

The demo applications demonstrate the usage of the peripheral drivers to achieve a system level solution. Each demo application contains a readme file that describes the operation of the demo and required setup steps.

The driver examples demonstrate the capabilities of the peripheral drivers. Each example implements a common use case to help demonstrate the driver functionality.

The RTOS and middleware folders each contain examples demonstrating the use of the included source.

## 6.2 Middleware

### 6.2.1 RTOS

The Kinetis SDK is preintegrated with FreeRTOS OS,  $\mu$ C/OS-II OS, and  $\mu$ C/OS-III OS.

### 6.2.2 CMSIS

The Kinetis SDK is shipped with the standard CMSIS development pack, including the prebuilt libraries.

### 6.2.3 Real Time Control Embedded Software Library (RTCESL)

RTCESL contains a set of functions for the real time control. See documentation in `<install_dir>/middleware/rtcsl_<version>`.

### 6.2.4 Motor control examples

Motor control examples include examples for PMSM and the BLDC control. See the motor control documentation in `<install_dir>/docs/MC`.

## 7 MISRA Compliance

All KSDK drivers comply to MISRA 2004 rules with the exceptions shown in the below figure.

Exception Rules	Description
1.1	All code shall conform to ISO 9899:1990 Programming languages - C, amended and corrected by ISO/IEC 9899/COR1:1995, ISO/IEC 9899/AMD1:1995, and ISO/IEC
2.4	Sections of code should not be commented out.
5.1	Identifiers (internal and external) shall not rely on the significance of more than 31 characters.
6.3	typedefs that indicate size and signedness should be used in place of the basic types.
6.4	Bitfields shall only be defined to be of type unsigned int or signed int.
8.1	Functions shall have prototype declarations and the prototype shall be visible at both the function definition and call.
8.5	There shall be no definitions of objects or functions in a header file.
8.1	All declarations and definitions of objects or functions at file scope shall have internal linkage unless external linkage is required.
8.12	When an array is declared with external linkage, its size shall be stated explicitly or defined implicitly by initialization.
	The value of an expression of integer type shall not be implicitly converted to a different underlying type if: <ul style="list-style-type: none"> <li>a. it is not a conversion to a wider integer type of the same signedness, or</li> <li>b. the expression is complex, or</li> <li>c. the expression is not constant and is a function argument, or</li> <li>d. the expression is not constant and is a return expression.</li> </ul>
10.1	
10.3	The value of a complex expression of integer type shall only be cast to a type that is not wider and of the same signedness as the underlying type of the expression.
11.3	A cast should not be performed between a pointer type and an integral type.
11.4	A cast should not be performed between a pointer to object type and a different pointer to object type.
11.5	A cast shall not be performed that removes any const or volatile qualification from the type addressed by a pointer.
12.2	The value of an expression shall be the same under any order of evaluation that the standard permits.
12.4	The right-hand operand of a logical && or    operator shall not contain side effects.
12.6	The operands of logical operators (&&,   , and !) should be effectively boolean. Expressions that are effectively boolean should not be used as operands to operators other than (&&,   , !, =, ==, !=, and ?:).
12.13	The increment (++) and decrement (--) operators should not be mixed with other operators in an expression.
14.3	Before preprocessing, a null statement shall only occur on a line by itself; it may be followed by a comment, provided that the first character following the null statement is a whitespace character.
14.5	The continue statement shall not be used.
14.7	A function shall have a single point of exit at the end of the function.
16.1	Functions shall not be defined with a variable number of arguments.
17.4	Array indexing shall be the only allowed form of pointer arithmetic.
18.4	Unions shall not be used.
19.1	#include statements in a file should only be preceded by other preprocessor directives or comments.
19.1	In the definition of a function-like macro, each instance of a parameter shall be enclosed in parentheses unless it is used as the operand of # or ##.
20.4	Dynamic heap memory allocation shall not be used.
20.9	The input/output library <stdio.h> shall not be used in production code.

Figure 1. MISRA exceptions

## 8 Known Issues

### 8.1 Maximum file path length in Windows® 7 Operating System


Windows 7 operating system imposes a 260 character maximum length for file paths. When installing the Kinetis SDK, place it in a directory close to the root to prevent file paths from exceeding the maximum character length specified by the Windows operating system. The recommended location is the C:\nxp folder.

### 8.2 Motor Control examples known issue

The supported IDEs are IAR/KDS/KEIL IDEs only. Atollic TrueSTUDIO and ARM GCC IDEs are not supported.

### 8.3 IAR CMSIS-DAP debugger option

An issue occurs using IAR with the CMSIS-DAP debugger interface when the reset option 'Custom (default)' reset is selected. If error and warning messages similar to the figure shown below appear during debug or download, ignore this by clicking the "Yes" button and make it work correctly.



**Figure 2. IAR CMSIS-DAP debugger warning message**

## 9 Driver Log

### ACMP

Current ACMP driver version is 2.0.2.

- 2.0.1
  - Bug Fix:
    - Fix the bug of the function "ACMP\_SetRoundRobinConfig". It will not continue execution but return directly after disabling round robin mode;
- 2.0.2
  - Coding style changes:
    - Change coding style of peripheral base address from "s\_acmpBases" to "s\_acmpBase";

### ADC12

Current ADC12 driver version is 2.0.0.

- 2.0.0
  - Initial version.

### CRC

Current CRC driver version is 2.0.1.

- 2.0.0
  - Initial version.
- 2.0.1
  - Bug fix:
    - DATA and DATALL macro definition moved from header file to source file.

### DMAMUX

Current DMAMUX driver version is 2.0.2.

- 2.0.0
  - Initial version.
- 2.0.1
  - Bug fix:
    - Fix build warning while setting DMA request source in DMAMUX\_SetSourceChange issue, by changing the type of the parameter source from uint8\_t to uint32\_t.
- 2.0.2
  - New feature:

- Add always on enable feature of a certain DMA channel for ULP1 DMAMUX support.

## eDMA

Current eDMA driver version is 2.0.5.

- 2.0.0
  - Initial version.
- 2.0.1
  - Bug fix:
    - Fix the eDMA callback does not check valid status issue in EDMA\_HandleIRQ API.
- 2.0.2
  - Bug fix:
    - Fix incorrect minorLoopBytes type definition in \_edma\_transfer\_config struct. Define minorLoopBytes as uint32\_t instead of uint16\_t.
- 2.0.3
  - Bug fix:
    - Fix the wrong pubweak IRQHandler name issue which will cause re-definition build errors when client sets his/her own IRQHandler, by changing the 32-channel IRQHandler name to DriverIRQHandler.
- 2.0.4
  - Improvement:
    - Add support for SoCs with multiple eDMA instances.
    - Add pubweak DriverIRQHandler for KL28T DMA1 and MCIMX7U5\_M4.
- 2.0.5
  - Improvement:
    - Add pubweak DriverIRQHandler for K32H844P (16 channels shared).

## EWM

Current EWM driver version is 2.0.1.

- 2.0.0
  - Initial version.
- 2.0.1
  - Fix EWM\_Deinit hardfault issue.

## Flash

Current Flash driver version is 2.2.0.

- 2.0.0
  - Initial version.
- 2.1.0
  - New features:
    - Support FTL device in FLASH\_Swap API.
    - Support various pflash start addresses.
    - Add support for KV58 in cache clear function.
  - Bug fix:
    - Compiled execute-in-ram functions as PIC binary code for driver use.
    - Added missed flexram properties.
    - Fixed unaligned variable issue for execute-in-ram function code array.
- 2.2.0
  - New features:
    - Add support for device with secondary flash (KW40).
    - Add support for device with LP flash (K3S/G).
    - Add flash prefetch speculation APIs.

## Driver Log

### FlexIO

Current FlexIO driver version is 2.0.1.

- 2.0.1
  - Bug fix:
    - Fix the Dozen mode configuration error in FLEXIO\_Init API. For enableInDoze = true, the configuration should be 0; for enableInDoze = false, the configuration should be 1.

### FlexIO\_UART

Current FlexIO\_UART driver version is 2.1.2.

- 2.1.0
  - New features:
    - Add Transfer prefix in transactional APIs.
    - Add txSize/rxSize in handle structure to record the transfer size.
  - Bug fix:
    - Add error handling to handle the data count is zero or data buffer is NULL situation.
- 2.1.1
  - Bug fix:
    - Change the API name FLEXIO\_UART\_StopRingBuffer to FLEXIO\_UART\_TransferStopRingBuffer to align with the definition in C file.
- 2.1.2
  - Bug fix:
    - Fix the transfer count calculation issue in FLEXIO\_UART\_TransferGetReceiveCount, FLEXIO\_UART\_TransferGetSendCount, FLEXIO\_UART\_TransferGetReceiveCountDMA, FLEXIO\_UART\_TransferGetSendCountDMA, FLEXIO\_UART\_TransferGetReceiveCountEDMA and FLEXIO\_UART\_TransferGetSendCountEDMA.
    - Fix the Dozen mode configuration error in FLEXIO\_UART\_Init API. For enableInDoze = true, the configuration should be 0; for enableInDoze = false, the configuration should be 1.

### FlexIO\_I2C

Current FlexIO\_I2C driver version is 2.1.2.

- 2.1.0
  - New features:
    - Add Transfer prefix in transactional APIs.
    - Add transferSize in handle structure to record the transfer size.
- 2.1.1
  - Bug fix:
    - Implement the FLEXIO\_I2C\_MasterTransferBlocking API which defined in header file but has no implementation in C file.
- 2.1.2
  - Fix the FlexIO I2C master cannot receive data from I2c slave in high baudrate issue.
  - Fix the FlexIO I2C master cannot receive NAK when master sends non exist addr issue.
  - Fix the FlexIO I2C master cannot get transfer count successfully issue.
  - Fix the FlexIO I2C master cannot receive data successfully when sending the data first issue.
  - Fix the Dozen mode configuration error in FLEXIO\_I2C\_MasterInit API. For enableInDoze = true, the configuration should be 0; for enableInDoze = false, the configuration should be 1.

### FlexIO\_SPI

Current FlexIO\_SPI driver version is 2.1.1.

- 2.1.0
  - New features:

- Add Transfer prefix in transactional APIs.
- Add transferSize in handle structure to record the transfer size.
- Bug fix:
  - Fix the error register address return for 16-bit data write in FLEXIO\_SPI\_GetTxDataRegisterAddress.
  - Provide independent IRQHandler/transfer APIs for Master and slave to fix the baudrate limit issue.
- 2.1.1
  - Bug fix:
    - Fix the bug when FlexIO SPI transfer data in 16 bit per frame mode with eDMA.
    - Fix the bug when FlexIO SPI transfer data in 16 bit per frame and direction is Lsbfirst mode with eDMA and interrupt.
    - Fix the Dozen mode configuration error in FLEXIO\_SPI\_MasterInit/FLEXIO\_SPI\_SlaveInit API. For enableInDoze = true, the configuration should be 0; for enableInDoze = false, the configuration should be 1.
  - Optimization:
    - Add #ifndef/#endif to allow user to change the default tx value at compile time.

## FlexIO\_I2S

Current FlexIO\_I2S driver version is 2.1.1.

- 2.1.0
  - New features:
    - Add Transfer prefix in transactional APIs.
    - Add transferSize in handle structure to record the transfer size.
- 2.1.1
  - Bug fix:
    - Fix FlexIO I2S RX data read error and eDMA address error.
    - Fix FlexIO I2S slave timer compare setting error.

## FTM

Current FTM driver version is 2.0.2.

- 2.0.0
  - Initial version.
- 2.0.1
  - Bug fix:
    - Update the FTM driver to fix write to ELSA and ELSB bits.
    - FTM combine mode: set the COMBINE bit before writing to CnV register.
- 2.0.2
  - Feature:
    - Add to support Quad Decoder feature with new APIs:
      - FTM\_GetQuadDecoderFlags()
      - FTM\_SetQuadDecoderModuloValue()
      - FTM\_GetQuadDecoderCounterValue()
      - FTM\_ClearQuadDecoderCounterValue()

## GPIO

Current GPIO driver version is 2.1.1.

- 2.1.0:
  - API interface change:
    - Adds "pins" or "pin" to some APIs' names.
    - Renames "GPIO\_PinConfigure" to "GPIO\_PinInit".
- 2.1.1
  - API interface change:
    - Adds API for the check attribute bytes.

## Driver Log

### LPI2C

Current LPI2C driver version is 2.1.1.

- 2.0.0
  - Initial version.
- 2.1.0
  - API name change:
    - LPI2C\_MasterTransferCreateHandle -> LPI2C\_MasterCreateHandle
    - LPI2C\_MasterTransferGetCount -> LPI2C\_MasterGetTransferCount
    - LPI2C\_MasterTransferAbort -> LPI2C\_MasterAbortTransfer
    - LPI2C\_MasterTransferHandleIRQ -> LPI2C\_MasterHandleInterrupt
    - LPI2C\_SlaveTransferCreateHandle -> LPI2C\_SlaveCreateHandle
    - LPI2C\_SlaveTransferGetCount -> LPI2C\_SlaveGetTransferCount
    - LPI2C\_SlaveTransferAbort -> LPI2C\_SlaveAbortTransfer
    - LPI2C\_SlaveTransferHandleIRQ -> LPI2C\_SlaveHandleInterrupt
- 2.1.1
  - Bug fix:
    - Disable auto stop feature in eDMA driver, previously the autostop feature is enabled at transfer when transfer with stop flag. If previous transfer without stop flag, then when start a new transfer with stop flag, because the auto stop feature is enabled, so the stop flag will be sent before starting the new transfer and the start flag can not successfully sent, so the transfer can not start.
    - Change default slave configuration with address stall false.

### LPIT

Current LPIT driver version is 2.0.0.

- 2.0.0
  - Initial version.

### LPSPI

Current LPSPI driver version is 2.0.1.

- 2.0.0
  - Initial version.
- 2.0.1
  - Bug Fix:
    - The clock source should divided by PRESCALE setting in LPSPI\_MasterSetDelayTimes function.
    - Fix the bug that LPSPI\_MasterTransferBlocking function would hang in some corner cases.

### LPTMR

Current LPTMR driver version is 2.0.0

- 2.0.0
  - Initial version.

### LPUART

Current LPUART driver version is 2.2.1.

- 2.1.0
  - Update transactional APIs.
- 2.1.1
  - Remove needless check of event flags and assert in LPUART\_RTOS\_Receive.
  - Wait always for rx event flag in LPUART\_RTOS\_Receive.
- 2.2.0
  - Add seven data bits and msb support.
- 2.2.1

- Add separate RX, TX irq number support.

## MMDVSQ

Current MMDVSQ driver version is 2.0.2.

- 2.0.0
  - Initial version.
- 2.0.1
  - Other changes:
    - Change name of MMDVSQ\_GetDivideRemainder and MMDVSQ\_GetDivideQuotient functions.
- 2.0.2
  - Bug fix:
    - Fix MMDVSQ\_GetExecutionStatus function get execution status wrong.

## PDB

Current PDB driver version is 2.0.1.

- 2.0.0
  - Initial version.
- 2.0.1
  - Change PDB register base array to const.

## PMC

Current PMC driver version is 2.0.0.

- 2.0.0
  - Initial version.

## PORT

Current PORT driver version is 2.0.2.

- 2.0.1:
  - Miscellaneous changes:
    - Adds "const" in function parameter.
    - Updates some enumeration variables' names.
- 2.0.2:
  - Miscellaneous changes:
    - Adds feature guard macros in the driver.

## PWT

Current PWT driver version is 2.0.0.

- 2.0.0
  - Initial version.

## RCM

Current RCM driver version is 2.0.1.

- 2.0.0
  - Initial version.
- 2.0.1
  - [KPSDK-10249] Fix kRCM\_SourceSw bit shift issue.

## RTC

Current RTC driver version is 2.0.0.

## Driver Log

- 2.0.0
  - Initial version.

## SIM

Current SIM driver version is 2.0.0.

- 2.0.0
  - Initial version.

## SMC

Current SMC driver version is 2.0.2.

- 2.0.0
  - Initial version.
- 2.0.1
  - Miscellaneous changes:
    - Update for KL8x.
- 2.0.2
  - Bug Fix:
    - Add DSB before WFI, add ISB after WFI.
  - Miscellaneous changes:
    - Update SMC\_SetPowerModeVlpw implementation.

## TRGMUX

Current TRGMUX driver version is 2.0.0.

- 2.0.0
  - Initial version.

## TSL\_V5

Current TSL\_V5 version is 2.0.0.

- 2.0.0
  - Initial version.

## WDOG32

Current WDOG32 driver version is 2.0.0.

- 2.0.0
  - Initial version.

## CLOCK

Current CLOCK driver version is 2.1.1.

- 2.0.0
  - Initial version.
- 2.1.0
  - Other changes:
    - Merge fsl\_scg and fsl\_osc into fsl\_clock.
- 2.1.1
  - Improvement:
    - Change reserved bit fields in \_scg\_sys\_clk\_config struct into unnamed bit fields.

## 10 Middleware Log

### DMA\_MANAGER

Current DMA\_MANAGER driver version is 2.0.0

- 2.0.0
  - Initial version

### MOTOR\_CONTROL for KSDK

Current version is 1.1.0

- 1.1.0
  - Initial version

### RTCESL for KSDK

Current version is 4.3

- 4.3
  - Initial version

## 11 RTOS Log

### FreeRTOS OS for KSDK

The current version is FreeRTOS OS 8.2.3. The original package is available at [freertos.org](http://freertos.org).

- 8.2.3
  - New features:
    - Added tickless idle mode support
    - Added a template application for Kinetis Expert (KEx) tool (template\_application)
  - Changes:
    - Reduced the folder structure to keep only Kinetis-related information

### μC/OS-II OS for KSDK

The current version is μC/OS-II OS V2.92.11

- 2.92.11
  - New features:
    - Added a template application for the Kinetis Expert (KEx) tool (template\_application)
  - Changes:
    - Reduced the folder structure to keep only Kinetis-related information
    - Added wrappers to adapt PendSV\_Handler and SysTick\_Handler. Related files are located in rtos\ucosii\_<version>\uCOS-II\Ports\ARM-Cortex-Mx\Generic\<compiler>\fsl\_isr\_wrapper.S

### μC/OS-III OS for KSDK

The current version is μC/OS-III OS V3.05.01

- V3.05.01
  - New features:
    - Added a template application for the Kinetis Expert (KEx) tool (template\_application)
  - Bug fix:

## Revision history

- [KPSDK-7247] Downgraded port files from V3.05.01 to V3.05.00 because of the context switch issue
- Changes:
  - Reduced the folder structure to keep only Kinetis-related information

## 12 Revision history

This table summarizes the revisions to this document.

**Table 3. Revision history**

Revision number	Date	Substantive changes
0	08/2016	Initial release

---

**How to Reach Us:**

**Home Page:**

[www.nxp.com](http://www.nxp.com)

**Web Support:**

[www.nxp.com/support](http://www.nxp.com/support)

Information in this document is provided solely to enable system and software implementers to use Freescale products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document.

Freescale reserves the right to make changes without further notice to any products herein. Freescale makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. Freescale does not convey any license under its patent rights nor the rights of others. Freescale sells products pursuant to standard terms and conditions of sale, which can be found at the following address: [www.nxp.com/SalesTermsandConditions](http://www.nxp.com/SalesTermsandConditions).

Freescale, the Freescale logo, and Kinetis are trademarks of Freescale Semiconductor, Inc., Reg. U.S. Pat. & Tm. Off. All other product or service names are the property of their respective owners. ARM, ARM Powered Logo, and Cortex are registered trademarks of ARM limited (or its subsidiaries) in the EU and/or elsewhere. All rights reserved.

© 2016 Freescale Semiconductor, Inc.

