

Test Report

號碼(No.): ETR23200365 日期(Date): 09-Feb-2023 頁數(Page): 1 of 6

MITSUBISHI MATERIALS CORPORATION 12-6, TECHNO-PARK, SANDA, HYOGO 669-1339, JAPAN

以下測試樣品係由申請廠商所提供及確認 (The following sample(s) was/were submitted and identified by the

applicant as):

送樣廠商(Sample Submitted By) : MITSUBISHI MATERIALS CORPORATION

樣品名稱(Sample Name) : MULAS

樣品型號(Style/Item No.) : MULAS W25-VMS-HC1, W-VMS-HC1

收件日(Sample Receiving Date) : 02-Feb-2023

測試期間(Testing Period) : 02-Feb-2023 to 09-Feb-2023

測試需求(Test Requested) : 依據客戶指定,參考RoHS指令2011/65/EU Annex II測試鎘、鉛、汞、六價鉻、

多溴聯苯、多溴聯苯醚。 (As specified by client, with reference to RoHS Directive 2011/65/EU Annex II to determine Cadmium, Lead, Mercury,

Cr(VI), PBBs, PBDEs contents in the submitted sample(s).)

測試結果(Test Results) : 請參閱下一頁 (Please refer to following pages.)

結 論(Conclusion) : 根據客戶所提供的樣品,其鎘、鉛、汞、六價鉻、多溴聯苯、多溴聯苯醚的測試

結果符合RoHS 2011/65/EU Annex II之限值要求。 (Based on the performed tests on submitted sample(s), the test results of Cadmium, Lead, Mercury,

Cr(VI), PBBs, PBDEs comply with the limits as set by RoHS Directive

2011/65/EU Annex II.)

Troy Chang / Department Malager Signed for and on behalf of SGS TAIWAN LTD.
Chemical Laboratory - Taipei



PIN CODE: DE6D6748



Test Report

號碼(No.): ETR23200365 日期(Date): 09-Feb-2023 頁數(Page): 2 of 6

MITSUBISHI MATERIALS CORPORATION 12-6, TECHNO-PARK, SANDA, HYOGO 669-1339, JAPAN

測試部位敘述 (Test Part Description)

No.1 : 藍色液體 (BLUE LIQUID)

測試結果 (Test Results)

測試項目	測試方法	單位	MDL	結果	限值
(Test Items)	(Method)	華血 (Unit)	WIDE	(Result)	(Limit)
(rest items)	(Wethou)	(OIIIt)		No.1	(Lilling)
鎘 (Cd) (Cadmium (Cd))	 参考IEC 62321-5: 2013 · 以感應耦合電	mg/kg	2	n.d.	100
	療發射光譜儀分析。(With reference to	mg/kg	2	II.U.	100
鉛 (Pb) (Lead (Pb))	IEC 62321-5: 2013, analysis was	mg/kg	2	n.d.	1000
VI (FD) (Lead (FD))	performed by ICP-OES.)	mg/kg	۷	n.u.	1000
汞 (Hg) (Mercury (Hg))	參考IEC 62321-4: 2013+ AMD1: 2017 ·	mg/kg	2	n.d.	1000
(rig) (Weredry (rig))	以感應耦合電漿發射光譜儀分析。(With	mg/kg	2	n.a.	1000
	reference to IEC 62321-4: 2013+				
	AMD1: 2017, analysis was performed				
	by ICP-OES.)				
六價鉻 Cr(VI) (Hexavalent Chromium	参考IEC 62321-7-2: 2017 · 以紫外光-可見光	mg/kg	8	n.d.	1000
Cr(VI))	分光光度計分析。(With reference to IEC	٥, ٥			
	62321-7-2: 2017, analysis was performed				
	by UV-VIS.)				
一溴聯苯 (Monobromobiphenyl)	· 參考IEC 62321-6: 2015·以氣相層析儀/ 質譜儀分析。(With reference to IEC 62321-6: 2015, analysis was performed by GC/MS.)	mg/kg	5	n.d.	-
二溴聯苯 (Dibromobiphenyl)		mg/kg	5	n.d.	-
三溴聯苯 (Tribromobiphenyl)		mg/kg	5	n.d.	-
四溴聯苯 (Tetrabromobiphenyl)		mg/kg	5	n.d.	-
五溴聯苯 (Pentabromobiphenyl)		mg/kg	5	n.d.	-
六溴聯苯 (Hexabromobiphenyl)		mg/kg	5	n.d.	-
七溴聯苯 (Heptabromobiphenyl)		mg/kg	5	n.d.	-
八溴聯苯 (Octabromobiphenyl)		mg/kg	5	n.d.	-
九溴聯苯 (Nonabromobiphenyl)		mg/kg	5	n.d.	-
十溴聯苯 (Decabromobiphenyl)		mg/kg	5	n.d.	-
多溴聯苯總和 (Sum of PBBs)		mg/kg	-	n.d.	1000



Test Report

號碼(No.): ETR23200365 日期(Date): 09-Feb-2023 頁數(Page): 3 of 6

MITSUBISHI MATERIALS CORPORATION 12-6, TECHNO-PARK, SANDA, HYOGO 669-1339, JAPAN

測試項目	測試方法	單位	MDL	結果	限值
(Test Items)	(Method)	(Unit)		(Result)	(Limit)
				No.1	
一溴聯苯醚 (Monobromodiphenyl ether)	参考IEC 62321-6: 2015·以氣相層析儀/ 質譜儀分析。(With reference to IEC 62321-6: 2015, analysis was performed by GC/MS.)	mg/kg	5	n.d.	-
二溴聯苯醚 (Dibromodiphenyl ether)		mg/kg	5	n.d.	-
三溴聯苯醚 (Tribromodiphenyl ether)		mg/kg	5	n.d.	-
四溴聯苯醚 (Tetrabromodiphenyl ether)		mg/kg	5	n.d.	-
五溴聯苯醚 (Pentabromodiphenyl ether)		mg/kg	5	n.d.	-
六溴聯苯醚 (Hexabromodiphenyl ether)		mg/kg	5	n.d.	-
七溴聯苯醚 (Heptabromodiphenyl ether)		mg/kg	5	n.d.	-
八溴聯苯醚 (Octabromodiphenyl ether)		mg/kg	5	n.d.	-
九溴聯苯醚 (Nonabromodiphenyl ether)		mg/kg	5	n.d.	-
十溴聯苯醚 (Decabromodiphenyl ether)		mg/kg	5	n.d.	-
多溴聯苯醚總和 (Sum of PBDEs)		mg/kg	-	n.d.	1000

備註(Note):

- 1. mg/kg = ppm; 0.1wt% = 0.1% = 1000ppm
- 2. MDL = Method Detection Limit (方法偵測極限值)
- 3. n.d. = Not Detected (未檢出); 小於MDL / Less than MDL
- 4. "-" = Not Regulated (無規格值)
- 5. 除非另有說明,參照ILAC-G8:09/2019,採用簡單二元(w=0)允收規則進行符合性判定;根據此規則,符合性結果之判定係以測試結果與限值做比較。(Unless otherwise stated, the decision rule for conformity reporting is based on Binary Statement for Simple Acceptance Rule (w=0) stated in ILAC-G8:09/2019. According to this rule, the judgement of conformity is based on the comparing test results with limits.)



Test Report

號碼(No.): ETR23200365 日期(Date): 09-Feb-2023


頁數(Page): 4 of 6

MITSUBISHI MATERIALS CORPORATION 12-6, TECHNO-PARK, SANDA, HYOGO 669-1339, JAPAN

重金屬流程圖 / Analytical flow chart of heavy metal

根據以下的流程圖之條件,樣品已完全溶解。(六價鉻測試方法除外)

These samples were dissolved totally by pre-conditioning method according to below flow chart. (Cr^{6+} test method excluded)






Test Report

MITSUBISHI MATERIALS CORPORATION
12-6, TECHNO-PARK, SANDA, HYOGO 669-1339, JAPAN

日期(Date): 09-Feb-2023 頁數(Page): 5 of 6

多溴聯苯/多溴聯苯醚分析流程圖 / Analytical flow chart - PBBs/PBDEs

號碼(No.): ETR23200365





Test Report

MITSUBISHI MATERIALS CORPORATION

12-6, TECHNO-PARK, SANDA, HYOGO 669-1339, JAPAN

號碼(No.): ETR23200365

日期(Date): 09-Feb-2023 頁數(Page): 6 of 6

* 照片中如有箭頭標示·則表示為實際檢測之樣品/部位. * (The tested sample / part is marked by an arrow if it's shown on the photo.)

ETR23200365



** 報告結尾 (End of Report) **