




Connected Radio

Last Updated: Dec 5, 2023

In-car audio systems today have changed from basic radio and CD systems to connected systems that can access content from various sources. Customers are expecting to plug in USB drives, insert SD cards or to connect their Bluetooth® hands-free devices even in the low-end segment.

NXP's comprehensive portfolio of AM/FM tuner and amplifier solutions and Arm®-based microprocessors offer a scalable set of product families that helps you design entry level connected radio and infotainment systems with USB, AM/FM and Bluetooth connectivity with enhanced audio and user interface capabilities.

Connected Radio Block Diagram



■ NXP Technology ■ Non NXP Technology □ Optional Technology

Recommended Products for Connected Radio

MPU	<ul style="list-style-type: none"> • i.MX6UL: i.MX 6UltraLite Processor - Low-Power, Secure, Arm® Cortex®-A7 Core • i.MX6SX: i.MX 6SoloX Processors - Heterogeneous Processing with Arm® Cortex®-A9 and Cortex-M4 Cores
GPIO	<ul style="list-style-type: none"> • PCAL9722: 22-Bit SPI I/O Expander with Agile I/O Features • PCAL9714: 14-Bit SPI I/O Expander with Agile I/O Features
Radio Chipset	<ul style="list-style-type: none"> • TDF8541: I²C-Bus Controlled 4 x 45 W Power Amplifier • SAF4000: Multi-Standard Software Defined Radio Processor With Integrated Audio
Audio Amplifier	<ul style="list-style-type: none"> • Car Audio Amplifiers: Car Audio Amplifiers

RF Amplifier	<ul style="list-style-type: none"> • TLH501x: ALNA – Low Noise Active Antenna Amplifier
Display/Push Button Driver	<ul style="list-style-type: none"> • Automotive LCD Drivers: Automotive LCD Drivers • Automotive Lighting LED Driver ICs: Automotive Lighting - LED Driver ICs
CD Drive Controller	<ul style="list-style-type: none"> • Audio Converters: Audio Converters
CAN/LIN Transceiver	<ul style="list-style-type: none"> • TJA144x: Automotive CAN FD Transceiver Family • TJA1044: High-Speed CAN Transceiver with Standby Mode - Mantis Family • TJA1043: High-Speed CAN Transceiver with Standby and Sleep Mode • Automotive LIN Solutions: Automotive LIN Solutions • TJA1463: CAN Signal Improvement Capability Transceiver with Sleep Mode
Power Management IC	<ul style="list-style-type: none"> • FS5600: Automotive Dual Buck Regulator and Controller with Voltage Monitors and Watchdog Timer • MMPF0100: 14-Channel Configurable PMIC • PF8101-PF8201: 9-Channel Power Management Integrated Circuit (PMIC) for High-Performance Processing Applications • VR5500: High Voltage PMIC with Multiple SMPS • VR5510: Multi-Channel (9) PMIC for S32G Processor – 8 High Power, 1 Low Power, Fit for ASIL D Safety Level • PF8100-PF8200: 12-Channel Power Management Integrated Circuit (PMIC) for High-Performance Processing Applications • PF7100: 7-Channel Power Management Integrated Circuit for High Performance Applications, Fit for ASIL B Safety Level • PF5020: Multi-Channel (5) PMIC for Automotive Applications – 4 High Power and 1 Low Power, Fit for ASIL B Safety Level • PF5024: Multi-Channel (4) PMIC for Automotive Applications – 4 High Power, Fit for ASIL B Safety Level
Sensors	<ul style="list-style-type: none"> • Sensors: Sensors
NFC Tag	<ul style="list-style-type: none"> • NCx3310: NFC Forum-Compliant Tag IC with I²C for Automotive
Bluetooth	<ul style="list-style-type: none"> • 88Q9098: 2.4/5 GHz Dual-Band 2x2 Wi-Fi[®] 6 (802.11ax) + Bluetooth[®] 5.3 Automotive Solution
Software	<ul style="list-style-type: none"> • i.MX Software: i.MX Software and Development Tools • Professional Support for Processors and Microcontrollers • Automotive Partner Services: Automotive Partner Services
Automotive Ethernet	<ul style="list-style-type: none"> • TJA1120: TJA1120 Automotive Ethernet PHY 100BASE-T1, ASIL B and TC-10 • TJA1104: MACsec Enabled 100BASE-T1 Ethernet PHY • TJA1103: ASIL B Compliant 100BASE-T1 Ethernet PHY • TJA1102-TJA1102S: TJA1102/TJA1102A: Dual Port 100BASE-T1 PHY Transceiver • TJA1101: TJA1101/TJA1101B: Robust, Low Power 100BASE-T1 PHY Transceiver
NFC Tag	<ul style="list-style-type: none"> • NCx3310: NFC Forum-Compliant Tag IC with I²C for Automotive
CAN / LIN Transceiver	<ul style="list-style-type: none"> • TJA1128: LIN Mini System Basis Chip

View our complete solution for [Connected Radio](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2024 NXP B.V.