




# Electric Pumps

Last Updated: Nov 12, 2021

Electrical pumps are more flexible than mechanical pumps as they can be placed closer to what they are pumping when creating a vacuum to tap fuel, water, oil, or coolant from one place to another.


NXP solutions for electrical pumps can be used in a variety of engines, motors, plumbing, and cooling systems to help ensure economic liquid management and optimal temperatures for efficient engine operation. We assist in delivering more accurate continuous flow and pressure or only-when-required operation within automotive engine applications.

## Electric pumps Block Diagram



MCU	<ul style="list-style-type: none"> <li>• <a href="#">S32K3 Microcontrollers for General Purpose</a></li> <li>• <a href="#">S32K1 Microcontrollers for General Purpose</a></li> <li>• <a href="#">S12VR</a>: S12VR Mixed-Signal MCU for Automotive &amp; Industrial Relay Based Motor Control</li> <li>• <a href="#">S12ZVM</a>: S12ZVM Mixed-Signal MCU for Automotive &amp; Industrial Motor Control Applications</li> </ul>
Physical I/F	<ul style="list-style-type: none"> <li>• <a href="#">TJA1029</a>: LIN 2.2A/SAE J2602 Transceiver with TXD Dominant Timeout</li> <li>• <a href="#">UJA113xHW</a>: Buck/Boost High-Speed CAN/Dual LIN System Basis Chip Family</li> </ul>
Pre Driver Module	<ul style="list-style-type: none"> <li>• <a href="#">MC33937</a>: 3-Phase Field Effect Transistor Pre-driver</li> <li>• <a href="#">MC33883</a>: H-Bridge, Pre-driver, 5.5-55 V, 1 A, 100 kHz</li> <li>• <a href="#">GD3000</a>: 3-Phase Brushless Motor Pre-Driver</li> </ul>
H-Bridge/ 3-ph Bridge	<ul style="list-style-type: none"> <li>• <a href="#">MC33931</a>: H-Bridge, Brushed DC Motor Driver, 5-28 V, 5 A, 11 kHz</li> <li>• <a href="#">MC33926</a>: H-Bridge, Brushed DC Motor Driver, 5-28 V, 5 A, 20 kHz</li> <li>• <a href="#">HB2001</a>: SPI Programmable 10 A H-Bridge Brushed DC Motor Driver</li> <li>• <a href="#">HB2000</a>: SPI Programmable 10 A H-Bridge Brushed DC Motor Driver</li> </ul>


## Water/Fuel pump Block Diagram



### Recommended Products for Water/Fuel pump

MCU	<ul style="list-style-type: none"> <li>• <a href="#">S12VR</a>: S12VR Mixed-Signal MCU for Automotive &amp; Industrial Relay Based Motor Control</li> <li>• <a href="#">S12ZVM</a>: S12ZVM Mixed-Signal MCU for Automotive &amp; Industrial Motor Control Applications</li> </ul>
H-Bridge/ 3-ph Bridge	<ul style="list-style-type: none"> <li>• <a href="#">MC33931</a>: H-Bridge, Brushed DC Motor Driver, 5-28 V, 5 A, 11 kHz</li> <li>• <a href="#">MC33926</a>: H-Bridge, Brushed DC Motor Driver, 5-28 V, 5 A, 20 kHz</li> <li>• <a href="#">HB2001</a>: SPI Programmable 10 A H-Bridge Brushed DC Motor Driver</li> <li>• <a href="#">HB2000</a>: SPI Programmable 10 A H-Bridge Brushed DC Motor Driver</li> </ul>
FreeMaster	<ul style="list-style-type: none"> <li>• <a href="#">FreeMASTER Run-Time Debugging Tool</a></li> </ul>

## Oil pump Block Diagram



### Recommended Products for Oil pump

MCU	<ul style="list-style-type: none"> <li>• <a href="#">S32K1 Microcontrollers for General Purpose</a></li> <li>• <a href="#">S12VR</a>: S12VR Mixed-Signal MCU for Automotive &amp; Industrial Relay Based Motor Control</li> <li>• <a href="#">S12ZVM</a>: S12ZVM Mixed-Signal MCU for Automotive &amp; Industrial Motor Control Applications</li> </ul>
Physical I/F	<ul style="list-style-type: none"> <li>• <a href="#">TJA1021</a>: LIN 2.1/SAE J2602 Transceiver</li> <li>• <a href="#">UJA113xHW</a>: Buck/Boost High-Speed CAN/Dual LIN System Basis Chip Family</li> </ul>
H-Bridge/ 3-ph Bridge	<ul style="list-style-type: none"> <li>• <a href="#">MC33937</a>: 3-Phase Field Effect Transistor Pre-driver</li> <li>• <a href="#">GD3000</a>: 3-Phase Brushless Motor Pre-Driver</li> </ul>
FreeMaster	<ul style="list-style-type: none"> <li>• <a href="#">FreeMASTER Run-Time Debugging Tool</a></li> </ul>
H-Bridge/ 3-ph Bridge	<ul style="list-style-type: none"> <li>• <a href="#">MC33931</a>: H-Bridge, Brushed DC Motor Driver, 5-28 V, 5 A, 11 kHz</li> <li>• <a href="#">MC33926</a>: H-Bridge, Brushed DC Motor Driver, 5-28 V, 5 A, 20 kHz</li> <li>• <a href="#">HB2001</a>: SPI Programmable 10 A H-Bridge Brushed DC Motor Driver</li> <li>• <a href="#">HB2000</a>: SPI Programmable 10 A H-Bridge Brushed DC Motor Driver</li> </ul>

View our complete solution for [Electric Pumps](#).

**Note:** The information on this document is subject to change without notice.

**[www.nxp.com](http://www.nxp.com)**

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2021 NXP B.V.