




Low-Power PowerQUICC® II Pro Processor with DDR2, TDM, PCI, PCI Express, 1 GB Ethernet, Security, USB

MPC8314E

Last Updated: Oct 17, 2022

Today's digital home consumers require a robust converged platform that supports distribution of voice, video and data simultaneously. The MPC8314E provides a high-performance Power Architecture® e300 core up to 400 MHz with 16K I/D L1 cache, integrated high-speed USB 2.0 with PHY and x2 PCI Express® controllers that help to reduce overall BOM cost. The system-on-chip (SoC) also includes two Gigabit Ethernet (GbE) controllers for network connectivity, TDM interface for supporting multiple channels of VoIP and a security engine for encryption algorithm offload. The MPC8314E, based in 90 nm process technology, provides high integration that simplifies board design and provides a cost-effective solution for applications such as converged home gateway supporting VoIP, Wi-Fi and streaming high-definition video content throughout the home.

Freescale PowerQUICC MPC8314E Communications Processor Block Diagram Block Diagram



View additional information for [Low-Power PowerQUICC[®] II Pro Processor with DDR2, TDM, PCI, PCI Express, 1 GB Ethernet, Security, USB](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2023 NXP B.V.