



# FRDM Development Board for 96 MHz KE17Z/KE13Z/KE12Z with 512 KB Flash MCUs


## FRDM-KE17Z512

Last Updated: May 28, 2024

FRDM-KE17Z512 are a compact and scalable development boards for rapid prototyping of 96 MHz KE17Z, KE13Z, KE12Z with 512 KB Flash MCUs. They offer industry-standard headers for easy access to the MCU's I/Os, integrated open-standard serial interfaces, external flash memory and an onboard MCU-Link debugger. Additional tools like our [Expansion Board Hub](#) for add-on boards and the [Application Code Hub](#) for software examples are available through the [MCUXpresso Developer Experience](#).

The FRDM-KE17Z512 is designed to work in standalone mode or as the main board of FRDM-TOUCH, FRDM-MC-LVBLDC and Arduino® boards. This FRDM board is compatible with DC 5 V and 3.3 V power supply and features a KE17Z512, a device boasting up to 512 KB Flash and 96 KB SRAM and numerous analog and digital peripherals.

# FRDM-KE17Z512 Block Diagram Block Diagram



View additional information for [FRDM Development Board for 96 MHz KE17Z/KE13Z/KE12Z with 512 KB Flash MCUs](#).

**Note:** The information on this document is subject to change without notice.

**www.nxp.com**

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2024 NXP B.V.