



Auto direction sensing dual supply

NTB0101AGW

Not Recommended for New Designs


This page contains information on a product that is not recommended for new designs.

Last Updated: Apr 8, 2022

The NTB0101A is a 1-bit, dual supply translating transceiver with auto direction sensing, that enables bidirectional voltage level translation. It consists of two 1-bit I/O ports (A and B), one output enable input (OE) and two supply pins (VCC(A) and VCC(B)). VCC(A) can be supplied at any voltage between 1.2 V and 3.6 V. VCC(B) can be supplied at any voltage between 1.65 V and 5.5 V. This flexibility allows translation between any of the low voltage nodes (1.2 V, 1.5 V, 1.8 V, 2.5 V, 3.3 V and 5.0 V).

Pins A and OE are referenced to VCC(A) and pin B is referenced to VCC(B). A HIGH level at pin OE causes the outputs to assume a high-impedance OFF-state. This device is fully specified for partial power-down applications using IOFF. The IOFF circuitry disables the output, preventing damage of the device due to backflow current, when it is powered down.

NTB0101A Block Diagram Block Diagram



View additional information for [Auto direction sensing dual supply](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2023 NXP B.V.