



Dual Bidirectional 1:2 Switch and VLT for I3C Interface


P3S0210BQ

Last Updated: Mar 21, 2026

P3S0210BQ is a dual bidirectional I3C-bus 1:2 and 2:1 switch and voltage level translator that can be used for both open-drain as well as push-pull application allowing for I3C-bus and other applications like I²C-bus, SMBus and SPI protocols in a DHVQFN14 package.

The controller, peripheral and interface ports can be set from 0.72 V to 3.63 V and must be less than or equal to the reference supply, which can be set between 1.62 V to 3.63 V. This part is specified for partial power down applications disabling the output which prevents damaging backflow current through the device.

P3S0210BQ Block Diagram



View additional information for [Dual Bidirectional 1:2 Switch and VLT for I3C Interface](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2026 NXP B.V.