



# Parallel Bus to 1 Channel Fm+ I<sup>2</sup>C-Bus Controller

## PCA9661B

### Not Recommended for New Designs

This page contains information on a product that is not recommended for new designs.

Last Updated: Jun 13, 2022

The PCA9661 is an advanced single leader mode I<sup>2</sup>C-bus controller. It is a fourth generation bus controller designed for data intensive I<sup>2</sup>C-bus data transfers. It has one I<sup>2</sup>C-bus channel with data rates up to 1 Mbits/s using the Fast-mode Plus (Fm+) open-drain topology. The serial channel has a generous 4352 byte data buffer which makes the PCA9661 the ideal companion to any CPU that needs to transmit and receive large amounts of serial data with minimal interruptions.

The PCA9661 is a 8-bit parallel-bus to I<sup>2</sup>C-bus protocol converter. It can be configured to communicate with up to 64 followers in one serial sequence with no intervention from the CPU. The controller also has a sequence loop control feature that allows it to automatically retransmit a stored sequence.

Its onboard oscillator and PLL allow the controller to generate the clocks for the I<sup>2</sup>C-bus and for the interval timer used in sequence looping. This feature greatly reduces CPU overhead when data refresh is required in fault tolerant applications.


An external trigger input allows data synchronization with external events. The trigger signal controls the rate at which a stored sequence is re-transmitted over the I<sup>2</sup>C-bus.

Error reporting is handled at the transaction level, channel level, and controller level. A simple interrupt tree and interrupt masks allow further customization of interrupt management.

The controller parallel bus interface runs at 3.3 V and the I<sup>2</sup>C-bus I/Os logic levels are referenced to a dedicated VDD(IO) input pin with a range of 3.0 V to 5.5 V.

### PCA9661 BLOCK DIAGRAM Block Diagram





View additional information for [Parallel Bus to 1 Channel Fm+ I2C-Bus Controller](#).

**Note:** The information on this document is subject to change without notice.

---

**[www.nxp.com](http://www.nxp.com)**

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2023 NXP B.V.