



Low-Power Multi-Channel UHF RF Wireless Platform

OL2385AHN


Last Updated: Apr 12, 2022

The OL2385 device is a radio frequency transceiver with an embedded MCU designed for a wide range of industrial and home applications requiring very high link budget for bidirectional RF communication.

- 2-way RF channel with the most common modulation schemes for networking applications covering full range of frequency bands from 160 up to 960 MHz
- Includes an embedded MCU to allow complete subsystem functions to be implemented. All device functions are included in a single CMOS die
- Strong radio performance with high sensitivity, very good phase noise and good image rejection
- Turnkey system solution with Kinetis and LPC SPI/UART drivers offering the broadest choice of Arm® based MCUs with integrated peripherals on the market today
- W-MBUS, SIGFOX® and IEEE802.15.4 are tested for standards compliance and certified where applicable

OL2385 Industrial RF Transceiver - Block Diagram Block Diagram

OL2385 SIMPLIFIED BLOCK DIAGRAM



View additional information for [Low-Power Multi-Channel UHF RF Wireless Platform](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2022 NXP B.V.