




# Respiratory Care

Last Updated: Oct 24, 2022

Respiratory care includes the promotion of optimum cardiopulmonary function and health, according to the AARC. To improve breathing, respiratory therapists give patients oxygen, make use of ventilators or respirators, and administer medication for the lungs.

NXP offers a broad portfolio of sensors and microcontrollers, such as Kinetis and i.MX RT crossover MCU families, capable of delivering sensing and precision for medical equipment and solutions used in respiratory care.

## Ventilator Respirators Block Diagram



### Recommended Products for Ventilator Respirators

Main Processor MCU / MPU

- [LPC553x/S3x: Advanced Analog Arm®Cortex®-M33-Based MCU Family](#)
- [i.MX 8M Nano Family - Arm® Cortex®-A53, Cortex-M7](#)
- [KV3x: Kinetis® KV3x-100–120 MHz, Advanced 3ph FOC / Sensorless Motor Control MCUs based on Arm® Cortex®-M4](#)

	<ul style="list-style-type: none"> <li>• <a href="#">i.MX RT1020 Crossover MCU with Arm® Cortex®-M7 Core</a></li> </ul>
Temperature	<ul style="list-style-type: none"> <li>• <a href="#">P3T1755DP</a>: I3C/I<sup>2</sup>C-Bus ±0.5 °C Accurate Digital Temperature Sensor</li> <li>• <a href="#">P3T1085UK</a>: I3C/I<sup>2</sup>C-Bus ±0.5 °C Accurate Digital Temperature Sensor</li> </ul>
Gauge Pressure Sensor	<ul style="list-style-type: none"> <li>• <a href="#">MPXx5050</a>: Differential and Gauge Pressure Sensor (-50 to 50 kPa)</li> </ul>
BLE	<ul style="list-style-type: none"> <li>• <a href="#">2.4/5 GHz Dual-Band 1x1 Wi-Fi® 4 (802.11n) + Bluetooth® 5.2 Solution</a></li> <li>• <a href="#">IW612</a>: 2.4/5 GHz Dual-Band 1x1 Wi-Fi® 6 (802.11ax) + Bluetooth® 5.2 + 802.15.4 Tri-Radio Solution</li> </ul>
USB Type-C	<ul style="list-style-type: none"> <li>• <a href="#">USB Type C</a>: USB Type-C Plug'n Play: Efficient Data and Power Delivery</li> </ul>
NFC	<ul style="list-style-type: none"> <li>• <a href="#">PN7160</a>: NFC Plug and Play Controller with Integrated Firmware and NCI Interface</li> </ul>
Secure Element	<ul style="list-style-type: none"> <li>• <a href="#">EdgeLock® SE050</a>: Plug &amp; Trust Secure Element Family – Enhanced IoT security with high flexibility</li> </ul>
PMIC	<ul style="list-style-type: none"> <li>• <a href="#">PCA9450</a>: Power Management IC (PMIC) for i.MX 8M Mini/Nano/Plus</li> <li>• <a href="#">PF8100-PF8200</a>: 12-Channel Power Management Integrated Circuit (PMIC) for High-Performance Processing Applications</li> <li>• <a href="#">PCA9420</a>: PMIC for Low Power Applications</li> <li>• <a href="#">Load Switches</a>: Load Switches</li> </ul>
AC/DC	<ul style="list-style-type: none"> <li>• <a href="#">AC-DC Solutions</a>: AC-DC Solutions</li> </ul>
LCD Display Driver	<ul style="list-style-type: none"> <li>• <a href="#">PCF8551</a>: Universal 36 × 4 LCD Segment Driver</li> <li>• <a href="#">LCD Graphic Drivers</a>: LCD Graphic Drivers</li> <li>• <a href="#">LCD Segment Drivers</a>: LCD Segment Drivers</li> </ul>
Real Time Clock	<ul style="list-style-type: none"> <li>• <a href="#">PCF2131</a>: Nano-Power Highly Accurate RTC with Integrated Quartz Crystal</li> </ul>
LED Driver	<ul style="list-style-type: none"> <li>• <a href="#">PCA9956BTW</a>: 24-Channel Fm+ I<sup>2</sup>C-Bus 57 MA/20 V Constant-Current LED Driver</li> </ul>
Wi-fi	<ul style="list-style-type: none"> <li>• <a href="#">2.4/5 GHz Dual-Band 1x1 Wi-Fi® 4 (802.11n) + Bluetooth® 5.2 Solution</a></li> <li>• <a href="#">KW39/38/37</a>: 32-Bit Bluetooth 5.0 Long-Range MCUs with CAN FD and LIN Bus Options, Arm® Cortex®-M0+ Core</li> <li>• <a href="#">QN9090/30</a>: Bluetooth Low-Energy MCU with Arm®Cortex®-M4 CPU, Energy Efficiency, Analog and Digital Peripherals and NFC Tag Option</li> </ul>
Keypad	<ul style="list-style-type: none"> <li>• <a href="#">General Purpose I/O (GPIO)</a>: General Purpose I/O (GPIO)</li> </ul>

View our complete solution for [Respiratory Care](#).

**Note:** The information on this document is subject to change without notice.



**[www.nxp.com](http://www.nxp.com)**

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2023 NXP B.V.