



S32K3x4-Q257 Full-Featured General Purpose Development Board

S32K3X4EVB-Q257

Last Updated: Jan 19, 2026

This development board is no longer manufactured. NXP will maintain support for this product but recommends the [S32K3X4EVB-T172](#) Board for optimized performance and support.

The S32K3X4EVB-Q257 is a full-featured evaluation and development board for general purpose industrial and automotive applications.


Based on the 32-bit Arm® Cortex®-M7 S32K3 MCU in a 257 MPABGA package, the full-featured S32K3X4EVB-Q257 offers dual cores configured in lockstep mode, ASIL D safety hardware, HSE security engine, OTA support, advanced connectivity and low power.

The full-featured S32K3X4EVB-Q257 brings a standard-based form factor compatible with the Arduino® UNO pin layout, providing a broad range of expansion board options for quick application prototyping and demonstration.

Offering the S32K3 EVB in two configurations:

- S32K3X4EVB-Q257: all components populated
- S32K3X4EVBQ257ND: Kinetis K26 MCU not populated, require using an external debugger like IAR's I-jet, PEmicro's Multilink and CYCLONE FX or CYCLONE LC, Lauterbach's PowerDebug USB 3 and PowerDebug PRO, SEGGER J-Link, iSYSTEM's BlueBoxes iC5000/iC5700, Keil's ULINK, or Green Hills Probe.

S32K3X4EVB-Q257 Block Diagram



S32K3 Family Features Block Diagram

K311	K312	K314	Common Features	K322	K324	K341	K342	K344	K328	K338	K348	K358
1 x Arm® Cortex®-M7 @120 MHz	1x Cortex-M7 @240 MHz	AEC-Q100, 125 °C, 3.3/5 V	2 x Cortex-M7 @240 MHz	1 Lockstep Cortex-M7 @ 240 MHz					2 x Cortex-M7 @ 240 MHz	3 x Cortex-M7 @ 240 MHz	1 LS Cortex-M7 @ 240 MHz	1 LS Cortex-M7 + 1 Cortex-M7 @ 240 MHz
1 MB Flash	2 MB Flash	4 MB Flash	HSE-B Crypto Security Engine	2 MB Flash	4 MB Flash	1 MB Flash	2 MB Flash	4 MB Flash	8 MB Flash			
128 K SRAM	192 K SRAM	512 K SRAM	FOTA (Firmware Over-the-Air)	256 k SRAM	512 k SRAM	256 k SRAM	256 k SRAM	512 k SRAM	1152 KB SRAM	1152 KB SRAM	1152 KB SRAM	1152 KB SRAM
up to 84 I/Os	up to 143 I/Os	up to 218 I/Os	up to 143 I/Os	up to 218 I/Os	up to 143 I/Os	up to 218 I/Os	up to 143 I/Os	up to 218 I/Os	up to 218 I/Os			
16-ch. eDMA	32-ch. eDMA	100 Mbit/s Ethernet (TSN)	Low-Power Operating Modes and Peripherals (LP UART, FlexIO)	32-ch. eDMA					32-ch. eDMA			
3 x CAN (3 x FD)	6 x CAN (6 x FD)	4 x CAN (4 x FD)	4 x CAN (4 x FD)	6 x CAN (6 x FD)	4 x CAN (4 x FD)	4 x CAN (4 x FD)	6 x CAN (6 x FD)	8 x CAN (8 x FD)	8 x CAN (8 x FD)	8 x CAN (8 x FD)	8 x CAN (8 x FD)	
2 x I²C	2 x I²C	2 x I²C	ASIL B/D Safety: (ECC Memories, MPU, CRC, Watchdog)	100 Mbit/s Ethernet (TSN)					1 Gbit/s Ethernet (TSN)			
4 x SPI*	6 x SPI*	4 x SPI*	eMOS Timers, Analogue Comparator, Logic Control Unit, Body Cross Triggering Unit, Trigger Mux	2 x I²C	2 x I²C	2 x I²C	2 x I²C	2 x I²C	2 x I²C			
2 x 24-ch, 12-bit ADC	3 x 24-ch, 12-bit ADC	2 x 24-ch, 12-bit ADC	4 x SPI*	6 x SPI*	4 x SPI*	4 x SPI*	6 x SPI*	6 x SPI*				
2 x SAI (I²S)	Quad SPI	2 x SAI (I²S)	2 x 24-ch, 12-bit ADC	3 x 24-ch, 12-bit ADC	2 x 24-ch, 12-bit ADC	2 x 24-ch, 12-bit ADC	3 x 24-ch, 12-bit ADC	3 x 24-ch, 12-bit ADC				
LOFP-48	HDQFP-172	HDQFP-100	Quad SPI IDE	2 x SAI (I²S)					2 x SAI (I²S)			
HDQFP-100	MAPBGA-257	MAPBGA-257	Real Time Drivers (AUTOSAR® and Non-AUTOSAR)	HDQFP-172					HDQFP-172			
			Security F/W Safety Software Framework Application Software	HDQFP-100	HDQFP-100	HDQFP-100	MAPBGA-257	MAPBGA-257	MAPBGA-289			

View additional information for [S32K3x4-Q257 Full-Featured General Purpose Development Board](#).

Note: The information on this document is subject to change without notice.