



9-Channel PMIC for High-Performance Applications, Fit for up to SIL-2

PF9455

Preproduction

This page contains information on a preproduction product. Specifications and information herein are subject to change without notice. For additional information [contact support](#) or your sales representative.

Last Updated: Jan 31, 2025

The PF9455 power management integrated circuit (PMIC) is optimized for high-performance [i.MX94](#) based applications. It features five high-efficiency buck converters and four linear regulators for powering the processor, memory and miscellaneous peripherals. PF9455 provides low quiescent current in standby and low-power off modes.

The PF9455 is developed in compliance with industrial IEC 61508 safety standards, including safety features, with failsafe outputs and integrated self-test mechanisms, becoming part of a safety oriented system partitioning targeting high integrity safety levels up to industrial SIL-2.

PF9455 Multi-Channel PMIC for i.MX 94 Block Diagram



View additional information for [9-Channel PMIC for High-Performance Applications, Fit for up to SIL-2](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2025 NXP B.V.