

AN13203

Application and Soldering Information for PCF2131 and PCA2131 RTCs

Rev. 1.1 — 7 November 2025

Application note



Document information

| Information | Content |
|-------------|--|
| Keywords | AN13203, PCA2131, PCF2131, application, soldering |
| Abstract | This application note gives additional information about application and soldering of the PCA2131 and PCF2131 Real-Time Clocks (RTCs). |



1 Introduction

This application note provides application and soldering information on the PCF2131 and PCA2131 Real-Time Clocks (RTCs).

2 Reflow soldering

This section provides soldering details for the PCF2131 and PCA2131 RTC devices.

2.1 Introduction to reflow soldering

Soldering is one of the most common methods through which packages are attached to Printed-Circuit Boards (PCBs) to form electrical circuits. The soldered joint provides the mechanical and the electrical connection. There is no single soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and Surface Mount Devices (SMDs) are mixed on one PCB. However, it is not suitable for fine pitch SMDs. Reflow soldering is ideal for the small pitches and high densities that come with increased miniaturization.

The PCF2131 and PCA2131 are intended for use in a reflow soldering process.

The reflow soldering process involves applying solder paste to a board, followed by component placement and exposure to a temperature profile. Leaded packages, packages with solder balls, and leadless packages are all reflow solderable.

Key characteristics in reflow soldering are:

- Board specifications, including the board finish, solder masks, and vias.
- Package footprints, including solder thieves and orientation.
- The moisture sensitivity level of the packages.
- Package placement
- Inspection and repair
- Lead-free versus SnPb soldering; note that a lead-free reflow process usually leads to higher minimum peak temperatures than a SnPb process, therefore reducing the process window.
- Solder pastes printing issues including smearing, release, and adjusting the process window for a mix of large and small components on one board.
- Reflow temperature profile (see [Figure 1](#); this profile includes preheat (T_s), reflow (in which the board is heated to the peak temperature (T_p)) and cooling down. It is imperative that the peak temperature is high enough for the solder to make reliable solder joints (a solder paste characteristic). In addition, the peak temperature must be low enough that the packages and/or boards are not damaged.

For further information on reflow soldering IC, refer to [ref.\[1\]](#).

2.2 Reflow soldering of PCF2131 and PCA2131

The PCF2131 and PCA2131 is intended for use in a lead-free reflow soldering process, classified in accordance with [ref.\[3\]](#).

[Figure 1](#) shows the reflow soldering temperature profile according to [ref.\[3\]](#), used for the qualification of the PCF2131 and PCA2131.




Figure 1. Reflow temperature profile

The reflow profile in this document is for classification/preconditioning and not meant to specify board assembly profiles. Actual board assembly profiles should be developed based on specific process needs and board designs, but must not exceed the parameters shown in Table 1. All temperatures refer to the center of the package, measured on the package body surface that is facing up during the reflow soldering process.

Table 1. Values of reflow temperature profile

| Symbol | Value | Unit |
|--------------|-----------|------|
| T_p | 260 | °C |
| T_L | 217 | °C |
| T_C | 255 | °C |
| $T_{s(max)}$ | 200 | °C |
| $T_{s(min)}$ | 150 | °C |
| t_p | 30 | s |
| t_L | 60 to 150 | s |
| t_s | 60 to 120 | s |
| t_{dur} | max 480 | s |

Recommendations:

1. The reflow soldering profile shown in Figure 1 is recommended. A full convection reflow system, capable of maintaining the reflow profile of Figure 1, is recommended.
2. The peak temperature (T_p) of the reflow soldering process must not exceed 260 °C. If the temperature exceeds 260 °C, the characteristics of the crystal oscillator are degraded or the device can even be damaged.
3. The time, while the PCF2131 and PCA2131 is heated above $T_C = 255$ °C, must not exceed 30 s (t_p), otherwise the characteristics of the crystal oscillator is degraded or the device can even be damaged.

2.3 Effect of reflow soldering on the frequency characteristics

The reflow soldering process typically generates a negative frequency shift.

After one-time reflow soldering, processed in accordance with the recommended temperature profile shown in [Figure 1](#) and [Table 1](#), a frequency shift of -2 ppm is typical. Any other reflow temperature profile or multiple soldering can cause a different frequency shift after soldering. The frequency shift after soldering can be reduced by lowering the peak temperature T_p and shortening the time t_p of the soldering process (see [Figure 1](#) and [Table 1](#)).

2.4 Frequency correction after reflow soldering

Depending on the actual soldering profile used, a frequency offset of some ppm can vary from case to case. To compensate for this shift in frequency due to reflow soldering, a frequency offset can be programmed through bits AO[3:0] of register address 0x30h.

A frequency measurement (see section 7.3.1 of [ref.\[2\]](#)) must be performed after the final assembly of the board if:

- the soldering was processed multiple times, or
- the soldering was not made according to the recommended temperature profile, or
- the best result in accuracy should be achieved.

Then the offset with the appropriate value given in [Table 2](#) must be programmed into AO[3:0]. Deviations caused by assembly steps or due to production tolerances can be compensated with it.

Table 2. Typical frequency correction at 25 °C

| AO[3:0] | | |
|---------|--------|-----|
| Decimal | Binary | ppm |
| 0 | 0000 | +16 |
| 1 | 0001 | +14 |
| 2 | 0010 | +12 |
| 3 | 0011 | +10 |
| 4 | 0100 | +8 |
| 5 | 0101 | +6 |
| 6 | 0110 | +4 |
| 7 | 0111 | +2 |
| 8 | 1000 | 0 |
| 9 | 1001 | -2 |
| 10 | 1010 | -4 |
| 11 | 1011 | -6 |
| 12 | 1100 | -8 |
| 13 | 1101 | -10 |
| 14 | 1110 | -12 |
| 15 | 1111 | -14 |

3 Application information

This section provides soldering details for the PCF2131 and PCA2131 RTC devices.

3.1 Assembly recommendations

- Take precautions when using the PCA2131 and PCF2131 with general-purpose mounting equipment to avoid excessive shocks that could damage the integrated quartz crystal.
- Avoid ultrasonic cleaning that could damage the integrated quartz crystal.

3.2 General application information

- The IFS pin must be connected to ground (VSS) to select the SPI-bus.
- The IFS pin must be connected to the VDD pin to select the Inter-Integrated Circuit (I²C) bus.
- The center thermal pad must be left floating.
- Avoid in the board layout running signal traces under the package unless a ground plane is placed between the package and the signal line.
- A backup battery can be attached to the VBAT pin to enable the battery switch-over when the main power VDD fails. If VBAT is not used, it has to be connected to the ground. If VBAT is used, one of the supplies (VBAT or VDD) has to be turned on before the other.
- The battery-backed voltage VBBS can be used to supply an external RAM to retain RAM data in battery backup mode. A low leakage decoupling capacitor should be connected from BBS to VSS: suggested value is 1 nF, max 100 nF. If BBS is not used to supply an external IC, the decoupling capacitor between the BBS and VSS pins must always be connected.
- INTA and INTB are open-drain, active LOW outputs, which require external pullup resistors: The maximum pullup voltage should be limited to the same voltage as VDD.

3.3 Battery switch-over applications

The functionality of the battery switch-over is limited by the fact that the power supply V_{DD} is monitored in every 1 ms to save power consumption. Considering that the battery switch-over threshold value ($V_{th(sw)bat}$) is typically 2.5 V, the power management operating limit ($V_{DD(min)}$) is 1.8 V, and that V_{DD} is monitored in every 1 ms, the battery switch-over works properly in all cases where V_{DD} falls with a rate lower than 0.7 V/ms, as shown in [Figure 2](#).




Figure 2. Supply voltage with respect to sampling and comparing rate

In an application where during power-down the current consumption on pin VDD is:

- in the range of a few μA a capacitor of 100 nF on pin VDD is enough to allow a slow power-down and the proper functionality of the battery switch-over;
- in the range of a few hundreds of μA , the value of the capacitor on pin VDD must be increased to force a falling gradient of less than 0.7 V/ms on pin VDD to assure the proper functionality of the battery switch-over;
- higher than some mA it is recommended to add an RC network on the VDD pin, as shown in [Figure 3](#).

A series resistor of 330 Ω and a capacitor of 47 μF assure the proper functionality of the battery switch-over even with fast VDD slope.

Note that:

- It is not suggested to assemble a series resistor higher than 1 k Ω because it would cause a large voltage drop at the VDD pin.
- Lower values of capacitors are possible, depending on the VDD slope at the power supply source in the application.




Figure 3. RC network on pin VDD

4 References

This section lists the references used to supplement this document.

- [1] NXP Semiconductors, *Surface mount reflow soldering description*, AN10365
- [2] NXP Semiconductors, *Highly accurate nano-power RTC with integrated quartz crystal*, PCF2131 datasheet, May 2021
- [3] IPC/JEDEC J-STD-020, *Moisture/Reflow Sensitivity Classification for Non-hermetic Solid State Surface Mount Devices*

5 Revision history

This section summarizes revisions to this document.

Table 3. Revision history

| Document ID | Release date | Description |
|---------------|------------------|--|
| AN13203 v.1.1 | 07 November 2025 | Updated as per CIN# 202411003I: <ul style="list-style-type: none">• Updated the Section 3.2: changed from “center pad must be connected to ground (VSS)” to “central pad must be left floating”.• Minor editorial changes |
| AN13203 v.1.0 | 26 May 2021 | <ul style="list-style-type: none">• Initial version |

Legal information

Definitions

Draft — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.nxp.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Suitability for use in non-automotive qualified products — Unless this document expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Evaluation products — This evaluation product is intended solely for technically qualified professionals, specifically for use in research and development environments to facilitate evaluation purposes. It is not a finished product, nor is it intended to be a part of a finished product. Any software or software tools provided with an evaluation product are subject to the applicable license terms that accompany such software or software tools. This evaluation product is provided on an "as is" and "with all faults" basis for evaluation purposes only and is not to be used for product qualification or production. If you choose to use these evaluation products, you do so at your risk and hereby agree to release, defend and indemnify NXP (and all of its affiliates) for any claims or damages resulting from your use. NXP, its affiliates and their suppliers expressly disclaim all warranties, whether express, implied or statutory, including but not limited to the implied warranties of non-infringement, merchantability and fitness for a particular purpose. The entire risk as to the quality, or arising out of the use or performance, of this evaluation product remains with user.

In no event shall NXP, its affiliates or their suppliers be liable to user for any special, indirect, consequential, punitive or incidental damages (including without limitation damages for loss of business, business interruption, loss of use, loss of data or information, and the like) arising out of the use or inability to use the evaluation product, whether or not based on tort (including negligence), strict liability, breach of contract, breach of warranty or any other theory, even if advised of the possibility of such damages.

Notwithstanding any damages that user might incur for any reason whatsoever (including without limitation, all damages referenced above and all direct or general damages), the entire liability of NXP, its affiliates and their suppliers and user's exclusive remedy for all of the foregoing shall be limited to actual damages incurred by user based on reasonable reliance up to the greater of the amount actually paid by user for the evaluation product or five dollars (US\$5.00). The foregoing limitations, exclusions and disclaimers shall apply to the maximum extent permitted by applicable law, even if any remedy fails of its essential purpose and shall not apply in case of willful misconduct.

HTML publications — An HTML version, if available, of this document is provided as a courtesy. Definitive information is contained in the applicable document in PDF format. If there is a discrepancy between the HTML document and the PDF document, the PDF document has priority.

Translations — A non-English (translated) version of a document, including the legal information in that document, is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — Customer understands that all NXP products may be subject to unidentified vulnerabilities or may support established security standards or specifications with known limitations. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP.

NXP has a Product Security Incident Response Team (PSIRT) (reachable at PSIRT@nxp.com) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

NXP B.V. — NXP B.V. is not an operating company and it does not distribute or sell products.

Trademarks

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

I2C-bus — logo is a trademark of NXP B.V.

Tables

| | | | | | |
|---------|---|---|---------|------------------------|---|
| Tab. 1. | Values of reflow temperature profile | 3 | Tab. 3. | Revision history | 7 |
| Tab. 2. | Typical frequency correction at 25 °C | 4 | | | |

Figures

| | | | | | |
|---------|---|---|---------|-----------------------------|---|
| Fig. 1. | Reflow temperature profile | 3 | Fig. 3. | RC network on pin VDD | 6 |
| Fig. 2. | Supply voltage with respect to sampling and comparing rate | 5 | | | |

Contents

| | | |
|----------|--|----------|
| 1 | Introduction | 2 |
| 2 | Reflow soldering | 2 |
| 2.1 | Introduction to reflow soldering | 2 |
| 2.2 | Reflow soldering of PCF2131 and PCA2131 | 2 |
| 2.3 | Effect of reflow soldering on the frequency characteristics | 4 |
| 2.4 | Frequency correction after reflow soldering | 4 |
| 3 | Application information | 5 |
| 3.1 | Assembly recommendations | 5 |
| 3.2 | General application information | 5 |
| 3.3 | Battery switch-over applications | 5 |
| 4 | References | 7 |
| 5 | Revision history | 7 |
| | Legal information | 8 |

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.
