

i.MX 6Quad/6Dual Personality Fuses

1 Introduction

This document describes on-chip fuses (called personality fuses) that are used to define the characteristics of the i.MX 6Quad and 6Dual SoCs.

Contents

1. Introduction	1
2. i.MX 6Quad/6Dual Personality Fuses	2
3. Revision History	2

2 i.MX 6Quad/6Dual Personality Fuses

Table 1 shows the fuses related to the definition of the SoC.

Table 1. Personality Fuses

Fuse Function	Fuse Address	OCOTP Address	Fuse Name	Settings			
Quad/ Dual	0x430[21:20]	0x021B_C430[21:20]	NUM_CORES[1:0]	00 – 4x Cores	01 – Reserved	10 – 2x Cores	11 – Reserved
				MCIMX6Qxxxxxxx		MCIMX6Dxxxxxxx	
MLB	0x430[26]	0x021B_C430[26]	MLB_DISABLE	0 – Enabled		1 – Disabled	
				MCIMX6x4xxxxxx MCIMX6x5xxxxxx MCIMX6x6xxxxxx		MCIMX6x7xxxxxx	
VPU	0x440[15]	0x021B_C440[15]	VPU_DISABLE	0 – Enabled		1 – Disabled	
				MCIMX6x5xxxxxx MCIMX6x6xxxxxx MCIMX6x7xxxxxx		MCIMX6x4xxxxxx	
Market Segment	0x480[7:6]	0x021B_C480[7:6]	Market_Segment[1:0]	00 – Reserved	01 – Extended commercial -20C to 105C	10 – Industrial -40C to 105C	11 – Automotive -40C to 125C
					MCIMX6xxExxxxx	MCIMX6xxCxxxx	MCIMX6xxAxxxx
Speed	0x440[17:16]	0x021B_C440[17:16]	SPEED_GRADING[5:4]	00 – 800 MHz (Industrial grade)	01 – 852 MHz (Automotive grade)	10 – 1000 MHz	11 – 1200 MHz
				MCIMX6xxxx00x	MCIMX6xxxx01x	MCIMX6xxxx10x	MCIMX6xxxx11x
HDCP	0x460[16]	0x021B_C460[16]	HDCP_ENCRYPTION_DISABLE	0 – Encryption enabled		1 – Encryption disabled	
				MCIMX6xxxxxxCx		MCIMX6xxxxxxAx	

3 Revision History

Revision 0 is the initial release of this document.

How to Reach Us:

Home Page:

nxp.com

Web Support:

nxp.com/support

Information in this document is provided solely to enable system and software implementers to use NXP products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document. NXP reserves the right to make changes without further notice to any products herein.

NXP makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in NXP data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals" must be validated for each customer application by customer, and technical experts. NXP does not convey any license under its patent rights nor the rights of others. NXP sells products pursuant to standard terms and conditions of sale, which can be found at the following address:

nxp.com/SalesTermsandConditions.

NXP, the NXP logo, NXP SECURE CONNECTIONS FOR A SMARTER WORLD, Freescale and the Freescale logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. ARM, the ARM Powered logo and Cortex are registered trademarks of ARM Limited (or its subsidiaries) in the EU and/or elsewhere.

© 2016 NXP B.V.

Document Number: AN5323

Rev. 0

08/2016

