

i.MX31 PDK 1.4 Power Measurements

Application Note

This document describes the current measurement capabilities of the 3-Stack board and explains how to obtain these measurements from the Debug board.

Contents

1	Overview.....	2
1.1	Maxim MAX4071 Modules	2
1.2	Debug Board Connector for Measurements	3
2	Measuring the Current	5

1 Overview

The 3-Stack board provides the functionality for measuring voltage and current. Checking these measurements enables you to determine the overall product efficiency.

1.1 Maxim MAX4071 Modules

The CPU and Personality boards contain seven Maxim MAX4071 modules, which reduce power supply noise and improve the accuracy of the readings. Figure 1 illustrates the MAX4031 module layout.




Figure 1 MAX4071 Connection Diagram

The power measurement system provides a way to easily test the system, using four output voltages and seven amplified currents. Table 1 describes the voltage and current outputs.

Table 1 Voltage and Current Outputs

Identifier	Category	Description
Voltage	NA	VMAIN
Voltage	NA	5V from Wall power supply
Voltage	NA	Battery Voltage
Voltage	NA	1.8V peripheral voltage
Current	CPU	Atlas SW1: MX31 ARM Core and L2
Current	CPU	Atlas SW2: 1.8V combined to MX31, mDDR and NAND

Identifier	Category	Description
Current	CPU	VMAIN: Combined Battery and/or Wall Supply
Current	Personality	1.8V combined to peripherals
Current	Personality	Lithium Prismatic Battery
Current	Personality	5V Wall Power Supply (power jack on Personality board)
Current	Personality	3.3V to Hard Drive

1.2 Debug Board Connector for Measurements

Figure 2 identifies the connector on the Debug board that is used to obtain measurements. Figure 3 provides an enlarged view of the connector.




Figure 2 Current Measurement Connector

Figure 3 provides a detailed view of the connector, and the table that follows describes the pin-out.




Figure 3 Current Measurement Connector Detail

Pin Number	Description
1	Ground
2	SW1 Core and L2 current (1V2_1V6_SW1)
3	VMAIN voltage
4	1.8V Memories (1V8_SW2A)
5	Ground
6	VMAIN current
7	LI_BATTERY voltage
8	Reserved
9	Ground
10	Reserved
11	1.8V voltage
12	1.8V peripherals (EXT_1V8)
13	Ground
14	3.3V to HDD (HDD_3V3)
15	WALL_5V_IN
16	Wall Supply 5V (WALL_5V_IN)
17	Ground
18	Lithium Battery (LI_BATTERY)
19	Ground
20	Reserved

2 Measuring the Current

To measure the current, use these steps:

1. Measure the voltage value using a multimeter on the desired pin (current pin ex. PIN6 VMAIN current).

The value reflected in the pin is the voltage reading from the MAX4071 chip.

2. To obtain the current value, subtract 1.5 from the voltage measured.
3. Multiple the results by 500.
4. The current value is expressed in mA.

Formula

The formula for obtaining the current consumption from the MAX4071 readings is:

$$I = (V - 1.5) \times 500$$

Where: V is the reading from the connector pin.

Example

The following table provides an example of the current consumption values for a given voltage on the pin.

Voltage	Current (mA)
3.5 V	1000 mA
2.5 V	500 mA
1.5 V	0 mA
0.5 V	- 500 mA

How to Reach Us:**Home Page:**

www.freescale.com

Web Support:

<http://www.freescale.com/support>

USA/Europe or Locations Not Listed:

Freescale Semiconductor
Technical Information Center, EL516
2100 East Elliot Road
Tempe, Arizona 85284
+1-800-521-6274 or +1-480-768-2130
www.freescale.com/support

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH
Technical Information Center
Schatzbogen 7
81829 Muenchen, Germany
+44 1296 380 456 (English)
+46 8 52200080 (English)
+49 89 92103 559 (German)
+33 1 69 35 48 48 (French)
www.freescale.com/support

Japan:

Freescale Semiconductor Japan Ltd.
Headquarters
ARCO Tower 15F
1-8-1, Shimo-Meguro, Meguro-ku,
Tokyo 153-0064, Japan
0120 191014 or +81 3 5437 9125
support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor China Ltd.
Exchange Building 23F
No. 118 Jianguo Road
Chaoyang District
Beijing 100022
China
+86 010 5879 8000
support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor Literature Distribution
Center
P.O. Box 5405
Denver, Colorado 80217
1-800-441-2447 or 303-675-2140
Fax: 303-675-2150
LDCForFreescaleSemiconductor@hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale and the Freescale logo are trademarks or registered trademarks of Freescale Semiconductor, Inc. in the U.S. and other countries. All other product or service names are the property of their respective owners. Microsoft and Windows are registered trademarks of Microsoft Corporation.

© Freescale Semiconductor, Inc. 2007- 2008. All rights reserved.