A5G07H800W19N Airfast RF Power GaN Transistor

Rev. 1 — 21 December 2023

This 112 W asymmetrical Doherty RF power GaN transistor is designed for cellular base station applications requiring very wide instantaneous bandwidth capability covering the frequency range of 717 to 850 MHz.

This part is characterized and performance is guaranteed for applications operating in the 717 to 850 MHz band. There is no guarantee of performance when this part is used in applications designed outside of these frequencies.

800 MHz

• Typical Doherty Single–Carrier W–CDMA Reference Circuit Performance: $V_{DD} = 48$ Vdc, $I_{DQA} = 300$ mA, $V_{GSB} = -5.0$ Vdc, $P_{out} = 112$ W Avg., Input Signal PAR = 9.9 dB @ 0.01% Probability on CCDF.⁽¹⁾

Frequency	G _{ps} (dB)	η _D (%)	Output PAR (dB)	ACPR (dBc)
758 MHz	19.7	61.2	8.9	-26.5
803 MHz	19.3	60.0	9.1	-29.3
821 MHz	18.8	59.8	9.0	-30.0

1. All data measured with device soldered to NXP reference circuit.

Features

- · High terminal impedances for optimal broadband performance
- Advanced high performance in-package Doherty
- Improved linearized error vector magnitude with next generation signal
- Able to withstand extremely high output VSWR and broadband operating conditions
- Plastic package

Product data sheet

A5G07H800W19N

717–850 MHz, 112 W Avg., 50 V AIRFAST RF POWER GaN TRANSISTOR






Figure 1. Pin Connections



Table 1. Maximum Ratings					
Rating		Symbol	Va	lue	Unit
Drain-Source Voltage		V _{DSS}	1:	25	Vdc
Gate-Source Voltage	V _{GS}	-10	6, 0	Vdc	
Operating Voltage		V _{DD}	5	5	Vdc
Maximum Forward Gate Current, $I_{G (A+B)}$, @ $T_{C} = 25^{\circ}C$		I _{GMAX}	g	0	mA
Storage Temperature Range		T _{stg}	-65 to	o +150	°C
Case Operating Temperature Range		T _C	-55 to	o +150	°C
Maximum Channel Temperature		Т _{СН}	22	25	°C
Table 2. Recommended Operating Conditions					
Characteristic		Symbol	Va	lue	Unit
Operating Voltage		V _{DD}	5	0	Vdc
Table 3. Thermal Characteristics					
Characteristic		Symbol	Va	lue	Unit
Thermal Resistance by Infrared Measurement, Active Die Surface-to-Case Case Temperature 88°C, P _D = 95 W			0.43 (1)		°C/W
Thermal Resistance by Finite Element Analysis, Channel-to-Case Case Temperature 88°C, P _D = 94.7 W	R _{θCHC} (FEA)	0.6 (2)		°C/W	
Table 4. ESD Protection Characteristics					
Test Methodology			Cla	ass	
Human Body Model (per JS-001-2017)		1A			
Charge Device Model (per JS-002-2014)		C3			
Table 5. Moisture Sensitivity Level					
Test Methodology	Rating	Package	e Peak Temp	perature	Unit
Per JESD22-A113, IPC/JEDEC J-STD-020	3		245		°C
Table 6. Electrical Characteristics ($T_A = 25^{\circ}C$ unless otherwise noted)					
Characteristic	Symbol	Min	Тур	Max	Unit
Dff Characteristics ⁽³⁾					
	I _{D(BR)}		_	15.4 26.4	mAdc
Dn Characteristics — Side A, Carrier				I	•
Gate Threshold Voltage (V _{DS} = 10 Vdc, I _D = 35 mAdc)	V _{GS(th)}	-4.6	-2.6	-1.9	Vdc
Gate Quiescent Voltage $(V_{DD} = 50 \text{ Vdc}, I_D = 350 \text{ mAdc}, \text{Measured in Functional Test})$	V _{GSA(Q)}	-3.1	-2.6	-2.1	Vdc
				•	•

On Characteristics — Side B, Peaking					
Gate Threshold Voltage (V _{DS} = 10 Vdc, I _D = 60 mAdc)	V _{GS(th)}	-4.6	-2.6	-1.9	Vdc

1. Refer to AN1955, Thermal Measurement Methodology of RF Power Amplifiers. Go to http://www.nxp.com/RF and search for AN1955. 2. R_{0CHC} (FEA) must be used for purposes related to reliability and limitations on maximum channel temperature. MTTF may be estimated

by the expression MTTF (hours) = $10^{[A + B/(T + 273)]}$, where T is the channel temperature in degrees Celsius, A = -11.6 and B = 9129. 3. Each side of device measured separately.

(continued)

Table 6. Electrical Characteristics (T_A = 25°C unless otherwise noted) (continued)

Characteristic	Symbol	Min	Typ	Max	Unit
Cital acteristic	Symbol	IVIIII	IVP	Max	Onit

Functional Tests (In NXP Doherty Production Test Fixture, 50 ohm system) ⁽¹⁾ $V_{DD} = 50$ Vdc, $I_{DQA} = 350$ mA, $V_{GSB} = (V_t - 2.4)$ Vdc, $P_{out} = 158$ W Avg., f = 758 MHz, Single–Carrier W–CDMA, IQ Magnitude Clipping, Input Signal PAR = 9.9 dB @ 0.01% Probability on CCDF. ACPR measured in 3.84 MHz Channel Bandwidth @ ± 5 MHz Offset.

Power Gain	G _{ps}	17.4	18.3	19.7	dB
Drain Efficiency	η_D	57.0	60.8	_	%
Saturated Power (Pulsed CW, 5% Duty Cycle)	P _{sat}	58.0	59.9	_	dBm
Adjacent Channel Power Ratio	ACPR	_	-32.8	-29.0	dBc

Wideband Ruggedness (In NXP Doherty Production Test Fixture, 50 ohm system) I_{DQA} = 350 mA, V_{GSB} = -5.0 Vdc, f = 790 MHz, Additive White Gaussian Noise (AWGN) with 10 dB PAR

ISBW of 400 MHz at 55 Vdc, 174 W Avg. Modulated Output Power (3 dB Input Overdrive from 100 W Avg. Modulated Output Power) No Device Degradation

Typical Performance (In NXP Doherty Production Test Fixture, 50 ohm system) $V_{DD} = 50$ Vdc, $I_{DQA} = 350$ mA, $V_{GSB} = -4.8$ Vdc, 758–821 MHz Bandwidth

Pulsed CW, 10% Duty Cycle					
Saturated Power ⁽²⁾	P _{sat}	—	955	—	W
AM/PM ⁽²⁾ (Maximum value measured at saturated power across the 758–821 MHz bandwidth)	Φ		-30		0
Gain Variation @ Avg. Power over Temperature (-40°C to +85°C)	ΔG		0.005		dB/°C
Output Power Variation @ Saturated Power over Temperature (-40°C to +85°C)	ΔP_{sat}		0.001		dB/°C
Single–Carrier W–CDMA, Unclipped					
Gain Flatness in 63 MHz Bandwidth @ P _{out} = 112 W Avg. ⁽²⁾	G _F	—	0.9	—	dB
2-Tone CW					
VBW Resonance Point ⁽²⁾ (IMD Third Order Intermodulation Inflection Point)	VBW _{res}	—	70		MHz

Table 7. Ordering Information

Device	Tape and Reel Information	Package
A5G07H800W19NR3	R3 Suffix = 250 Units, 44 mm Tape Width, 13-inch Reel	OM-780-4S4S

1. Internally matched part.

2. All data measured with device soldered to NXP production test fixture.


Correct Biasing Sequence for GaN Depletion Mode Transistors in a Doherty Configuration

Bias ON the device

- 1. Set gate voltage V_{GSA} and V_{GSB} to –5 V.
- 2. Set drain voltage V_{DSA} and V_{DSB} to nominal supply voltage (+50 V).
- 3. Increase V_{GSA} (carrier side) until I_{DQA} current is attained.
- 4. Increase V_{GSB} (peaking side) to target bias voltage.
- 5. Apply RF input power to desired level.

Bias OFF the device

- 1. Disable RF input power.
- 2. Adjust gate voltage V_{GSA} and V_{GSB} to –5 V.
- 3. Adjust drain voltage V_{DSA} and V_{DSB} to 0 V. Allow adequate time for drain voltage to reduce to 0 V from external drain capacitors.
- 4. Disable V_{GSA} and V_{GSB} .



Part	Description	Part Number	Manufacturer	
C1, C2, C7, C8	100 pF Chip Capacitor	600S101JT250XT	ATC	
C3	12 pF Chip Capacitor	GQM1875C2E120FB12D	Murata	
C4	9.1 pF Chip Capacitor	GQM1875C2E9R1BB12D	Murata	
C5	6.8 pF Chip Capacitor	GQM1875C2E6R8BB12D	Murata	
C6	1.2 pF Chip Capacitor	GQM1875C2E1R2BB12D	Murata	
C9	2.2 pF Chip Capacitor	600F2R2BT250XT	ATC	
C10	6.8 pF Chip Capacitor	600F6R8BT250XT	ATC	
C11	12 pF Chip Capacitor	600F120JT250XT	ATC	
C12	15 pF Chip Capacitor	600F150JT250XT	ATC	
C13	9.1 pF Chip Capacitor	600F9R1BT250XT	ATC	
C14	5.1 pF Chip Capacitor	600F5R1BT250XT	ATC	
C15, C16, C17, C18	100 pF Chip Capacitor	600F101JT250XT	ATC	
C19	4.3 pF Chip Capacitor	GQM1875C2E4R3BB12D	Murata	
C21, C22	4.7 μF Chip Capacitor	GQM2195C2E4R7BB12D	Murata	
C23, C24	10 nF Chip Capacitor	GRM21BR72A103KA01B	Murata	
C25, C26, C27, C28	4.7 μF Chip Capacitor	C4532X7S2A475M	TDK	
C29, C30	470 μF, 100 V Electrolytic Capacitor	MCGPR100V477M16X32	Multicomp	
Q1	RF Power GaN Transistor	A5G07H800W19N	NXP	
R1, R2	3.0 Ω, 1/8 W Chip Resistor	CRCW08053R00JNEA	Vishay	
R3, R4	10 Ω, 1/8 W Chip Resistor	CRCW080510R0FKEA	Vishay	
R5	50 Ω , 8 W Termination Chip Resistor	C8A50Z4B	Anaren	
Z1	800–1000 MHz Band, 90°, 2 dB Asymmetric Coupler	CMX09Q02	RN2 Technologies	
РСВ	Rogers, RO4350B, 0.020″, ε _r = 3.66	D174971	MTL	

Table 8. A5G07H800W19N Reference Circuit Component Designations and Values

Note: Component number C20 is intentionally omitted.





Figure 3. Product Marking

Table 9. Product Marking Trace Code

Identifier	Description
A	Assembly location
WL	Wafer lot indicator
YYWW	Date code
Z	Assembly lot

Package Information





)M-780	–4S4S					SOT2082-
NOTE 1. C	S: ONTROLLING DIMENS	ION: INCH				
2. I	NTERPRET DIMENSIO	NS AND TOLERANCES	PER	ASME Y14.5M	-1994.	
	ATUM PLANE H IS L HERE THE LEAD EXI					
I	IMENSIONS DD AND S .006 INCH (0.15 IISMATCH AND ARE D	MM) PER SIDE. DI	MENS	IONS DD AND		
<u>́</u> Р	DIMENSION 66 DOES PROTRUSION SHALL B T MAXIMUM MATERIA	E .005 INCH (0.13				E DAMBAR F THE bb DIMENSION
6. D	ATUMS A AND B TO	BE DETERMINED AT [DATUM	PLANE H.		
	ND 7. A2 APPLIES			J ONLY. A1	APPLIE	ES TO PINS 2, 3, 6
A	ATCHING REPRESENT ND E2 REPRESENT T F EXPOSED AREA OF	HE VALUES BETWEEN				E DIMENSIONS D1 TS ALONG THE EDGES
<u>)</u> D	IMPLED HOLE REPRE	SENTS INPUT SIDE.				
	ONE K REPRESENTS N PERMITTED ON BOTH SI		ни ис	ERE MOLD FL	ASH AND	RESIN BLEED ARE
	INCH	MILLIMETER		INCH		MILLIMETER
DIM	MIN MAX	MIN MAX	DIM	MIN	MAX	MIN MAX

DIM	MIN	MAX	MIN	MAX	DIM	MIN	MAX	MIN	МАХ		
AA	.148	.152	3.76	3.86	W2	.321	.331	8.15	8.41		
A1	.059	.065	1.50	1.65	W3	.281	.291	7.14	7.39		
A2	.056	.068	1.42	1.73	W4	.538	.554	13.67	14.07		
DD	.808	.812	20.52	20.62	U	.037	.043	0.94	1.09		
D1	.720		18.29	18.29 Y		.956 BSC		24.28	BSC		
Е	.610	.618	15.49	15.70	bb	.147	.153	3.73	3.89		
E1	.390	.394	9.91	10.01	c1	.007	.011	0.18	0.28		
E2	.306		7.77		e .317 BSC 8.05		8.05	BSC			
E3	.383	.387	9.73	9.83	e1	.116	.124	2.95	3.15		
F	.025	BSC	0.64	D.64 BSC aaa		0.64 BSC		.004		0.	10
G	.030	BSC	0.76	BSC	bbb	.006		0.	15		
W1	.195	.205	4.95	5.21	ccc	.0	10	0.:	25		

S NXP B.V.	DATE: 2	9 JUL 2020		
MECHANICAL OUTLINE	STANDARD:	DRAWING NUMBER:	REVISION:	PAGE:
PRINT VERSION NOT TO SCALE	NON JEDEC	98ASA01641D	0	3

Product Documentation, Software and Tools

Refer to the following resources to aid your design process.

Application Notes

- AN1907: Solder Reflow Attach Method for High Power RF Devices in Plastic Packages
- AN1955: Thermal Measurement Methodology of RF Power Amplifiers

Software

.s2p File

Development Tools

• Printed Circuit Boards

Revision History

The following table summarizes revisions to this document.

Revision	Date	Description	
0	12 April 2023	Initial release of data sheet	
1	21 December 2023	 Table 5, Moisture Sensitivity Level: package peak temperature updated to reflect actual test data, p. 2 Table 6, DC On Characteristics, V_{GSA(Q)}: updated Min value to match production test value, p. 2 Table 6, Functional Tests: updated output power test condition, p. 3 Table 6, Typical Performance: added VBW_{res}, p. 3 General updates made to align data sheet to current standard 	

Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

Definitions

Draft — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including – without limitation – lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk. **Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Suitability for use in non-automotive qualified products — Unless this document expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non–English (translated) version of a document, including the legal information in that document, is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — Customer understands that all NXP products may be subject to unidentified vulnerabilities or may support established security standards or specifications with known limitations. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately.

Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP.

NXP has a Product Security Incident Response Team (PSIRT) (reachable at PSIRT@nxp.com) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

 $\ensuremath{\text{NXP B.V.}}$ – NXP B.V. is not an operating company and it does not distribute or sell products.

Trademarks

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

Airfast — is a trademark of NXP B.V.

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© 2023 NXP B.V.

For more information, please visit: http://www.nxp.com

Date of release: 21 December 2023 Document identifier: A5G07H800W19N