



NXP Near Field Communication (NFC) controller PN532 for embedded devices

Easy, secure connectivity

Offering proximity connectivity for 13.56 MHz reader/writer applications in embedded devices, this highly integrated transmission module includes a microcontroller that reduces processing overhead on the host controller.

Key features

- ▶ Reader/writer functionality compatible with ISO/IEC 14443 A&B, MIFARE™, FeliCa and NFC Forum tag types (Jewel, MIFARE Ultralight™, FeliCa, MIFARE DESFire™)
- ▶ Full peer-to-peer functionality (ISO/IEC 18092 NFC IP1)
- ▶ Card emulation functionality
- ▶ Operating distance up to 70 mm*
- ▶ Integrated microcontroller with embedded firmware in ROM
- ▶ Multiple interfaces (UART, SPI, I²C)
- ▶ Integrated MIFARE reader support

Key benefits

- ▶ Fast design-in time
- ▶ Real-time processing of integrated microcontroller
- ▶ Supports the most widely deployed contactless card protocols (ISO 14443 A&B and Felica)
- ▶ Small footprint (HVQFN40 6 x 6 x 1 mm)

- ▶ Application notes to optimize antenna and software design
- ▶ Excellent design-in support available worldwide
- ▶ Easy access to NFC technology, built with NXP's expertise and experience with major device manufacturers

Target markets and applications

- ▶ Embedded devices
- ▶ Industrial and medical applications
- ▶ Gaming and entertainment systems

*Depends on antenna device and device integration



Key technical data

| Product features | |
|--------------------------------|--|
| Host interfaces | SPI up to 5 Mbit/s Serial UART up to 1228 kbit/s I ² C up to 400k bit/s |
| Microcontroller | 80C51 core with 40 kbyte ROM and 1 kbyte RAM |
| RF interface | |
| Analog interface | Fully integrated |
| Carrier frequency | 13.56 MHz |
| Baud rates | up to 424 kbit/s |
| Contactless protocols | |
| Reader / writer | ISO/IEC 14443 A&B MIFARE NFC Forum Tag Type support FeliCa |
| Peer-to-peer | ISO/IEC 18092 (active and passive) |
| Card emulation | ISO 14443 A & Mifare |
| Additional product information | |
| Supply voltage | 2.7 - 5.5 V |
| Power-down mode | 12 µA |
| Typical RF current | 60 mA |
| Temperature range | -25 to +85 °C |
| Package | HVQFN40 (6 x 6 x 1 mm) |
| Software | NFC Forum Reference implementation |

Design-in kit

To support product development and enable easy access to PN532 and NFC technology, NXP offers the OM5581/ N5322S02 design-in kit. Equipped with all the necessary hardware, software sources, and documentation, it includes two reference PN532 boards, two cables, and two power supplies. A reference implementation for the NFC Forum's protocol stack is also available.

To order samples or design kits, please contact a local NXP distributor (www.nxp.com) or access the NXP distributor portal (<https://extranet.nxp.com>).

Ordering information

| Part number | | PN5321A3HN/C106 | |
|----------------------|---------|-----------------|---------------------------------------|
| Sales description | Package | HVQFN40 | |
| | Status | Available | |
| Ordering information | 12NC | 9352 852 23518 | MOQ=4000 (5trays with dry pack) |
| | | 9352 852 23551 | MOQ=490 (Rail with dry pack) |
| | | 9352 852 23557 | MOQ=2450 (simple tray with dry pack) |

MIFARE pedigree

NXP MIFARE is the leading technology platform for contactless ticket, card, and reader solutions. With more than 40 million core reader components, two billion cards, and one billion smart ticket ICs sold, MIFARE is a proven and reliable technology that represents the largest installed base worldwide.

MIFARE, MIFARE Ultralight, MIFARE DESFire, FeliCa, Topaz are registered trademarks of NXP, Sony Corporation and Innovision Research and Technology plc. respectively

MIFARE.net

www.nxp.com

© 2012 NXP Semiconductors N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Date of release: March 2012

Document order number: 9397 750 17218

Printed in the Netherlands