BB182LX

VHF variable capacitance diode
Rev. 01 — 29 January 2009

Product data sheet

Product profile

1.1 General description

The BB182LX is a planar technology variable capacitance diode in a SOD882T ultra small leadless plastic SMD package. The excellent matching performance is achieved by gliding matching and a Direct Matching Assembly (DMA) procedure.

1.2 Features

- High linearity
- Excellent matching to 2 % DMA
- Ultra small leadless SMD package
- $C_{d(28V)}$:2.7 pF; $C_{d(1V)}$ to $C_{d(28V)}$ ratio: 22
- Low series resistance

1.3 Applications

- Voltage Controlled Oscillators (VCO)
- Electronic tuning in VHF television tuners, Band A up to 160 MHz

Pinning information 2.

Table 1. **Pinning**

	3	
Pin	Description	Simplified outline Graphic symbol
1	cathode	[1]
2	anode	1 2
		Transparent sym008 top view

^[1] The marking bar indicates the cathode.

Ordering information 3.

Table 2. **Ordering information**

Type number	Package				
	Name	Description	Version		
BB182LX	-	leadless ultra small plastic package; 2 terminals; body $1.0 \times 0.6 \times 0.4$ mm	SOD882T		



NXP Semiconductors BB182LX

VHF variable capacitance diode

4. Marking

Table 3. Marking codes

Type number	Marking code
BB182LX	L7

5. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{R}	reverse voltage		-	32	V
I _F	forward current		-	20	mA
T _{stg}	storage temperature		-55	+150	°C
Tj	junction temperature		-55	+125	°C

6. Characteristics

Table 5. Characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
I _R	reverse current	see Figure 3				
		V _R = 30 V	-	-	10	nA
		$V_R = 30 \text{ V}; T_j = 85 ^{\circ}\text{C}$	-	-	200	nΑ
r _s	diode series resistance	$f = 100 \text{ MHz}$ at $C_d = 30 \text{ pF}$; see Figure 2	-	1.0	-	Ω
C _d	diode capacitance	f = 1 MHz; see <u>Figure 1</u> and <u>Figure 4</u>				
		$V_R = 1 V$	52	-	62	pF
		V _R = 28 V	2.48	2.7	2.89	pF
$C_{d(1V)}/C_{d(2V)}$	diode capacitance ratio (1 V to 2 V)	f = 1 MHz	-	1.31	-	
C _{d(1V)} /C _{d(28V)}	diode capacitance ratio (1 V to 28 V)	f = 1 MHz	20.6	22	-	
C _{d(25V)} /C _{d(28V)}	diode capacitance ratio (25 V to 28 V)	f = 1 MHz	-	1.05	-	
$\Delta C_d/C_d$	diode capacitance matching	$V_R = 1 \text{ V to } 28 \text{ V; in sequence of } 5 \text{ diodes (gliding)}$	-	-	2	%

NXP Semiconductors

BB182LX

VHF variable capacitance diode




Fig 1. Diode capacitance as a function of reverse voltage; typical values






Fig 3. Reverse current as a function of junction temperature; maximum values



f = 100 MHz; $T_j = 25 \,^{\circ}\text{C}$.

Fig 2. Diode serial resistance as a function of reverse voltage; typical values



 $T_i = 0$ °C to 85 °C.

Fig 4. Temperature coefficient of diode capacitance as a function of reverse voltage; typical values

7. Package outline




Fig 5. Package outline SOD882T

NXP Semiconductors BB182LX

VHF variable capacitance diode

8. Abbreviations

Table 6. Abbreviations

Acronym	Description
SMD	Surface Mounted Device
VHF	Very High Frequency

9. Revision history

Table 7. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
BB182LX_1	20090129	Product data sheet	-	-

NXP Semiconductors

BB182LX

VHF variable capacitance diode

10. Legal information

10.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

10.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

10.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental

damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

10.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

11. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

®NXP B.V. 2009. All rights reserved.

NXP Semiconductors BB182LX

VHF variable capacitance diode

12. Contents

1	Product profile
1.1	General description
1.2	Features
1.3	Applications
2	Pinning information 1
3	Ordering information
4	Marking 2
5	Limiting values
6	Characteristics
7	Package outline 4
8	Abbreviations 5
9	Revision history 5
10	Legal information 6
10.1	Data sheet status 6
10.2	Definitions
10.3	Disclaimers 6
10.4	Trademarks6
11	Contact information 6
12	Contents 7

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.





© NXP B.V. 2009.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 29 January 2009 Document identifier: BB182LX_1