

# **2.8 GHz Prescaler**

The MC12089 is a single modulus divide by 64 and 128 prescaler for low power frequency division of a 2.8 GHz high frequency input signal. The low power (10.2 mA typical at 5.0 V) and high operating frequency features make this prescaler ideal in satellite TV receiver applications.

Divide ratio control input SW selects the required divide ratio of  $\div$ 64 or  $\div$ 128.

On-chip output termination provides 2.5 mA of output current to drive a 12 pF (typical) high impedance load. The output voltage swing under typical supply voltage and temperature conditions is 1.2 V. If additional drive is required for the prescaler output, an external resistor can be added in parallel from the OUT pin to Gnd to increase the output power. Care must be taken not to exceed the maximum allowable current through the output.

- 2.8 GHz Toggle Frequency
- Supply Voltage 4.5 to 5.5 V
- Low Power Dissipation 51 mW Typical
- Operating Temperature Range of –40 to 85°C

## FUNCTIONAL TABLE

SW	Divide Ratio
Н	64
L	128

**NOTE:**  $H = V_{CC}$ , L = Open.

### MAXIMUM RATINGS


Characteristic	Symbol	Range	Unit
Power Supply Voltage, Pin 4	VCC	-0.5 to 7.0	Vdc
Operating Temperature Range	TA	-40 to 85	°C
Storage Temperature Range	T <sub>stg</sub>	-65 to 150	°C
Maximum Output Current, Pin 7	IO	4.0	mA

NOTE: ESD data available upon request.


# MECL PLL COMPONENTS +64/128 PRESCALER

MC12089

SEMICONDUCTOR TECHNICAL DATA



### **PIN CONNECTIONS**



ORDERING INFORMATION

Device		Operating Temperature Range	Package	
	MC12089D	T <sub>A</sub> = −40 to 85°C	SO–8	

### © Motorola, Inc. 1998





Semiconductor, Inc

Freescale

Σ

Ш


# Freescale Semiconductor, Inc.


**ELECTRICAL CHARACTERISTICS** ( $V_{CC}$  = 4.5 to 5.5 V;  $T_A$  = -40 to 85°C, unless otherwise noted.)

Parameter		Symbol	Min	Тур	Max	Unit
Toggle Frequency (Sine Wave)		ft	0.25	3.4	2.8	GHz
Supply Current Output (Pin 2)		ICC	-	10.2	14.5	mA
Input Voltage Sensitivity	250–500 MHz 500–2800 MHz	V <sub>in</sub>	400 100		1000 1000	mVpp
Divide Ratio Control Input High (SW)		VIH	VCC	Vcc	VCC	V
Divide Ratio Control Input Low (SW)		VIL	Open	Open	Open	-
Output Voltage Swing (Note 1)		Vout	0.8	1.2	-	V <sub>pp</sub>

NOTE: 1. Assumes C<sub>L</sub> = 12 pF

Figure 1. Logic Diagram (MC12089)







# Freescale Semiconductor, Inc.





Figure 3. Input Signal Amplitude versus Input Frequency


**ARCHIVE INFORMATION** 



# Freescale Semiconductor, Inc.

# OUTLINE DIMENSIONS





Semiconductor

6

Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Motorola data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights nor the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part. Motorola and (A) are registered trademarks of Motorola, Inc. Motorola, Inc. is an Equal Opportunity/Affirmative Action Employer.

### How to reach us:

USA/EUROPE/Locations Not Listed: Motorola Literature Distribution; P.O. Box 5405, Denver, Colorado 80217. 1-303-675-2140 or 1-800-441-2447

Customer Focus Center: 1-800-521-6274

Mfax™: RMFAX0@email.sps.mot.com - TOUCHTONE 1-602-244-6609 - US & Canada ONLY 1-800-774-1848 Motorola Fax Back System - http://sps.motorola.com/mfax/

HOME PAGE: http://motorola.com/sps/



ASIA/PACIFIC: Motorola Semiconductors H.K. Ltd.; 8B Tai Ping Industrial Park, 51 Ting Kok Road, Tai Po, N.T., Hong Kong. 852–26629298

4-32-1 Nishi-Gotanda, Shinagawa-ku, Tokyo, Japan. 81-3-5487-8488

JAPAN: Motorola Japan Ltd.; SPD, Strategic Planning Office, 141,

# **ARCHIVE INFORMATION**

 $^{\Diamond}$ For More Information On This Product, Go to: www.freescale.com

Mfax is a trademark of Motorola. Inc.