

### . reescale Semiconductor

Technical Data

MHL9838 Rev. 4, 1/2005

Replaced by MHL9838N. There are no form, fit or function changes with this part replacement. N suffix added to part number to indicate transition to lead-free terminations

## Cellular Band RF Linear LDMOS Amplifier

Designed for ultra-linear amplifier applications in 50 ohm systems operating in the cellular frequency band. A silicon FET Class A design provides outstanding linearity and gain. In addition, the excellent group delay and phase linearity characteristics are ideal for the most demanding analog or digital modulation systems, such as TDMA and CDMA.

- Third Order Intercept: 50 dBm Typ
- Power Gain: 31 dB Typ (@ f = 880 MHz)
- Excellent Phase Linearity and Group Delay Characteristics
- Ideal for Feedforward Base Station Applications
- For Use in TDMA and CDMA Multi-Carrier Applications

## **MHL9838**

800 - 925 MHz 8.0 W, 31 dB RF LINEAR LDMOS AMPLIFIER




Table 1. Absolute Maximum Ratings (T<sub>C</sub> = 25°C unless otherwise noted)

| Rating                           | Symbol           | Value        | Unit |
|----------------------------------|------------------|--------------|------|
| DC Supply Voltage                | V <sub>DD</sub>  | 30           | Vdc  |
| RF Input Power                   | P <sub>in</sub>  | +6           | dBm  |
| Storage Temperature Range        | T <sub>stg</sub> | - 40 to +100 | °C   |
| Operating Case Temperature Range | T <sub>C</sub>   | - 20 to +100 | °C   |

Table 2. Electrical Characteristics (V<sub>DD</sub> = 28 Vdc, T<sub>C</sub> = 25°C; 50 Ω System)

| Characteristic                              |                     | Symbol                | Min | Тур   | Max   | Unit |
|---|---------------------|-----------------------|-----|-------|-------|------|
| Supply Current                              |                     | I <sub>DD</sub>       | _   | 770   | 800   | mA   |
| Power Gain                                  | (f = 880 MHz)       | G <sub>p</sub>        | 30  | 31    | 32    | dB   |
| Gain Flatness                               | (f = 800 - 925 MHz) | G <sub>F</sub>        | _   | 0.1   | 0.3   | dB   |
| Power Output @ 1 dB Comp.                   | (f = 880 MHz)       | P <sub>out</sub> 1 dB | _   | 39    | _     | dBm  |
| Input VSWR                                  | (f = 800 - 925 MHz) | VSWR <sub>in</sub>    | _   | 1.2:1 | 1.5:1 |      |
| Output VSWR                                 | (f = 800 - 925 MHz) | VSWR <sub>out</sub>   | _   | 1.2:1 | 1.5:1 |      |
| Third Order Intercept (f1 = 879 MHz, f2 = 8 | 84 MHz)             | ITO                   | 49  | 50    | _     | dBm  |
| Noise Figure                                | (f = 925 MHz)       | NF                    | _   | 3.7   | 4.5   | dB   |



### **TYPICAL CHARACTERISTICS**




Figure 1. Power Gain, Input Return Loss, Output Return Loss versus Frequency




Figure 2. P1dB, ITO versus Frequency




Figure 3. Power Gain, I<sub>DD</sub> versus Temperature




Figure 4. ITO, P1dB versus Temperature




Figure 5. Phase<sup>(1)</sup>, Group Delay<sup>(1)</sup> versus Temperature

1. In Production Test Fixture





Figure 6. Gain Flatness, Phase Linearity versus Temperature

### MHL9838




### **TYPICAL CHARACTERISTICS**



52 40 50 39 ITO 38 ITO (dBm) 48 P1dB P1dB (dBm) 46 37 f = 880 MHz 36 44 T<sub>C</sub> = 25°C 42 L 22 \_\_\_35 30 26 28 24 **VOLTAGE (VOLTS)** 

Figure 7. Power Gain,  $I_{DD}$  versus Voltage

Figure 8. ITO, P1dB versus Voltage






Figure 9. Phase<sup>(1)</sup>, Group Delay<sup>(1)</sup> versus Voltage

1. In Production Test Fixture

Figure 10. Phase Linearity, Gain Flatness versus Voltage

0.15



# **NOTES**





# **NOTES**





# **NOTES**



**ARCHIVE INFORMATION** 

### **PACKAGE DIMENSIONS**





NOTES:

- 1. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 1994. 2. CONTROLLING DIMENSION: INCH. 3. DIMENSION "F" TO CENTER OF LEADS.

|     | INC       | HES       | MILLIMETERS |           |  |  |
|-----|-----------|-----------|-------------|-----------|--|--|
| DIM | MIN       | MAX       | MIN         | MAX       |  |  |
| Α   | 1.760     | 1.780     | 44.70       | 45.21     |  |  |
| В   | 1.370     | 1.390     | 34.80       | 35.31     |  |  |
| С   | 0.245     | 0.265     | 6.22        | 6.73      |  |  |
| D   | 0.017     | 0.023     | 0.43        | 0.58      |  |  |
| E   | 0.080     | 0.100     | 2.03        | 2.54      |  |  |
| F   | 0.086 BSC |           | 2.18 BSC    |           |  |  |
| G   | 1.650     | 1.650 BSC |             | 41.91 BSC |  |  |
| Н   | 1.290     | BSC       | 32.77 BSC   |           |  |  |
| J   | 0.266     | 0.280     | 6.76        | 7.11      |  |  |
| K   | 0.125     | 0.165     | 3.18        | 4.19      |  |  |
| L   | 0.990     | 0.990 BSC |             | BSC       |  |  |
| N   | 0.390 BSC |           | 9.91 BSC    |           |  |  |
| P   | 0.008     | 0.013     | 0.20        | 0.33      |  |  |
| Q   | 0.118     | 0.132     | 3.00        | 3.35      |  |  |
| R   | 0.535     | 0.555     | 13.59       | 14.10     |  |  |
| S   | 0.445     | 0.465     | 11.30       | 11.81     |  |  |
| W   | 0.090 BSC |           | 2.29 BSC    |           |  |  |

STYLE 1:
PIN 1. RF INPUT
2. VDD1
3. VDD2
4. RF OUTPUT
CASE: GROUND

**CASE 301AP-02 ISSUE C** 

### How to Reach Us:

Home Page:

www.freescale.com

E-mail:

support@freescale.com

#### **USA/Europe or Locations Not Listed:**

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 +1-800-521-6274 or +1-480-768-2130 support@freescale.com

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH
Technical Information Center
Schatzbogen 7
81829 Muenchen, Germany
+44 1296 380 456 (English)
+46 8 52200080 (English)
+49 89 92103 559 (German)
+33 1 69 35 48 48 (French)
support@freescale.com

#### Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

#### Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd. Technical Information Center 2 Dai King Street
Tai Po Industrial Estate
Tai Po, N.T., Hong Kong
+800 2666 8080
support.asia@freescale.com

### For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center P.O. Box 5405
Denver, Colorado 80217
1-800-441-2447 or 303-675-2140
Fax: 303-675-2150
LDCForFreescaleSemiconductor@hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale<sup>™</sup> and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. © Freescale Semiconductor, Inc. 2005. All rights reserved.



Document Number: MHL9838

Rev. 4, 1/2005