Document Number: MHL9838N

Rev. 7, 8/2006

8.0 W, 31 dB **RF LINEAR LDMOS AMPLIFIER**

CASE 301AP-02, STYLE 1

MHL9838N

800 - 925 MHz

Cellular Band **RF Linear LDMOS Amplifier**

Designed for ultra-linear amplifier applications in 50 ohm systems operating in the cellular frequency band. A silicon FET Class A design provides outstanding linearity and gain. In addition, the excellent group delay and phase linearity characteristics are ideal for the most demanding analog or digital modulation systems, such as TDMA and CDMA.

- Third Order Intercept: 50 dBm Typ
- Power Gain: 31 dB Typ (@ f = 880 MHz)
- Input and Output VSWR ≤ 1.5:1

Features

- Excellent Phase Linearity and Group Delay Characteristics
- Ideal for Feedforward Base Station Applications
- For Use in TDMA and CDMA Multi-Carrier Applications
- N Suffix Indicates Lead-Free Terminations

Table 1. Absolute Maximum Ratings (T_C = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
DC Supply Voltage	V_{DD}	30	Vdc
RF Input Power	P _{in}	+6	dBm
Storage Temperature Range	T _{stg}	- 40 to +100	°C
Operating Case Temperature Range	T _C	- 20 to +100	°C

Table 2. Electrical Characteristics (V_{DD} = 28 Vdc, T_{C} = 25°C; 50 Ω System)

· -	=	-				
Characteristic		Symbol	Min	Тур	Max	Unit
Supply Current		I _{DD}	_	770	800	mA
Power Gain	(f = 880 MHz)	G _p	29.5	31	32.5	dB
Gain Flatness	(f = 800 - 925 MHz)	G _F	_	0.1	0.3	dB
Power Output @ 1 dB Compression	(f = 880 MHz)	P1dB	_	39	_	dBm
Third Order Intercept (f1 = 879 MHz, f2 = 884 MHz)		ITO	49	50	_	dBm
Noise Figure	(f = 925 MHz)	NF	_	3.7	4.5	dB

NOTE - CAUTION - MOS devices are susceptible to damage from electrostatic charge. Reasonable precautions in handling and packaging MOS devices should be observed.





TYPICAL CHARACTERISTICS




Figure 1. Power Gain, Input Return Loss, Output Return Loss versus Frequency




Figure 2. P1dB, ITO versus Frequency




Figure 3. Power Gain, I_{DD} versus Temperature




Figure 4. ITO, P1dB versus Temperature




Figure 5. Phase⁽¹⁾, Group Delay⁽¹⁾ versus Temperature

1. In Production Test Fixture





Figure 6. Gain Flatness, Phase Linearity versus Temperature

MHL9838N




TYPICAL CHARACTERISTICS



52 40 50 39 ITO 38 ITO (dBm) 48 P1dB P1dB (dBm) 46 37 f = 880 MHz 36 44 T_C = 25°C 42 L 22 ___35 30 26 28 24 **VOLTAGE (VOLTS)**

Figure 7. Power Gain, I_{DD} versus Voltage

Figure 8. ITO, P1dB versus Voltage






Figure 9. Phase⁽¹⁾, Group Delay⁽¹⁾ versus Voltage


1. In Production Test Fixture


Figure 10. Phase Linearity, Gain Flatness versus Voltage

0.15



PACKAGE DIMENSIONS





- NOTES:

 1. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 1994.
 2. CONTROLLING DIMENSION: INCH.
 3. DIMENSION "F" TO CENTER OF LEADS.

	INC	HES	MILLIMETERS			
DIM	MIN	MAX	MIN	MAX		
Α	1.760	1.780	44.70	45.21		
В	1.370	1.390	34.80	35.31		
C	0.245	0.265	6.22	6.73		
D	0.017	0.023	0.43	0.58		
Е	0.080	0.100	2.03	2.54		
F	0.086	BSC	2.18 BSC			
G	1.650 BSC		41.91 BSC			
Н	1.290	1.290 BSC		BSC		
7	0.266	0.280	6.76	7.11		
K	0.125	0.165	3.18	4.19		
L	0.990	BSC	25.15 BSC			
N	0.390 BSC		9.91 BSC			
P	0.008	0.013	0.20	0.33		
Ø	0.118	0.132	3.00	3.35		
R	0.535	0.555	13.59	14.10		
S	0.445	0.465	11.30	11.81		
w	0.090	0.090 BSC		2 29 BSC		

STYLE 1:
PIN 1. RF INPUT
2. VDD1
3. VDD2
4. RF OUTPUT
CASE: GROUND

CASE 301AP-02 ISSUE E

How to Reach Us:

Home Page:

www.freescale.com

E-mail:

support@freescale.com

USA/Europe or Locations Not Listed:

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 +1-800-521-6274 or +1-480-768-2130 support@freescale.com

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) support@freescale.com

Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd.
Technical Information Center
2 Dai King Street
Tai Po Industrial Estate
Tai Po, N.T., Hong Kong
+800 2666 8080
support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center P.O. Box 5405
Denver, Colorado 80217
1-800-441-2447 or 303-675-2140
Fax: 303-675-2150
LDCForFreescaleSemiconductor@hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or quarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale $^{>}$ and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. © Freescale Semiconductor, Inc. 2006, 2007. All rights reserved.



Document Number: MHL9838N

Rev. 7, 8/2006