

. reescale Semiconductor Technical Data

Replaced by MHPA18010N. There are no form, fit or function changes with this part replacement. N suffix added to part number to indicate transition to lead-free terminations.

CDMA Band RF Linear LDMOS Amplifier

Designed for Class AB amplifier applications in 50 ohm systems operating in the 1800 to 1900 MHz frequency band. A silicon FET design provides outstanding linearity and gain. In addition, the excellent group delay and phase linearity characteristics are ideal for digital CDMA and GSM modulation systems.

- Typical CDMA Performance: 1840 MHz, 28 Volts IS-95 CDMA Pilot, Sync, Paging, Traffic Codes 8 Through 13
- Adjacent Channel Power: -51 dBc @ 30 dBm Average Power, 885 kHz Channel Spacing
- Power Gain: 24.5 dB Min (@ f = 1840 MHz)
- Excellent Phase Linearity and Group Delay Characteristics
- Ideal for Feedforward Base Station Applications

MHPA18010

1805-1880 MHz 10 W, 24.5 dB RF HIGH POWER LDMOS AMPLIFIER




Table 1. Maximum Ratings (T_C = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
DC Supply Voltage	V_{DD}	30	Vdc
RF Input Power (Single Carrier CW)	P _{in}	+20	dBm
Storage Temperature Range	T _{stg}	- 40 to +100	°C
Operating Case Temperature Range	T _C	- 20 to +100	°C

Table 2. Electrical Characteristics (V_{DD} = 28 Vdc, V_{BIAS} ≅ 8 V Set for Supply Current of 600 mA, T_C = 25°C, 50 Ω System)

Character	Symbol	Min	Тур	Max	Unit	
Supply Current		I _{DD}	_	600	_	mA
Power Gain	(f = 1840 MHz)	G _p	24.5	25.5	_	dB
Gain Flatness	(f = 1805 - 1880 MHz)	G _F	_	0.2	0.5	dB
Power Output @ 1 dB Comp.	(f = 1840 MHz)	P1dB	_	41.5	_	dBm
Input VSWR	(f = 1805 - 1880 MHz)	VSWR _{in}	_	1.5:1	2:1	
Noise Figure	(f = 1840 MHz)	NF	_	8	10	dB
Adjacent Channel Power Rejection @ 30 dBm Average Power, 1.23 MHz BW, 885 kHz Channel Spacing		ACPR	_	-58	- 51	dBc




NOTES



ARCHIVE INFORMATION

PACKAGE DIMENSIONS





NOTES:

- I. INTERPRET DIMENSIONS AND TOLERANCES
 PER ASME Y14.5M, 1994.
- 2. CONTROLLING DIMENSION: INCH.
 3. DIMENSION "F" TO CENTER OF LEADS.

	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	1.760	1.780	44.70	45.21	
В	1.370	1.390	34.80	35.31	
С	0.245	0.265	6.22	6.73	
D	0.017	0.023	0.43	0.58	
E	0.080	0.100	2.03	2.54	
F	0.086	BSC	2.18 BSC		
G	1.650) BSC	41.91 BSC		
Н	1.290 BSC		32.77 BSC		
J	0.266	0.280	6.76	7.11	
K	0.125	0.165	3.18	4.19	
L	0.990 BSC		25.15 BSC		
N	0.390	BSC	9.91 BSC		
P	0.008	0.013	0.20	0.33	
Q	0.118	0.132	3.00	3.35	
R	0.535	0.555	13.59	14.10	
S	0.445	0.465	11.30	11.81	
W	0.090 BSC		2.29 BSC		

STYLE 3:
PIN 1. RF INPUT
2. VBIAS
3. VDD
4. RF OUTPUT
CASE: GROUND

CASE 301AP-02 ISSUE C

How to Reach Us:

Home Page:

www.freescale.com

E-mail:

support@freescale.com

USA/Europe or Locations Not Listed:

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 +1-800-521-6274 or +1-480-768-2130 support@freescale.com

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) support@freescale.com

Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd.
Technical Information Center
2 Dai King Street
Tai Po Industrial Estate
Tai Po, N.T., Hong Kong
+800 2666 8080
support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center P.O. Box 5405
Denver, Colorado 80217
1-800-441-2447 or 303-675-2140
Fax: 303-675-2150
LDCForFreescaleSemiconductor@hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale [™] and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. © Freescale Semiconductor, Inc. 2005. All rights reserved.

