

. reescale Semiconductor Technical Data

Document Number: MHW1223LA

Rev. 1, 10/2002

CATV Amplifier Module

Features

- Specified for 6- and 10-Channel Loading
- **Excellent Distortion Performance**
- Low Power Consumption
- Capable of Handling Multiple Channels in the Return Path with Good Distortion Performance
- Silicon Bipolar Transistor Technology
- Unconditionally Stable Under All Load Conditions

Applications

- CATV Systems Operating in the 5 to 200 MHz Frequency Range
- Specified for Use as a Return Path Amplifier for Low-, Mid- and High-Split 2-Way Cable TV Systems

Description

• 24 Vdc Supply, 5 to 200 MHz, CATV Reverse Amplifier Module

MHW1223LA

5-200 MHz, 22.7 dB, 10-CHANNEL **CATV LOW CURRENT AMPLIFIER MODULE**




Table 1. Maximum Ratings

Parameter	Symbol	Value	Unit
DC Supply Voltage	V _{CC}	+28	Vdc
RF Input Voltage (Single Tone)	V _{in}	+60	dBmV
Operating Case Temperature Range	T _C	- 20 to +100	°C
Storage Temperature Range	T _{stg}	- 40 to +100	°C

Table 2. Electrical Characteristics (V_{CC} = 24 Vdc, T_{C} = 30°C, 75 Ω system, unless otherwise noted)

Character	Symbol	Min	Тур	Max	Unit	
Bandwidth	All	BW	5	_	200	MHz
Power Gain	(f = 5 MHz)	G _p	22.1	22.7	23.5	dB
Slope	(5-200 MHz)	S	- 0.2	_	0.7	dB
Gain Flatness (Peak To Valley)	(5-200 MHz)	G _F	=	_	0.4	dB
Return Loss — Input/Output (@ f = 5-150 MHz) (@ f = 150-200 MHz)		IRL/ORL	20 18	_ _	_ _	dB
Composite Second Order (Vout = +50 dBmV per Ch., Worst Case)		000				dBc
	6-Channel FLAT 10-Channel FLAT	CSO ₆ CSO ₁₀	_	- 73 - 72	- 68 - 65	





Table 2. Electrical Characteristics (V_{CC} = 24 Vdc, T_C = 30°C, 75 Ω system, unless otherwise noted) (continued)

Characteristic	Symbol	Min	Тур	Max	Unit	
Cross Modulation Distortion						dBc
(V _{out} = +50 dBmV per Ch., Worst Case)						
	6-Channel FLAT	XMD_6	_	- 69	- 65	
	10-Channel FLAT	XMD ₁₀	_	- 63	- 60	
Composite Triple Beat						dBc
(V _{out} = +50 dBmV per Ch., Worst Case)						
	6-Channel FLAT	CTB ₆	_	- 78	- 75	
	10-Channel FLAT	CTB ₁₀	_	- 69	- 66	
Noise Figure		NF				dB
	(f = 5-200 MHz)		_	6.3	7	
DC Current		I _{DC}	85	95	110	mA

ARCHIVE INFORMATION

PACKAGE DIMENSIONS





	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α		1.775		45.085	
В		1.085		27.559	
С		0.840		21.336	
D	0.015	0.021	0.381	0.533	
E	0.465	0.510	11.811	12.954	
F	0.300	0.325	7.62	8.255	
G	0.100 BSC		2.540 BSC		
J	0.156	BSC 3.962 BS		BSC	
K	0.315	0.355	8.001	9.017	
L	1.000 BSC		25.400 BSC		
N	0.165 BSC		4.191 BSC		
P	0.100 BSC		2.540 BSC		
Q	0.148	0.168	3.759	4.267	
R		0.600		15.24	
S	1.500 BSC		38.100 BSC		
U	0.200	BSC	5.080 BSC		
٧		0.250		6.350	
W	0.435		11.049		
Х	0.400 BSC		10.160 BSC		
Y	0.152	0.163	3.861	4.140	
Z	0.009	0.011	0.229	0.279	

CASE 1302-01 ISSUE B

ARCHIVE INFORMATION

STYLE 1:
PIN 1. RF INPUT
2. GROUND
3. GROUND
4. DELETED
5. VDC
6. DELETED
7. GROUND
8. GROUND
9. RF OUTPUT

How to Reach Us:

Home Page:

www.freescale.com

E-mail:

support@freescale.com

USA/Europe or Locations Not Listed:

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 +1-800-521-6274 or +1-480-768-2130 support@freescale.com

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) support@freescale.com

Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd.
Technical Information Center
2 Dai King Street
Tai Po Industrial Estate
Tai Po, N.T., Hong Kong
+800 2666 8080
support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center P.O. Box 5405
Denver, Colorado 80217
1-800-441-2447 or 303-675-2140
Fax: 303-675-2150
LDCForFreescaleSemiconductor@hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale [™] and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. © Freescale Semiconductor, Inc. 2002, 2006. All rights reserved.



Document Number: MHW1223LA Rev. 1, 10/2002