

MPC7410 RISC Microprocessor Hardware Specifications Addendum for the MPC7410RX nnn PE Series

This document describes part-number-specific changes to recommended operating conditions and revised electrical specifications, as applicable, from those described in the general *MPC7410 Hardware Specifications* (Document No. MPC7410EC).

Specifications provided in this document supersede those in the *MPC7410 Hardware Specifications*, for the part numbers listed in [Table A](#) only. Specifications not addressed herein are unchanged. Because this document is frequently updated, refer to <http://www.freescale.com> or to your Freescale sales office for the latest version.

Note that headings and table numbers in this document are not consecutively numbered. They are intended to correspond to the heading or table affected in the general hardware specification. Part numbers addressed in this document are listed in [Table A](#). For more detailed ordering information see [Table 17](#).

Freescale Part Numbers Affected:

MPC7410RX450PE
MPC7410RX500PE
MPC7410RX550PE

Table A. Part Numbers Addressed by this Data Sheet

Freescale Part Number	Operating Conditions			Significant Differences from Hardware Specification
	CPU Frequency	Vdd	T _J (°C)	
MPC7410RX450PE	450 MHz	2.0V±50mV	0 to 65	Modified Voltage & Temperature Specification to achieve 450Mhz frequency
MPC7410RX500PE	500 MHz	2.0V±50mV	0 to 65	Modified Voltage & Temperature Specification to achieve 500Mhz frequency
MPC7410RX550PE	550 MHz	2.0V±50mV	0 to 65	Modified Voltage & Temperature Specification to achieve 550Mhz frequency

2 Features

This section summarizes changes to the features of the MPC7410 described in the MPC7410 Hardware Specifications, of which there were none.

4.1 DC Electrical Characteristics

Table 3 provides the recommended operating conditions for the MPC7410 part numbers described herein.

Table 3. Recommended Operating Conditions

Characteristic		Symbol	Recommended Value	Unit
Core supply voltage		Vdd	2.0V ± 50mV	V
PLL supply voltage		AVdd	2.0V ± 50mV	V
L2 DLL supply voltage		L2AVdd	2.0V ± 50mV	V
Processor bus supply voltage	BVSEL = 1 or BVSEL = HRESET	OVdd	3.3V ± 165mV	
	BVSEL = $\overline{\text{HRESET}}$	OVdd	2.5V ± 125mV	V
	BVSEL = GND	OVdd	1.8V ± 90mV	V
L2 bus supply voltage	L2VSEL = 1 or L2VSEL = $\overline{\text{HRESET}}$	L2OVdd	2.5V ± 125mV	V
	L2VSEL = GND	L2OVdd	1.8V ± 90mV	V
Input voltage	Processor bus	V _{in}	GND to OVdd	V
	L2 Bus	V _{in}	GND to L2OVdd	V
	JTAG Signals	V _{in}	GND to OVdd	V
Die-junction temperature		T _J	0-65	°C

Note:

These are the recommended and tested operating conditions. Proper device operation outside of these conditions is not guaranteed.

Table 6 provides the power consumption for the MPC7410 part at the frequencies described herein.

Table 6. Power Consumption for MPC7410

	Processor (CPU) Frequency	Processor (CPU) Frequency	Processor (CPU) Frequency	Unit	Notes
	450Mhz	500Mhz	550Mhz		
Full-On Mode					
Typical	5.9	6.5	7.1	W	1, 3
Maximum	13.2	14.7	16.2	W	1, 2
Doze Mode					
Maximum	4.5	5	5.5	W	1, 2
Nap Mode					
Maximum	2.13	2.25	2.37	W	1, 2
Sleep Mode					
Maximum	2.13	2.25	2.37	W	1, 2
Sleep Mode—PLL and DLL Disabled					
Typical	0.5	0.5	0.5	W	1, 3
Maximum	2.0	2.0	2.0	W	1, 2

Notes:

1. These values apply for all valid processor bus and L2 bus ratios. The values do not include I/O Supply Power (OVdd and L2OVdd) or PLL/DLL supply power (AVdd and L2AVdd). OVdd and L2OVdd power is system dependent, but is typically <10% of Vdd power. Worst case power consumption for AVdd = 15 mw and L2AVdd = 15 mW.
2. Maximum power is measured at 65 °C and Vdd = 2.0V while running an entirely cache-resident, contrived sequence of instructions which keep the execution units, including Altivec, maximally busy.
3. Typical power is an average value measured at 65 °C and Vdd = 2.0V in a system while running typical benchmarks.

4.2.1 Clock AC Specifications

Table 7 provides the additional clock AC timing specifications described in this document. Refer to the *MPC7410 Hardware Specification* for the remaining frequencies.

Table 7. Clock AC Timing Specifications

At recommended operating conditions (See Table 3)

Characteristic	Symbol	450 MHz		500 MHz		550 MHz		Unit	Notes
		Min	Max	Min	Max	Min	Max		
Processor frequency	f_{core}	300	450	300	500	300	550	MHz	
VCO frequency	f_{VCO}	600	900	600	1000	600	1100	MHz	
SYSCLK frequency	f_{SYSCLK}	33	133	33	133	33	133	MHz	1
SYSCLK cycle time	t_{SYSCLK}	7.5	30	7.5	30	7.5	30	ns	
SYSCLK rise and fall time	t_{KR}	—	1.0	—	1.0	—	1.0	ns	2
	t_{KF}	—	0.5	—	0.5	—	0.5	ns	3
SYSCLK duty cycle measured at $OV_{dd}/2$	t_{KHKL}/t_{SYSCLK}	40	60	40	60	40	60	%	4
SYSCLK jitter		—	± 150	—	± 150	—	± 150	ps	5
Internal PLL relock time		—	100	—	100	—	100	μs	6

Note:

See general hardware specification.

4.2.2 Processor Bus AC Specifications

Table 8 provides the processor bus AC timing specifications for the MPC7410 part described in this document.

Table 8. Processor Bus AC Timing Specifications

At $V_{dd}=AV_{dd}=2.0V \pm 50mV$; $0 \leq T_j \leq 65^\circ C$, $OV_{dd} = 2.5V \pm 0.125V$ and $OV_{dd} = 1.8V \pm 0.090V$, 60X bus at 133MHz

Parameter	Symbol	450, 500, 550 Mhz		Unit	Notes
		Min	Max		
Mode select input setup to \overline{HRESET}	t_{MVRH}	8	—	t_{sysclk}	2,3,4,5
\overline{HRESET} to mode select input hold	t_{MXRH}	0	—	ns	2,3,5
Setup Times:				ns	10
Address/Transfer Attribute	t_{AVKH}	1.4	—		6
Transfer Start (TS)	t_{TSVKH}	1.4	—		—
Data/Data Parity	t_{DVKH}	1.4	—		7
$\overline{ARTRY}/\overline{SHD0}/\overline{SHD1}$	t_{ARVKH}	1.4	—		—
All Other Inputs	t_{IVKH}	1.4	—		8

Table 8. Processor Bus AC Timing Specifications (continued)

 At $V_{dd}=AV_{dd}=2.0V\pm 50mV$; $0 \leq T_j \leq 65^\circ C$, $OV_{dd} = 2.5V\pm 0.125V$ and $OV_{dd} = 1.8V\pm 0.090V$, 60X bus at 133MHz

Parameter	Symbol	450, 500, 550 Mhz		Unit	Notes
		Min	Max		
Input Hold Times:				ns	11
Address/Transfer Attribute	t_{AXKH}	0	—		6
Transfer Start (\overline{TS})	t_{TSXKH}	0	—		—
Data/Data Parity	t_{DXKH}	0	—		7
$\overline{ARTRY}/\overline{SHD0}/\overline{SHD1}$	t_{ARXKH}	0	—		—
All Other Inputs	t_{IXKH}	0	—		8
Valid Times:				ns	12
Address/Transfer Attribute	t_{KHAV}	—	3.0		6
\overline{TS} , \overline{ABB} , \overline{DBB}	t_{KHTSV}	—	3.0		—
Data	t_{KHDV}	—	3.5		7
Data Parity	t_{KHDPV}	—	3.5		7
$\overline{ARTRY}/\overline{SHD0}/\overline{SHD1}$	t_{KHARV}	—	2.3		—
All Other Outputs	t_{KHOV}	—	3.0		9
Output Hold Times:				ns	13
Address/Transfer Attribute	t_{KHAX}	0.75	—		6
\overline{TS} , \overline{ABB} , \overline{DBB}	t_{KHTSX}	0.75	—		—
Data/Data Parity	t_{KHDX}	0.6	—		7
$\overline{ARTRY}/\overline{SHD0}/\overline{SHD1}$	t_{KHARX}	0.75	—		—
All Other Outputs	t_{KHOX}	0.75	—		9
SYSCLK to Output Enable	t_{KHOE}	0.5	—	ns	14
SYSCLK to Output High Impedance (all except \overline{TS} , $\overline{ABB}/\overline{AMON}(0)$, $\overline{ARTRY}/\overline{SHD}$, $\overline{DBB}/\overline{DMON}(0)$)	t_{KHOZ}	—	3.5	ns	15
SYSCLK to \overline{TS} , $\overline{ABB}/\overline{AMON}(0)$, $\overline{DBB}/\overline{DMON}(0)$ High Impedance after precharge	t_{KHABPZ}	—	1.0	t_{sysclk}	4,15, 16,17
Maximum Delay to $\overline{ARTRY}/\overline{SHD0}/\overline{SHD1}$ Precharge	t_{KHARP}	—	1	t_{sysclk}	4,17
SYSCLK to $\overline{ARTRY}/\overline{SHD0}/\overline{SHD1}$ High Impedance After Precharge	t_{KHARPZ}	—	2	t_{sysclk}	4,17

Notes:

See General hardware specification.

4.2.3 L2 Clock AC Specifications

Table 9 provides the L2CLK Output AC Timing Specifications for the MPC7410 part described in this document.

Table 9. L2CLK Output AC Timing Specifications

At recommended operating conditions (See Table 3)

Parameter	Symbol	450 MHz		500 MHz		550 MHz		Unit	Notes
		Min	Max	Min	Max	Min	Max		
L2CLK frequency	f_{L2CLK}	150	225	150	250	150	275	MHz	1
L2CLK cycle time	t_{L2CLK}	4.4	6.67	4.0	6.67	3.64	6.67	ns	
L2CLK duty cycle	t_{CHCL}/t_{L2CLK}	50		50		50		%	2
Internal DLL-relock time		640	—	640	—	640	—	L2CLK	4
DLL capture window			±200		±200		±200	ns	5

Note:

See general hardware specification.

4.2.4 L2 Bus AC Specifications

Table 10 provides the L2 Bus Interface AC Timing Specifications for the frequencies described in this document.

Table 10. L2 Bus Interface AC Timing Specifications

At Vdd=AVdd=L2AVdd= 2.05V±50mV; 0 ≤ Tj ≤ 65°C, L2OVdd = 2.5V±0.125V and L2OVdd = 1.8V±0.090V

Parameter	Symbol	450, 500, 550 MHz		Unit	Notes
		Min	Max		
L2SYNC_IN rise and fall time	t _{L2CR} & t _{L2CF}	—	1.0	ns	1
Setup Times: Data and parity	t _{DVL2CH}	1.250	—	ns	2
Input Hold Times: Data and parity	t _{DXL2CH}	—	0.0	ns	2
Valid Times: All outputs when L2CR[14-15] = 00 All outputs when L2CR[14-15] = 01 All outputs when L2CR[14-15] = 10 All outputs when L2CR[14-15] = 11	t _{L2CHOV}	- - - -	2.25 2.50 2.75 3.25	ns	3,4
Output Hold Times All outputs when L2CR[14-15] = 00 All outputs when L2CR[14-15] = 01 All outputs when L2CR[14-15] = 10 All outputs when L2CR[14-15] = 11	t _{L2CHOX}	0.5 0.9 1.3 1.7	- - - -	ns	3
L2SYNC_IN to high impedance: All outputs when L2CR[14-15] = 00 All outputs when L2CR[14-15] = 01 All outputs when L2CR[14-15] = 10 All outputs when L2CR[14-15] = 11	t _{L2CHOZ}	- - - -	2.0 2.5 3.0 3.5	ns	

Notes: See General Hardware Specification

9 Document Revision History

Table 16 provides a revision history for this document.

Table 16. Document Revision History

Revision	Date	Substantive Change(s)
1.1	4/19/2005	Document template update
		Document ID change from MPC7410RXPEPNS for Part Number Specification to MPC7410ECS05AD for Hardware Specification Addendum.
1	10/2002	Minor formatting
		Section 1.10.1 - added Table 17 - Part Marking Nomenclature
0		Initial release.

10 Ordering Information

10.1 Part Numbers Addressed by this Specification

Table 17 provides the ordering information for the MPC7410 part described in this document.

Table 17. Part Marking Nomenclature

MPC 7410 RX xxx X X


Product Code	Part Identifier	Package	Processor Frequency ¹	Application Modifier	Revision Level
MPC	7410	RX = CBGA	450 500 550	P: 2.0 V ± 50 mV 0 to 65 °C	E: 1.4; PVR = 800C 1104

Notes:

1. Processor core frequencies supported by parts addressed by this specification only. Parts addressed by other specifications may support other maximum core frequencies.

10.3 Part Marking

Parts are marked as the example shown in [Figure 26](#).



Notes:

- nnn* is the speed grade of the part
- MMMMM is the 6-digit mask number
- ATWLYYWWA is the traceability code
- CCCCC is the country of assembly (this space is left blank if parts are assembled in the United States)

BGA

Figure 26. Freescale Part Marking for BGA Device

THIS PAGE INTENTIONALLY LEFT BLANK

THIS PAGE INTENTIONALLY LEFT BLANK

How to Reach Us:

Home Page:

www.freescale.com

email:

support@freescale.com

USA/Europe or Locations Not Listed:

Freescale Semiconductor
Technical Information Center, CH370
1300 N. Alma School Road
Chandler, Arizona 85224
(800) 521-6274
480-768-2130
support@freescale.com

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH
Technical Information Center
Schatzbogen 7
81829 Muenchen, Germany
+44 1296 380 456 (English)
+46 8 52200080 (English)
+49 89 92103 559 (German)
+33 1 69 35 48 48 (French)
support@freescale.com

Japan:

Freescale Semiconductor Japan Ltd.
Headquarters
ARCO Tower 15F
1-8-1, Shimo-Meguro, Meguro-ku
Tokyo 153-0064, Japan
0120 191014
+81 2666 8080
support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd.
Technical Information Center
2 Dai King Street
Tai Po Industrial Estate,
Tai Po, N.T., Hong Kong
+800 2666 8080
support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor
Literature Distribution Center
P.O. Box 5405
Denver, Colorado 80217
(800) 441-2447
303-675-2140
Fax: 303-675-2150
LDCForFreescaleSemiconductor
@hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale™ and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners.

© Freescale Semiconductor, Inc., 2002, 2005.

Document Number: MPC7410ECS05AD
Rev. 1.1
04/2005