

# Freescale Semiconductor Advance Information

Document Number: MPC7410ECS06AD

Rev. 1.1, 04/2005

# MPC7410 RISC Microprocessor Hardware Specifications Addendum for the MPC7410TRX*nnn*LE Series

This document describes part-number-specific changes to recommended operating conditions and revised electrical specifications, as applicable, from those described in the *MPC7410 RISC Microprocessor Hardware Specifications* (Document No. MPC7410EC).


Specifications provided in this document supersede those in the *MPC7410 RISC Microprocessor Hardware*Specifications, Rev. 1 or later, for the part numbers listed in Table A only. Specifications not addressed herein are unchanged. Because this document is frequently updated, refer to http://www.freescale.com or to your Freescale sales office for the latest version.

Note that headings and table numbers in this document are not consecutively numbered. They are intended to correspond to the heading or table affected in the general hardware specification.

Part numbers addressed in this document are listed in Table A. For more detailed ordering information Table 17

Freescale Part Numbers Affected: MPC7410TRX400LE MPC7410TRX450LE MPC7410TRX500LE

This document contains information on a new product. Specifications and information herein are subject to change without notice.





### **DC Electrical Characteristics**

Table A. Part Numbers Addressed by this Data Sheet

	Operating Conditions					
Freescale Part Number	CPU Frequency (MHz)	V <sub>DD</sub>	T <sub>J</sub> (°C)	OV <sub>DD</sub> (V)	Significant Differences from Hardware Specification	
MPC7410TRX500LE	500	1.8 V ±100 mV	-40 to 105	1.8/2.5/3.3	Extended temperature range. For all DC/AC specifications not mentioned in this document, please refer to the MPC7410RX500LE specifications in the MPC7410 RISC Microprocessor Hardware Specifications.	
MPC7410TRX450LE	450	1.8 V ±100 mV	-40 to 105	1.8/2.5/3.3	Extended temperature range. For all DC/AC specifications not mentioned in this document, please refer to the MPC7410RX450LE specifications in the MPC7410 RISC Microprocessor Hardware Specifications.	
MPC7410TRX400LE	400	1.8 V ±100 mV	-40 to 105	1.8/2.5/3.3	Extended temperature range. For all DC/AC specifications not mentioned in this document, please refer to the MPC7410RX400LE specifications in the MPC7410 RISC Microprocessor Hardware Specifications.	

# 4.1 DC Electrical Characteristics

Table 3 provides the recommended operating conditions for the MPC7410 part numbers described herein.

**Table 3. Recommended Operating Conditions** 

Characteristic	Symbol	Recommended Value	Unit	Notes
Die-junction temperature	T <sub>j</sub>	-40 to 105	°C	

Note: See MPC7410 RISC Microprocessor Hardware Specifications.



# 9 Document Revision History

Table 16 provides a revision history for this document.

**Table 16. Document Revision History** 

Revision	Date	Substantive Chagnes(s)	
1.1	4/20/2005	Document template update.	
		Document ID change from MPC7410TRXLEPNS for Part Number Specification to MPC7410ECS06AD for Hardware Specification Addendum.	
1	10/2002	Minor Formatting.	
0		Initial release.  Note that this part number specification replaces the MPC7410RXnnnTE part number specification (Order No. MPC7410RXnnnTE/D).	

# 10 Ordering Information

# 10.1 Part Numbers Addressed by this Specification

Table 17 provides the ordering information for the MPC7410 part described in this document.

**Table 17. Part Marking Nomenclature** 

MPC	7410	X	НX	nnn	X	X
Product Code	Part Identifier	Process Descriptor	Package	Processor Frequency <sup>1</sup>	Application Modifier	Revision Level
MPC	7410	T: -40 to 105°C	RX = CBGA	400 450 500	L: 1.8 V ±100 mV	E: 1.4; PVR = 800C 1104

### Note:

MPC7410 RISC Microprocessor Hardware Specifications Addendum for the MPC7410TRXnnnLE Series, Rev. 1.1


<sup>1.</sup>Processor core frequencies supported by parts addressed by this specification only. Parts addressed by other specifications may support other maximum core frequencies.



**Ordering Information** 

# 10.3 Part Marking

Parts are marked as the example shown in Figure 26.



### Notes:

nnn is the speed grade of the part. MMMMMM is the 6-digit mask number. ATWLYYWWA is the traceability code.

CCCCC is the country of assembly. This space is left blank if parts are assembled in the United States.

Figure 26. Part Marking for BGA Device





# THIS PAGE INTENTIONALLY LEFT BLANK



**Ordering Information** 

# THIS PAGE INTENTIONALLY LEFT BLANK

MPC7410 RISC Microprocessor Hardware Specifications Addendum for the MPC7410TRXnnnLE Series, Rev. 1.1





# THIS PAGE INTENTIONALLY LEFT BLANK



### How to Reach Us:

#### **Home Page:**

www.freescale.com

#### email

support@freescale.com

### **USA/Europe or Locations Not Listed:**

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 (800) 521-6274 480-768-2130 support@freescale.com

#### Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) support@freescale.com

#### Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku Tokyo 153-0064, Japan 0120 191014 +81 2666 8080 support.japan@freescale.com

### Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd. Technical Information Center 2 Dai King Street Tai Po Industrial Estate, Tai Po, N.T., Hong Kong +800 2666 8080 support.asia@freescale.com

# For Literature Requests Only:

Freescale Semiconductor
Literature Distribution Center
P.O. Box 5405
Denver, Colorado 80217
(800) 441-2447
303-675-2140
Fax: 303-675-2150
LDCForFreescaleSemiconductor
@ hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale<sup>™</sup> and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners.

© Freescale Semiconductor, Inc., 2002, 2005.

Document Number: MPC7410ECS06AD

Rev. 1.1 04/2005

