

Order this document by EB254/D

Motorola Semiconductor Engineering Bulletin

EB254

Setting the Programming Voltage on Modular Microcontrollers with FLASH EEPROM

By Sharon Darley Austin, Texas

Introduction

The MC68F333 has two FLASH electrically erasable programmable read-only memory (EEPROM) modules:

- 16-Kbyte module
- 48-Kbyte module

By programming the FLASH EEPROM base address registers, the user can place the 16-K array on any 16-K boundary and the 48-K array in the lower 48-K of any 64-K boundary. Either module can be configured to generate the initial program counter and stack pointer value on system reset.

They can be individually configured to reside in supervisor or unrestricted address space, and they can also be programmed to reside in either program space or data space. If desired, the user can configure them to appear as a single memory block.

The FLASH EEPROM and its control bits are erasable and programmable under software control. Explicit directions for programming the FLASH EEPROM are given in the *MC68F333 Technical Summary*, Motorola document order number





Freescale Semiconductor, Inc.

Engineering Bulletin

MC68F333TS/D, and in Engineering Bulletin 255, *Modular Microcontroller FLASH EEPROM*, Motorola document order number EB255/D.

One point of confusion that sometimes arises concerns the state of the VFPE voltage, which is the external program/erase voltage on the VFPE pins.

In normal operation, this VFPE voltage is V_{DD} , or 5 volts. However, in program/erase mode, this voltage must be 12 volts. The transition between these two voltages must be continuous. The user cannot disconnect 5 volts from VFPE before applying the 12 volts or else the VFPE pin will be destroyed.

NOTE:

The user must never allow the voltage on the VPFE pins to fall below V_{DD} .

There are two recommended ways to power-up:

- Bring VFPE to 4.7 to 5 volts at the same time as V_{DD} and then bring VFPE to 12 volts.
- Bring VFPE to 4.7 to 5 volts before powering V_{DD} and then bring VFPE to 12 volts.

See Figure 4 in Engineering Bulletin 255 for a circuit that can be safely used to switch between 5 volts and 12 volts.

Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Motorola data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights or the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part. Motorola and Archiver are registered trademarks of Motorola, Inc. Motorola, Inc. is an Equal Opportunity/Affirmative Action Employer.

How to reach us:

USA/EUROPE/Locations Not Listed: Motorola Literature Distribution, P.O. Box 5405, Denver, Colorado 80217, 1-800-441-2447 or 1-303-675-2140. Customer Focus Center, 1-800-521-6274

JAPAN: Nippon Motorola Ltd.: SPD, Strategic Planning Office, 141, 4-32-1 Nishi-Gotanda, Shinigawa-Ku, Tokyo, Japan. 03-5487-8488 ASIA/PACIFIC: Motorola Semiconductors H.K. Ltd., 8B Tai Ping Industrial Park, 51 Ting Kok Road, Tai Po, N.T., Hong Kong. 852-26629298 Mfax™, Motorola Fax Back System: RMFAX0@email.sps.mot.com; http://sps.motorola.com/mfax/;

TOUCHTONE, 1-602-244-6609; US and Canada ONLY, 1-800-774-1848

HOME PAGE: http://motorola.com/sps/

MOTOROLA

Mfax is a trademark of Motorola, Inc.

© Motorola, Inc., 1998

