The RF Line NPN Silicon RF Power Transistor


Designed for 24 Volt UHF large-signal, common base amplifier applications in industrial and commercial FM equipment operating in the range of 850–960 MHz.

- Motorola Advanced Amplifier Concept Package
- Specified 24 Volt, 900 MHz Characteristics
 Output Power = 60 Watts
 Power Gain = 7.0 dB Min
 Efficiency = 60% Min
- Double Input/Output Matched for Wideband Performance and Simplified External Matching
- Series Equivalent Large

 Signal Characterization
- Gold Metallized, Emitter Ballasted for Long Life and Resistance to Metal Migration
- Silicon Nitride Passivated
- Circuit board photomaster available upon request by contacting RF Tactical Marketing in Phoenix, AZ.

MRF898

60 W, 850-960 MHz RF POWER TRANSISTOR NPN SILICON



CASE 333A-02, STYLE 1

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector–Emitter Voltage	V _{CEO}	30	Vdc
Collector–Base Voltage	V _{CBO}	55	Vdc
Emitter-Base Voltage	V _{EBO}	4.0	Vdc
Collector Current — Continuous	I _C	10	Adc
Total Device Dissipation @ T _C = 25°C Derate above 25°C	P _D	175 1.0	Watts W/°C
Storage Temperature Range	T _{stg}	-65 to +150	°C

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction to Case	$R_{\theta JC}$	1.0	°C/W

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted.)

Characteristic	Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS	·	•			
Collector–Emitter Breakdown Voltage $(I_C = 50 \text{ mAdc}, I_B = 0)$	V _{(BR)CEO}	30	_	_	Vdc
Collector–Emitter Breakdown Voltage $(I_C = 50 \text{ mAdc}, V_{BE} = 0)$	V _(BR) CES	55	_	_	Vdc
Emitter–Base Breakdown Voltage $(I_E = 5.0 \text{ mAdc}, I_C = 0)$	V _{(BR)EBO}	4.0	_	_	Vdc
Collector Cutoff Current (V _{CE} = 30 Vdc, V _{BE} = 0, T _C = 25°C)	I _{CES}	_	_	10	mAdc

(continued)








ELECTRICAL CHARACTERISTICS — continued ($T_C = 25^{\circ}C$ unless otherwise noted.)

Characteristic	Symbol	Min	Тур	Max	Unit
ON CHARACTERISTICS			•	•	
DC Current Gain (I _C = 2.0 Adc, V _{CE} = 5.0 Vdc)	h _{FE}	20	50	150	_
DYNAMIC CHARACTERISTICS			•	•	
Output Capacitance (1) (V _{CB} = 24 Vdc, I _E = 0, f = 1.0 MHz)	C _{ob}	_	60	_	pF
FUNCTIONAL TESTS			•	•	
Common–Base Amplifier Power Gain (V _{CC} = 24 Vdc, P _{out} = 60 W, f = 900 MHz)	G _{pb}	7.0	7.9	_	dB
Collector Efficiency (V _{CC} = 24 Vdc, P _{out} = 60 W, f = 900 MHz)	η	60	65	_	%
Output Mismatch Stress (V _{CC} = 24 Vdc, P _{out} = 60 W, f = 900 MHz, VSWR = 5:1, all phase angles)	Ψ	No Degradation in Output Power			

NOTE:

1. Value of "Cob" is that of die only. It is not measurable in MRF898 because of internal matching network.



B1, B2, B3 — Bead, Ferroxcube 56-390-65/3B

C1, C2, C12 - 39 pF, 100 Mil Chip Capacitor

C3, C11 — 91 pF, Mini Underwood or Equivalent

C4, C7, C9 — 10 µF, 35 V Electrolytic

C5 — 4000 pF, 1.0 kV Ceramic

C6, C10 — 1000 pF, 350 V Unelco or Equivalent

C8 — 47 pF, 100 Mil Chip Capacitor

L1, L4 — 4 Turns #18 AWG Choke

L2 — 11 Turns #20 AWG Choke on 10 Ohm, 1.0 Watt Resistor

L3 — 3 Turns #18 AWG Choke on 10 Ohm, 1.0 Watt Resistor

TL1, TL6 — 50 Ohm Microstrip

TL2 — 400 x 950 Mils

TL3, TL4 — 140 x 200 Mils

TL5 - 320 x 690 Mils

TL7 — 260 x 230 Mils

Board — 3M Epsilam-10, 50 Mil

Bias Boards — 1/32" G10 or Equivalent

Figure 1. 850-960 MHz Broadband Test Circuit



ARCHIVE INFORMATION





Figure 2. Output Power versus Input Power

Figure 3. Output Power versus Frequency






Figure 4. Output Power versus Supply Voltage

Figure 5. Typical Broadband Circuit Performance





Figure 6. Input/Output Impedance versus Frequency

MOTOROLA RF DEVICE DATA MRF898



PACKAGE DIMENSIONS



Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters can and do vary in different applications. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights nor the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part. Motorola and All opportunity/Affirmative Action Employer.

Literature Distribution Centers:

USA: Motorola Literature Distribution; P.O. Box 20912; Phoenix, Arizona 85036.

EUROPE: Motorola Ltd.; European Literature Centre; 88 Tanners Drive, Blakelands, Milton Keynes, MK14 5BP, England.

JAPAN: Nippon Motorola Ltd.; 4-32-1, Nishi-Gotanda, Shinagawa-ku, Tokyo 141, Japan.

ASIA PACIFIC: Motorola Semiconductors H.K. Ltd.; Silicon Harbour Center, No. 2 Dai King Street, Tai Po Industrial Estate, Tai Po, N.T., Hong Kong.

