

## Motorola Semiconductor Engineering Bulletin

EB273

# Which Pins on the MC68331/332 and MC68HC16Z1 Need Pullup Resistors

By Christopher Hale Austin, Texas

### **General Information**

These pins should use a 10-k $\Omega$  resistor to five volts:

- BR/CS0 To prevent unexpected bus request
- BERR The bus error signal (BERR) is asserted in the absence of DSACK to indicate a bus error condition. The pullup resistor prevents unexpected assertion of bus error.
- HALT To prevent erroneous bus halt
- IRQ[1:7] To prevent erroneous interrupt requests
- DSACK0, DSACK1 During normal bus transfer, external devices assert the data and size acknowledge signals DSACK1 and DSACK0 to indicate port width to the MC68HC16. The pullups prevent accidental assertion of DSACK[0:1] during reset.
- AVEC The autovector signal AVEC can be used to terminate external interrupt acknowledge cycles. Assertion of AVEC causes the MC68HC16 to generate vector numbers to locate an interrupt handler routine. The pullup prevents unexpected assertion of the AVEC pin.
- TSTME/TSC The test mode is entered if the signal line TSTME is held low and if the enter test mode bit in one of the special test registers is written. The pullup prevents the M68HC16 from

EB273



Freescale Semiconductor, Inc.

© Motorola, Inc., 1998

For More Information On This Product, Go to: www.freescale.com



### **Engineering Bulletin**

enabling test mode. However, test mode could be entered only if the software became corrupted and accidentally wrote the special test register. Consult your user's manual for what to do with this pin if you have anything other than a 68331, 68332, or 68HC16Z1.

#### **NOTE:** This pin behaves differently for other MCUs.

- R/W To prevent accidental writes to memory during reset
- MODCLK If using the internal PLL to generate the system clock, this pin must be pulled up or driven high during reset. If using an external clock source and bypassing the PLL, connect this pin to ground or drive it low during reset. PCLK, PAI should be pulled up with 10 k on MCUs with a GPT.
- RESET The reset pullup resistor should be 820. If RESET does not rise within 10 system clocks, the MCU will re-drive reset and it will get stuck in this state.
- BKPT/DSCLK Put a 4.7-k pullup resistor on this pin. Background debug mode operation is enabled when BKPT is asserted at the rising edge of the RESET signal. BDM remains enabled until the next system reset. If BKPT is at a logic level 1 on the trailing edge of RESET, BDM is disabled. BKPT is relatched on each rising transition of RESET. BKPT is synchronized internally, and must be asserted for at least two clock cycles prior to negation of RESET. A pullup resistor will ensure that the BDM is not unexpectedly enabled upon reset.

Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Motorola data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights or the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death mascciated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part. Motorola and ( $\widehat{M}$ ) are registered trademarks of Motorola, Inc. Motorola, Inc. is an Equal Opportunity/Affirmative Action Employer.

#### How to reach us:

USA/EUROPE/Locations Not Listed: Motorola Literature Distribution, P.O. Box 5405, Denver, Colorado 80217, 1-800-441-2447 or 1-303-675-2140. Customer Focus Center, 1-800-521-6274

JAPAN: Nippon Motorola Ltd.: SPD, Strategic Planning Office, 141, 4-32-1 Nishi-Gotanda, Shinagawa-ku, Tokyo, Japan. 03-5487-8488 ASIA/PACIFIC: Motorola Semiconductors H.K. Ltd., 8B Tai Ping Industrial Park, 51 Ting Kok Road, Tai Po, N.T., Hong Kong. 852-26629298 Mfax™, Motorola Fax Back System: RMFAX0@email.sps.mot.com; http://sps.motorola.com/mfax/;

TOUCHTONE, 1-602-244-6609; US and Canada ONLY, 1-800-774-1848

HOME PAGE: http://motorola.com/sps/



Mfax is a trademark of Motorola, Inc.

© Motorola, Inc., 1998