

Motorola Semiconductor Engineering Bulletin

EB369

In-Circuit Programming of FLASH Memory Using the Monitor Mode for the MC68HC908KX2/8

By Timothy J. Airaudi
Applications Engineering, Microcontroller Division
Austin, Texas

Introduction

This engineering bulletin describes how to perform in-circuit programming (ICP) of the FLASH memory using monitor mode.

Two methods are discussed here:

- Using the M68ICS08KX in-circuit simulator (ICS) with P&E Microsystems software.
- Using P&E Microsystems software with an external communications circuit

ICP is a process where user code is programmed into the device's FLASH memory after the part has been assembled into the application. ICP also allows the original users code to be erased and re-programmed. This method can be used in development, production/manufacturing, and in a field environment.



Using Monitor Mode for FLASH Programming

Motorola's current solution for ICP is the in-circuit simulators and P&E's software.

The software and ICS allow programming of the parts on the simulator or in the target circuit via a MON08 ribbon cable. The software also allows programming of the part, without the ICS, with an external communications circuit.

All the programming described here is accomplished by placing the part into monitor mode. In this mode, erasing and programming are accomplished through a single-wire interface with the host computer.

Two ways to enter monitor mode are:

- The ICS provides the entry requirements to enter standard monitor mode. These entry requirements must be implemented on the target board if the ICS is not used.
- A second way to enter monitor mode, that does not require a high voltage on the $\overline{\text{IRQ}}$ pin, is forced monitor mode. This mode does not need to meet all the monitor mode entry conditions of the standard monitor mode, but it does require the part to be blank (erased).

This engineering bulletin describes how to connect the part, communicate at different baud rates, place the part into monitor mode, pass security, and erase and program the part. If the security code is not known, the contents of the FLASH can't be read, but the FLASH can be erased and reprogrammed.

Information on the M68ICS08KX can be found at <http://mcu.motsps.com>. P&E Microsystems software can be downloaded free from that company's Web site.

NOTE: *All of the oscillators used in this engineering bulletin are the 4-pin "powered" or "canned" type oscillators. Discussing all the different vendors of crystals, ceramic oscillators, other required external components, and component layout variables would be too extensive.*

**ICP Using
 M68ICS08KX's
 MON08 Interface**

Use this procedure for performing ICP using the ICS's MON08 cable to the target application.

1. Materials required:
 - a. PC with P&E software installed
 - b. M68ICS08KX simulator
 - c. Adapter/connector to connect the female end of the MON08 cable to the part on the target application
 - d. Pin assignment diagram (see [Figure 1](#))
 - e. Monitor mode entry requirements (see [Table 1](#))
 - f. Crystal oscillator on the target or from an external clock source with a value from [Table 2](#)
 - g. Target board must have the ability to perform a power-on reset (POR) not just a reset (required to enter monitor mode).
2. Connections (see [Figure 2](#)):
 - a. 9-pin serial cable from PC to the ICS
 - b. 5 volts to the ICS
 - c. MON08 cable from J4 of the ICS to the target board with these connections:
 - MON08 GND to the V_{SS} pin on the part
 - MON08 RST to the \overline{RST} pin on the part
 - MON08 IRQ to the \overline{IRQ} pin on the part
 - MON08 PTA0 to the PTA0 pin on the part
 - MON08 PTA1 to the PTA1 pin on the part
 - MON08 PTB0 to the PTB0 pin on the part
 - MON08 PTB1 to the PTB1 pin on the part
3. Operation — Standard monitor mode entry:
 - a. Launch P&E's WINIDE in the ICS08KXZ software.
 - b. Open desired file. (Demo file can be used.)
 - c. Assemble/Compile the file (see [Figure 5](#)).

- d. Plug in power to the ICS.
 - e. Turn on power to the target.
 - f. Launch the programmer.
 - g. From “Target Hardware Type,” select “Class II” (see [Figure 6](#)).
 - h. From “PC Serial Port Configuration,” select the PC port you are using and the appropriate baud rate (see [Table 2](#)).
 - i. From “Target MCU Security Bytes,” select appropriate security code (blank part = FF).
 - j. Select “Contact Target with these Settings...”
 - k. Follow the instructions in the “Power Down/Up Dialog” windows.
 - l. Select appropriate algorithm for the part being used.
 - m. Double click on “Erase Module” – EM (see [Figure 7](#)).
 - n. Double click on “Program Module” – PM.
 - o. Record security bytes. This information can be seen by quitting and then re-entering the programmer. The S19 record will have the same security bytes as the part just programmed as long as it is not changed. The security bytes consist of the information stored in the interrupt vectors, \$FFF6–\$FFFD.
4. Operation — Forced monitor mode entry:
- a. Blank part with an oscillator value from [Table 2](#)
 - b. Remove connection from the MON08 to the $\overline{\text{IRQ}}$ pin.
 - c. $\overline{\text{IRQ}}$ has an internal pullup.
 - d. PTB0 and PTB1 are not required.

**ICP Using
 the External
 Communications
 Circuit (No ICS)**

Use this procedure for performing ICP via an external communications circuit in place of this ICS to the target application.

1. Materials required:
 - a. PC with P&E software installed
 - b. Adapter/connector to connect the male end of the 9-pin serial cable to the part on the target application
 - c. RS-232 communications circuit. Also needed is a 5-volt power source to power this circuit. (see [Figure 3](#) and [Figure 4](#))
 - d. Pin assignment diagram (see [Figure 1](#))
 - e. Monitor mode entry requirements (see [Table 1](#))
 - f. Crystal oscillator on the target or from an external clock source with a value from [Table 2](#)
 - g. Target board must have the ability to perform a POR not just a reset (required to enter monitor mode).
2. Connections (see [Figure 3](#)):
 - a. 9-pin serial cable from PC to the communications circuit
 - b. V+ pin of the RS-232 part to the $\overline{\text{IRQ}}$ pin of the part
 - c. Communications pin of 'HC125 to PTA0 of the part
 - d. Target pin requirements:
 - PTA1 of part to V_{SS}
 - PTB0 of the part to V_{DD} via pullup resistor
 - PTB1 of the part to V_{SS}
 - RESET to V_{DD} via pullup resistor
3. Operation — Standard monitor mode entry:
 - a. Launch P&E's WINIDE in the ICS08KX software.
 - b. Open desired file. (Demo file can be used.)
 - c. Assemble/Compile the file (see [Figure 5](#)).
 - d. Apply power to the communications circuit.
 - e. Turn on power to the target.

- f. Launch the programmer.
 - g. From “Target Hardware Type,” select “Class III” (see [Figure 6](#)).
 - h. From “PC Serial Port Configuration,” select the PC port in use and the appropriate baud rate (see [Table 2](#)).
 - i. From “Target MCU Security Bytes,” select appropriate security code (blank part = FF).
 - j. Select “Contact Target with these Settings...”
 - k. Follow the instructions in the “Power Cycle Dialog” window.
 - l. Select appropriate algorithm for the part being used.
 - m. Double click on “Erase Module” – EM (see [Figure 7](#)).
 - n. Double click on “Program Module” – PM.
 - o. Record security bytes. This information can be seen by quitting and re-entering the programmer. The S19 record will have the same security bytes as the part just programmed as long as it is not changed. The security bytes consist of the information stored in the interrupt vectors, \$FFF6– \$FFFD.
4. Operation — Forced monitor mode entry:
- a. Blank part with oscillator from [Table 2](#). See [Figure 4](#).
 - Remove the connection to the $\overline{\text{IRQ}}$ pin of the part.
 - $\overline{\text{IRQ}}$ has an internal pullup resistor.
 - PTB0 and PTB1 are not required.




Figure 1. PDIP and SOIC Pin Assignments

Table 1. Monitor Mode Entry

| \$FFFE/ \$FFFF | $\overline{\text{IRQ1}}$ Pin | PTB1 Pin (PTXMOD1) | PTB0 Pin (PTXMOD0) | PTA1 Pin | PTA0 Pin | CGMOUT | Bus Frequency (f_{OP}) |
|-------------------|---------------------------------|-----------------------|-----------------------|-------------|-------------|----------------------------|----------------------------------|
| X | V_{TST} | 0 | 1 | 0 | 1 | $\frac{\text{CGMXCLK}}{2}$ | $\frac{\text{CGMOUT}}{2}$ |
| \$FF blank | V_{DD} | X | X | 0 | 1 | $\frac{\text{CGMXCLK}}{2}$ | $\frac{\text{CGMOUT}}{2}$ |

Table 2. Crystal Frequency vs. Baud Rate

| Crystal Frequency (MHz) | Internal Bus Frequency (MHz) | Baud Rate |
|----------------------------|---------------------------------|--------------|
| 4.9152 | 1.2288 | 4800 |
| 9.8304 | 2.4576 | 9600 |
| 14.7456 | 3.6864 | 14,400 |
| 19.6608 | 4.9152 | 19,200 |
| 29.4912 | 7.3728 | 28,800 |




Figure 2. MC68HC908KX2/8 MON08 Connections




Figure 3. MC68HC908KX2/8 Standard Monitor Mode (9.8304 MHz)




Figure 4. MC68HC908KX2/8 Forced Monitor Mode (9.8304 MHz)


```

WIN IDE - [HICBBOX.PHY] - [c:\projects\local\bin\ADEMDROCLASM]
File Edit Equipment Search Window Help

; Here is the sample application...

RAMStart EQU $0040
RomStart EQU $1000 ; This is valid ROM on the M3B
VectorStart EQU $FF0C
ADC_Channel EQU 2%
ADC_ENABLE_INT EQU 01000000% ; Bit mask for interrupt enable bit
; in the ADC status/control register

$include 'kregs.inc'

org RamStart

temp_long ds 4
temp_word ds 2
temp_byte ds 1
Timeout1 ds 1 ; Allows three timeout routines to be called each of which
Timeout2 ds 1 ; can run for up to ~ 1/2 second.
Timeout3 ds 1

org RomStart

*****
* Init_SCI - Turns on the asynchronous communications port *
* For "transmitting only" at 9600 baud NS1. *
*****
Init_SCI:
    mov #03,SC0R ; Baud Rate = 9600
    mov #40,SCC1 ; Enable the SCI peripheral
    mov #0B,SCC2 ; Enable the SCI transmitter
    rts

*****
* Init_AtoD - Sets up the AtoD clock * turns it on *
*****
Copy selected text to clipboard

```

Figure 5. P&E's WINIDE Window




Figure 6. P&E's Target and Security Window





Figure 7. P&E's Programmer Window

Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Motorola data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights nor the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part. Motorola and  are registered trademarks of Motorola, Inc. Motorola, Inc. is an Equal Opportunity/Affirmative Action Employer.

How to reach us:

USA/EUROPE/Locations Not Listed: Motorola Literature Distribution; P.O. Box 5405, Denver, Colorado 80217. 1-303-675-2140 or 1-800-441-2447

JAPAN: Motorola Japan Ltd.; SPS, Technical Information Center, 3-20-1, Minami-Azabu, Minato-ku, Tokyo 106-8573 Japan. 81-3-3440-3569

ASIA/PACIFIC: Motorola Semiconductors H.K. Ltd.; Silicon Harbour Centre, 2 Dai King Street, Tai Po Industrial Estate, Tai Po, N.T., Hong Kong.
852-26668334

Technical Information Center: 1-800-521-6274

HOME PAGE: <http://www.motorola.com/semiconductors/>


MOTOROLA

© Motorola, Inc., 2000

EB369/D

**For More Information On This Product,
Go to: www.freescale.com**