



i.MX applications  
processors

## Evaluation Kit Based on i.MX 6ULL Applications Processors

NXP delivers the next installment in a line of highly flexible, market-focused development tools with an evaluation kit (EVK) for i.MX 6ULL and i.MX 6ULZ applications processors.

The i.MX 6ULL/6ULZ processor is an extension of the popular i.MX 6 series, with a single Arm® Cortex®-A7 core running up to 900 MHz. This EVK enables an LCD display and audio playback as well as many connectivity options. It is designed to showcase the most commonly used features of the processor in a small, low-cost package and to facilitate software development with the ultimate goal of faster time-to-market through the support of the Linux® operating system.

### **EFFICIENT PERFORMANCE WITH LOW POWER AT A LOW BOM COST**

Leveraging the energy efficiency of the Cortex-A7 core, the i.MX 6ULL/6ULZ is the smallest and most energy-efficient processor built on Arm technology, providing maximum performance in low-power, space-constrained embedded environments. The board is powered by discrete power circuitry consisting of three DC-to-DC converters and one low dropout (LDO) regulator.

### **i.MX 6ULL EVK System Contents**


- ▶ i.MX 6ULL CPU board and base board

### **SENSORS**

The NXP FXLS8471Q accelerometer is highly versatile for industrial and consumer high-performance low-g applications that offer noise density, board mount offset, temperature performance and sensitivity. Integrated motion detection features include tilt, shake and tap detection with a new vector magnitude output that simplifies implementation and reduces power consumption. The NXP MAG3110 eCOMPASS is a small, low-power digital 3D magnetic sensor with a wide dynamic range to allow operation in PCBs with high extraneous magnetic fields. A footprint is also available to enable a gyroscope sensor.



## i.MX 6ULL EVK



## SOFTWARE AND TOOLS

Simplify product design with a low-cost, feature-rich development platform that allows you to work with the majority of the processor's primary features and the corresponding software support. For software, design files, development tools and additional information, visit [www.nxp.com/iMX6tools](http://www.nxp.com/iMX6tools).

## MCIMX6ULL-EVK FEATURES

CPU Board	
<b>Processor</b>	NXP i.MX 6ULL 900 MHz Arm Cortex®-A7 core, MCIMX6Y2DVM09AB
<b>Power management</b>	Discretes
<b>Memory</b>	<ul style="list-style-type: none"><li>• 4 GB DDR3L SDRAM, 400 MHz</li><li>• 256 MB Quad SPI flash</li><li>• MicroSD connector</li><li>• Footprint for eMMC</li><li>• Footprint for NAND flash</li></ul>
<b>Size</b>	2.66 inch x 1.27 inch (6.76 cm x 4.24 cm), 4-layer board
Base Board	
<b>Display board interface</b>	<ul style="list-style-type: none"><li>• LCD expansion port connector</li><li>• HDMI connector and footprint for HDMI transmitter</li></ul>
<b>Audio</b>	<ul style="list-style-type: none"><li>• Audio codec</li><li>• 3.5 mm stereo headphone output with MIC</li><li>• Mono-microphone input on board</li><li>• Left and right speaker out connectors</li></ul>
<b>Connectivity</b>	<ul style="list-style-type: none"><li>• One USB 2.0 Micro-B OTG connector</li><li>• One USB 2.0 Standard-A host connector</li><li>• Two Ethernet (10/100T) connectors</li><li>• Dual CAN connector</li><li>• SD/SDIO connector</li></ul>
<b>Camera</b>	Parallel camera connector
<b>Sensors</b>	<ul style="list-style-type: none"><li>• NXP MAG3110 eCOMPASS</li><li>• NXP FXLS8471Q accelerometer</li><li>• Footprint for gyroscope</li></ul>
<b>Debug</b>	<ul style="list-style-type: none"><li>• 20-pin standard JTAG connector</li><li>• UART to Micro USB connector</li></ul>
<b>Expansion port</b>	Arduino® header
<b>Size</b>	5.12 inch x 4.25 inch (13.0 cm x 10.8 cm), 4-layer board

[www.nxp.com/iMX6ULLEVK](http://www.nxp.com/iMX6ULLEVK) and [imxcommunity.org](http://imxcommunity.org)

NXP, the NXP logo, and the Energy Efficient Solutions logo are trademarks of NXP Semiconductors. All other product or service names are the property of their respective owners. Arm and Cortex are registered trademarks of Arm Limited (or its subsidiaries) in the EU and/or elsewhere. All rights reserved. © 2018 NXP B.V.

Document Number: EVKIMX6ULFS REV 3

