


MC9S12A512

Target Applications

- > Instrumentation
- > Energy management
- > Industrial control
- > Robotics
- > Safety equipment
- > Security

Overview

Freescale Semiconductor's MC9S12A512
Flash microcontroller (MCU) is the next
generation of the highly successful 68HC12
architecture. Using Freescale's industry-leading
0.25 µs Flash, the A512 is part of a
pin-compatible family that is planned to
scale from 32 KB to 512 KB of Flash memory.
The MC9S12A512 provides an upward
migration path from Freescale's 68HC08,
68HC11 and 68HC12 architectures for
applications that need larger memory, more
peripherals and higher performance.



Features	Benefits	
High-Performance 16-bit HCS12 CPU Core		
> 25 MHz bus operation at 5V for 40 ns minimum instruction cycle time	> Opcode compatible with the 68HC11 and 68HC12	
	> C-optimized architecture produces extremely compact code	
On-Chip Debug Interface		
Dedicated serial debug interfaceOn-chip breakpoints	 Real-time in-circuit emulation and debug without expensive and cumbersome box emulators 	
	> Read/write memory and registers while running at full speed	
Integrated Third-Generation Flash Memory		
> In-application reprogrammable	> Flexibility to change code in the field	
> Self-timed, fast programming	> Efficient end-of-line programming	
 Fast Flash page erase—20 ms (512 bytes) 	> Total program time for 512 KB code is less than 10 seconds	
 Can program 16 bits in 20 μs while in burst mode 	> Reduces production programming cost through ultra-fast programming	
> 5V Flash program/erase/read	> No external high voltage or charge pump	
> Flash granularity—512 byte Flash erase/2 byte Flash program	required > Virtual EEPROM implementation, Flash array	
> Four independently programmable Flash arrays	usable for EE extension > Can erase one array while executing code	
> Flexible block protection and security	from another	
4 KB Integrated EEPROM		
> Flexible protection scheme for protection against accidental program or erase	> Can erase 4 bytes at a time and program 2 bytes at a time for calibration, security,	
> EEPROM can be programmed in 46 μs	personality and diagnostic information	
10-bit Analog-to-Digital Converter (ADC)		
> Two, 8-channel ADCs	> Fast, easy conversion from analog inputs like position sensors, analog meters and photovoltaic cells to digital values for CPU processing	
> 7 μs , 10-bit single conversion time, scan mode available		
	> ADC run in parallel for a 7 μs conversion for two 10-bits or, in other words, 3.5 μs for 10-bits	





Benefits Clock Generation Module with Phase-Lock Loop (PLL) Clock monitor with limp home mode in case of > Reliable, robust operation no external clock > Provides high performance using low-cost > Programmable clock frequency with 1024 reference crystals options ranging from divide by 16 to multiply > Reduces generated noise by 64 form base oscillator > Reduces power consumption > Slow mode divider Easily able to implement real-time clock > Real-time interrupt > Watchdog **Enhanced Capture Timer** > 8-channel, 16-bit with input capture, output > Flexible, programmable timer system compare and pulse accumulator > 16-bit modulus down counter 8-bit or 16-bit Pulse-Wide Modulation (PWM) > 8-channel, 8-bit or 4-channel, 16-bit PWM > Efficiently implement motor control, battery charging or digital-to-analog (DAC) functions > PWM supports center-aligned operation **Two Serial Communications Interfaces** > Asynchronous communication between the MCU and a terminal, computer or a network of MCUs **Three Serial Peripheral Interfaces** > High-speed synchronous communication between multiple MCUs or between MCU and serial peripherals Inter IC (I2C) Bus > Provides a simple, efficient method of data exchange between devices > Minimizes the need for large numbers of connections between devices and eliminates the need for an address decoder Up to 91 Input/Output (I/O) Lines

Application	Notes	and	Engineering	Bulletins
-------------	-------	-----	-------------	-----------

> Programmable pull-ups/pull-downs

> Dual drive capability

Approacion Notes and Engineering Bancons				
	AN2206	Security and Protection on the HCS12 Family		
	AN2213	Using Cosmic Software's M68HC12 Compiler for MC9S12DP256 Software Development		
	AN2216	MC9S12DP256 Software Development Using Metrowerks CodeWarrior™		
	AN2250	Audio Reproduction on HCS12 Microcontrollers		
	EB386	HCS12 D-Family Compatibility		

> Reduce system cost

high current loads

> Able to tailor application for minimum EMC or

Data Sheets

9S12DP512DGV1 9S12DX512 Device Guide

S12BDMV4 HCS12 Background Debug (BDM)

Block Guide

S12BKVD1 HCS12 Breakpoint (BKP) Block Guide

S12CPUV2 HCS12 CPU Reference Manual

S12ATD10B8CV2 HCS12 10-bit, 8-Channel Analog to Digital Converter (ADC) Block Guide

HCS12 Byte Data Link Controller

S12BDLCV1 (BDLC) Block Guide

S12CRGV4 HCS12 Clocks and Reset Generator (CRG) Block

S12DP256PIMV3 9S12DP256 Port Integration

Module (PIM)

HCS12 16-bit, 8-Channel Enhanced Capture Timer (ECT) Block Guide S12ECT16B8CV1

HCS12 4K EEPROM Block Guide S12FFTS4KV2 S12FTS512K4V1 HCS12 512K Flash Block Guide

S12IICV2 HCS12 I2C Block Guide

S12INTV1 HCS12 Interrupt (INT) Block Guide HCS12 Multiplexed External Bus S12MEBIV3

Interface (MEBI) Block Guide

S12MMCV4 HCS12 Module Mapping Control (MMC)

S12PWM8B8CV1 HCS12 8-bit, 8-Channel Pulse Width

Modulator (PWM) Block Guide

S12SCIV2 HCS12 Serial Communications Interface (SCI) Block Guide

S12SPIV3 HSC12 Serial Peripheral Interface (SPI)

Block Guide

S12VREGV1 HCS12 Voltage Regulator Block Guide

Cost-Effective Development Tools

For more information on development tools, please refer to the Freescale Development Tool Selector Guide (SG1011).

\$495

M68KIT912DP256 Evaluation kit for development and evaluation of HCS12 application code that includes the M68EVB912DP256

and USBMULTILINKBDM

\$499

M68CYCLONEPRO HC08/HCS08/HC12/HCS12 stand-alone Flash programmer or in-circuit emulator, debugger, Flash programmer; USB, serial or Ethernet

interface options

USBMULTILINKBDM Universal HCS08/HCS12 in-circuit emulator, debugger, and Flash programmer; USB PC interface

CWX-H12-SE

Free

\$99

CodeWarrior™ Special Edition for HCS12 MCUs; includes integrated development environment (IDE), linker, debugger, unlimited assembler, Processor Expert™ auto-code generator,

full-chip simulation and limited C compiler

Package Options

Part Number MC9S12A512CPV

Package 112 I OFP 112-Lead LQFP

Temp. Range -40°C to +85°C

PV

Learn More: For more information about Freescale products, please visit www.freescale.com.

