

Processor Enablement

Cost-Effective MPC830x PowerQUICC II Pro Processor Evaluation Kit


Overview

The MPC830x evaluation kit (MPC830x-KIT) is a cost-optimized reference design board for Freescale's MPC8306/S and MPC8309 PowerQUICC II Pro processors, built on Power Architecture® technology. The kit consists of a carrier card and a system on module (SoM) representing each of the two processors.

The MPC830x-KIT can be customized per project and combined with off-the-shelf software for product development. The module components provide the tools, device drivers and additional features needed for embedded Linux® OS projects.

Target Applications

- · Network communication
- · Low-end printers
- · Factory or building automation
- IEEE® 1588 in test and measurement equipment and industrial automation
- Programmable logic controller
- Managed industrial router



Tools

- Linux target image builer (LTIB) is a tool framework used to manage, configure, extend and build Linux software elements to develop a u-boot boot loader, Linux target image and a root file system. LTIB runs on a personal computer with Linux OS.
- CodeWarrior Power Architecture 8.8 Service Pack 2
- NetComm Software for MPC830x Rev 1.0

Evaluation Kit Pricing		
MPC8306-KIT	MPC8309-KIT	
USD \$759	USD \$779	

MPC830x Reference Design Kit Contents

The MPC830x evaluation kit includes the following items:

- MPC830x SOM board
- MPC830x carrier card
- Two UART cables
- · Board support package
- Ethernet cable
- Power adaptor (12V-5A) and cable

Production quantity SoMs may be purchased from partner elnfochips at einfochips.com.





MPC830x PowerQUICC II Pro Processors on SoM			
	MPC8309	MPC8306	MPC8306S (Supported on the MPC8306-KIT)
Core	e300	e300	e300
I-Cache/D-Cache	16K/16K	16K/16K	16K/16K
Floating Point Unit	Yes	Yes	Yes
Core Frequency	266/333/400/417	133/200/266	133/200/266
QUICC Engine Subsystem	32-bit RISC	32-bit RISC	32-bit RISC
Memory Controller	16/32-bit DDR2 with ECC	16-bit DDR2	16-bit DDR2
Local Bus	8/16-bit up to 66 MHz	8/16-bit up to 66 MHz	8/16-bit up to 66 MHz
PCI Interface	32-bit up to 66 MHz	No	No
Ethernet	3 x 10/100 MII/RMII or 2 x 10/100 with IEEE 1588 V2	3 x 10/100 MII/RMII or 2 x 10/100 with IEEE 1588 V2	3 x 10/100 , MII/RMII
USB 2.0	Yes	Yes	Yes
UART	Yes (4 x)	Yes (4 x)	Yes (4 x)
l ² C Controller	Dual	Dual	Dual
SPI	Yes	Yes	Yes
Interrupt Controller	IPIC	IPIC	IPIC
IEEE® 1588 Support	Yes	Yes	No
eSDHC	Yes	Yes	No
FlexCAN	Yes	Yes	No
Package	489-pin MAPBGA	369-pin MAPBGA	369-pin MAPBGA

MPC830x Kit Features			
	MPC8306-KIT	MPC8309-KIT	
СРИ	MPC8306 PowerQUICC II Pro	MPC8309 PowerQUICC II Pro	
CPU Frequency Supported on SoM	133/266 MHz	266/333 MHz	
Memory Subsystem	128 MB DDR2 SDRAM	256 MB DDR2 SDRAM	
	8 MB NOR flash memory	8 MB NOR flash memory	
	512 MB NAND flash memory	512 MB NAND flash memory	
	256 KB serial EEPROM	256 KB serial EEPROM	
Ethernet	1 x 10/100 MII/RMII, 2 x 10/100 MII	3 x 10/100 MII/RMII	
USB 2.0	1	1	
eSDHC	1 (microSD)	1 (microSD)	
UART	2	2	
I ² C	2	2	
FlexCAN	1	1	
Connectors-SOM	3-pin power jack	3-pin power jack	
	3-pin UART header for console	3-pin UART header for console	
	JTAG/COP for debug	JTAG/COP for debug	
	120-pin and 140-pin board-to-board connector	120-pin and 140-pin board-to-board connector	
	6-pin BDM header for KA2 programming	6-pin BDM header for KA2 programming	
	RJ-45 for Ethernet	RJ-45 for Ethernet	
	microSD card	microSD card	
	6-pin header for boot device (NAND/NOR) selection	6-pin header for boot device (NAND/NOR) selection	
Connectors—Carrier Board	Dual stack DB9 connector for RS-232 console and RS-485	PCI card edge connector	
	RJ45 connector for T1/E1	Mini PCI card edge connector	
	RJ45 connector for FEC-3	Dual stack DB9 connector for RS-232 console and RS-485	
	MiniAB USB	RJ45 connector for T1/E1	
	Microcontroller UART header	RJ45 connector for FEC-3	
	Microcontroller BDM header	MiniAB USB	
	4-pin CAN header	Microcontroller UART header	
	RJ-11 for SLIC/PSTN phone interface	Microcontroller BDM header	
	60-pin local bus	4-pin CAN header	
	120-pin and 140-pin board-to-board connector	RJ-11 for SLIC/PSTN phone interface	
	16-pin SPI and IEEE® 1588 header	60-pin local bus	
	16-pin GPIO header	120-pin and 140-pin board-to-board connector	
		16-pin SPI and IEEE 1588 header	
		16-pin GPIO header	
Form Factor—SOM	90 mm x 70 mm	90 mm x 70 mm	
Form Factor - Carrier Board	170 mm x 170 mm	170 mm x 170 mm	
Certification	FCC Class A, CE	FCC Class A, CE	
RoHS	Yes	Yes	

Learn More:

For current information about Freescale products and documentation, please visit **freescale.com/PowerQUICC.**



