



# MM908E624

Integrated Triple High Side Switch with Embedded MCU and LIN Serial Communication for Relay Drivers


## **Applications**

- Automotive
- Robotics
- · DC Motor Control
- · Relay Driver Applications
- · Marine Systems

#### Overview

The 908E624 is an integrated single package solution that includes a high-performance HC08 microcontroller with a SMARTMOS analog control IC. The HC08 includes flash memory, a timer, enhanced serial communications interface (ESCI), an analog-to-digital converter (ADC), internal serial peripheral interface (SPI), and an internal clock generator module. The analog control die provides three high side outputs with diagnostic functions, voltage regulator, watchdog, current sense operational amplifier, and local interconnect network (LIN) physical layer.

The single-package solution, together with LIN, provides optimal application performance adjustments and space-saving PCB design. It is well-suited for the control of automotive high-current motors applications using relays (e.g., window lifts, fans, and sun roofs).



Performance	Typical Values	
Outputs	3 HS	
R <sub>DS(ON)</sub> @ 25 °C HS1 and HS2 HS3	2.5 W 7.0 W	
Operating Voltage	7.5 V to 20.0 V	
ESD	± 2000 V	
Ambient Operating Temperature	-40 °C ≤ T <sub>A</sub> ≤ 125 °C	
Junction Operating Temperature	$-40~^{\circ}\text{C} \le \text{T}_{\text{J}} \le 125~^{\circ}\text{C}$	





#### **Features**

- · High-performance M68HC908EY16 core
- · 16 KB of on-chip flash memory
- 512 B of RAM
- · Internal clock generator module
- · Two 16-bit, two-channel timers
- · 10-bit ADC
- · LIN physical layer interface
- · Low drop voltage regulator
- · Three high side outputs
- Two wake-up inputs
- Devices available for comparison are in the Analog Product Selector Guide - SG1002 and Automotive Product Selector Guide -SG187

## **Customer Benefits**

- Integrate microcontroller and analog features in the same package solution
- · Provide a full LIN node solution
- Easy control of high-current motors using relays and current recopy features
- Reduced space resulting in enhanced reliability
- Internal protection features provide full protection for output stages (with status reporting)
- Economical and autonomous multifunction solution with few external components
- · Two wake-up inputs for system use
- Low-power mode flexibility and wake-up options

## Questions


- Are you using a LIN communication system?
- Do you need a single package solution integrating a HC08 microcontroller, a LIN node, and motor drivers?
- Do you have to minimize the size of your PCB application?
- Do you need to control high-current motors?
- · Do you need to reduce system cost?

Ordering Information			
Device	Temperature Range	Package	
MM908E624ACPEW/R2	-40 to 85°C	54 SOICW	
MM908E624AYPEW/R2	-40 to 125°C		
Evaluation Board			
KIT908E624DWBEVB	Evaluation Board. Contact sa	Evaluation Board. Contact sales for kit availability.	
Documentation			
MM908E624	Data sheet order number	Data sheet order number	
SG1002	Analog Product Selector Gui	Analog Product Selector Guide	
SG 187	Automotive Product Selector	Automotive Product Selector Guide	

# 54 SOICW



**Learn More**: For current information about Freescale products, please visit **www.freescale.com**.



Document Number: MM908E624FS

REV 5.0

