



DETAIL "Y"



DETAIL "Y"

© NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE
TITLE: NI-880S-2 GULL A1 SPECIAL	DOCUMENT NO: 98ASA00194D	REV: B
	STANDARD: NON-JEDEC	
	SOT1803-1	05 FEB 2016



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M-1994.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION A1 IS MEASURED WITH REFERENCE TO DATUM T. THE POSITIVE VALUE IMPLIES THAT THE PACKAGE BOTTOM IS HIGHER THAN THE LEAD BOTTOM.

DIM	INCH		MILLIMETER		DIM	INCH		MILLIMETER	
	MIN	MAX	MIN	MAX		MIN	MAX	MIN	MAX
A	.905	– .915	22.99	– 23.24	t	0	– 8	0	– 8
A1	.002	– .008	0.05	– 0.20	aaa	– .007	–	– 0.18	–
B	.535	– .545	13.59	– 13.84	bbb	– .010	–	– 0.25	–
B1	.704	– .714	17.88	– 18.14	ccc	– .015	–	– 0.38	–
C	.147	– .200	3.73	– 5.08	–	–	–	–	–
D	.495	– .505	12.57	– 12.83	–	–	–	–	–
E	.035	– .045	0.89	– 1.14	–	–	–	–	–
F	.003	– .006	0.08	– 0.15	–	–	–	–	–
L	.038	– .046	0.97	– 1.17	–	–	–	–	–
L1	.01 BSC		0.25 BSC		–	–	–	–	–
M	.872	– .888	22.15	– 22.56	–	–	–	–	–
N	.871	– .889	22.12	– 22.58	–	–	–	–	–
R	.515	– .525	13.08	– 13.34	–	–	–	–	–
S	.515	– .525	13.08	– 13.34	–	–	–	–	–

© NXP SEMICONDUCTORS N.V.
ALL RIGHTS RESERVED

MECHANICAL OUTLINE

PRINT VERSION NOT TO SCALE

TITLE: NI-880S-2 GULL A1 SPECIAL	DOCUMENT NO: 98ASA00194D	REV: B
	STANDARD: NON-JEDEC	
	SOT1803-1	05 FEB 2016