



NOTES:

- 1. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M–1994.
- 2. CONTROLLING DIMENSION: INCH
- 3. DIMENSION H IS MEASURED .030 AWAY FROM PACKAGE BODY

STYLE 1:
PIN 1 – DRAIN
2 – DRAIN
3 – GATE
4 – GATE
5 – SOURCE

DIM	INCH		MILLIMETER		DIM	INCH		MILLIMETER	
	MIN	MAX	MIN	MAX		MIN	MAX	MIN	MAX
A	.885	.895	22.48	22.73	R	.395	.405	10.03	10.29
B	.380	.390	9.65	9.91	S	.394	.406	10.01	10.31
C	.180	.224	4.57	5.69					
D	.325	.335	8.26	8.51	bbb	.010		0.25	
E	.060	.070	1.52	1.78	ccc	.015		0.38	
F	.004	.006	0.10	0.15					
H	.097	.107	2.46	2.72					
K	.085	.115	2.16	2.92					
L	.425 BSC		10.80 BSC						
M	.852	.868	21.64	22.05					
N	.851	.869	21.62	22.07					
© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.				MECHANICAL OUTLINE			PRINT VERSION NOT TO SCALE		
TITLE: NI–860 SURFACE MOUNT					DOCUMENT NO: 98ARH99095A				REV: C
					CASE NUMBER: 375H–03				04 AUG 2005
					STANDARD: NON–JEDEC				