



© NXP SEMICONDUCTORS N. V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE
TITLE: NI-880XS-2 GULL	DOCUMENT NO: 98ASA00456D REV: A	
	STANDARD: NON-JEDEC	
	SOT1804-2	08 FEB 2016



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M-1994.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION A1 IS MEASURED WITH REFERENCE TO DATUM T. THE POSITIVE VALUE IMPLIES THAT THE PACKAGE BOTTOM IS HIGHER THAN THE LEAD BOTTOM.

DIM	INCH		MILLIMETER		DIM	INCH		MILLIMETER	
	MIN	MAX	MIN	MAX		MIN	MAX	MIN	MAX
A	.905	– .915	22.99	– 23.24	U	R.000	– R.040	R0.00	– R1.02
A1	.000	– .010	0.00	– 0.25	Z	–	– .030	–	– 0.76
B	.380	– .390	9.65	– 9.91	t	0	– 8	0	– 8
B1	.549	– .559	13.94	– 14.20					
C	.125	– .170	3.18	– 4.32					
D	.595	– .605	15.11	– 15.37	aaa	–	.005	–	– 0.127
E	.035	– .045	0.89	– 1.14	bbb	–	.010	–	– 0.254
F	.003	– .006	0.08	– 0.15	ccc	–	.015	–	– 0.381
L	.038	– .046	0.97	– 1.17	–	–	–	–	–
L1	.01 BSC		0.25 BSC		–	–	–	–	–
M	.872	– .888	22.15	– 22.56	–	–	–	–	–
N	.871	– .889	22.12	– 22.58	–	–	–	–	–
R	.365	– .375	9.27	– 9.53					
S	.365	– .375	9.27	– 9.53					

© NXP SEMICONDUCTORS N.V.
ALL RIGHTS RESERVED

MECHANICAL OUTLINE

PRINT VERSION NOT TO SCALE

TITLE:

NI-880XS-2 GULL

DOCUMENT NO: 98ASA00456D

REV: A

STANDARD: NON-JEDEC

SOT1804-2

08 FEB 2016