




- NOTES:
- 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 - 2. CONTROLLING DIMENSION: INCH.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.355	0.365	9.02	9.27
B	0.225	0.235	5.72	5.96
C	0.110	0.125	2.80	3.17
D	0.115	0.125	2.93	3.17
F	0.075	0.085	1.91	2.15
H	0.035	0.045	0.89	1.14
J	0.004	0.006	0.11	0.15
K	0.090	0.110	2.29	2.79

- STYLE 1:

 - PIN 1. BASE (COMMON)
 - 2. EMITTER (INPUT)
 - 3. BASE (COMMON)
 - 4. BASE (COMMON)
 - 5. COLLECTOR (OUTPUT)
 - 6. BASE (COMMON)
- STYLE 2:

 - PIN 1. EMITTER
 - 2. BASE
 - 3. EMITTER
 - 4. EMITTER
 - 5. COLLECTOR
 - 6. EMITTER