



TOP VIEW



SIDE VIEW



BOTTOM VIEW

© NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED	<b>MECHANICAL OUTLINE</b>	<b>PRINT VERSION NOT TO SCALE</b>
<b>TITLE:</b> 121 I/O, LOW PROFILE, FINE PITCH, PBGA, 10 X 10 PKG, 0.8MM PITCH (HYBRID MAP)	DOCUMENT NO: 98ASA10527D	REV: D
	STANDARD: JEDEC	
	SOT1560-1	22 MAR 2016



NOTES:

1. ALL DIMENSIONS IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
3. MAXIMUM SOLDER BALL DIAMETER MEASURED PARALLEL TO DATUM A.
4. DATUM A, THE SEATING PLANE, IS DETERMINED BY THE SPHERICAL CROWNS OF THE SOLDER BALLS.
5. PARALLELISM MEASUREMENT SHALL EXCLUDE ANY EFFECT OF MARK ON TOP SURFACE OF PACKAGE.

© NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED	<b>MECHANICAL OUTLINE</b>	PRINT VERSION NOT TO SCALE	
TITLE: 121 I/O, LOW PROFILE, FINE PITCH, PBGA, 10 X 10 PKG, 0.8MM PITCH (HYBRID MAP)		DOCUMENT NO: 98ASA10527D	REV: D
		STANDARD: JEDEC	
		SOT1560-1	10 MAR 2016