



DIM	MILLIMETERS		DIM	MILLIMETERS		NOTES:	
	MIN	MAX		MIN	MAX		
A	29.08	29.85	N	10.67	11.18		1. DIMENSIONS ARE IN MILLIMETERS. 2. DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994. 3. STYLE 1: PIN 1: GROUND 2: + OUTPUT 3: + SUPPLY 4: - OUTPUT
B	17.40	18.16	P	∅3.89	∅4.04		
C	10.29	11.05	Q	∅3.89	∅4.04		
D	0.41	0.51	R	1.60	2.11		
F	1.22	1.63	S	5.59	6.10		
G	2.54 BSC		U	23.11 BSC			
H	∅4.62	∅4.93	V	6.30	7.06		
J	0.36	0.41	W	7.89	8.38		
K	17.65	18.42					
L	7.37	7.62					

© NXP SEMICONDUCTORS N.V.
ALL RIGHTS RESERVED

MECHANICAL OUTLINE

PRINT VERSION NOT TO SCALE

TITLE:

SENSOR, 4 LEAD UNIBODY

DOCUMENT NO: 98ASB14912C

REV: E

STANDARD: NON-JEDEC

SOT1754-1

18 JAN 2016