



DIM	MILLIMETERS		DIM	MILLIMETERS		NOTES:	
	MIN	MAX		MIN	MAX		
A	29.08	29.85	P	Ø3.89	Ø4.04		1. DIMENSIONS ARE IN MILLIMETERS. 2. DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994. 3. 867C-01 THRU -04 OBSOLETE, NEW STANDARD 867C-05. 3. STYLE 1: PIN 1: V OUT                      5: V2 2: GROUND                6: V EX 3: VCC 4: V1
B	17.40	18.16	Q	Ø3.89	Ø4.04		
C	10.29	11.05	R	1.60	2.11		
D	0.68	0.84	S	5.59	6.10		
F	1.22	1.63	U	23.11	BSC		
G	2.54 BSC		V	4.62	4.93		
J	0.36	0.41	W	7.87	8.38		
K	17.65	18.42	X	6.30	7.06		
L	7.37	7.62					
N	10.67	11.18					

© NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED		<b>MECHANICAL OUTLINE</b>		PRINT VERSION NOT TO SCALE	
TITLE:  SENSOR, 4 LEAD UNIBODY			DOCUMENT NO: 98ASB42797B		REV: H
			STANDARD: NON-JEDEC		
			SOT1756-1		29 JAN 2016