

SOT1919-1

LFBGA157, low profile, fine-pitch ball grid array package, 157 terminals, 0.5 mm pitch, 8 mm x 8 mm x 1.25 mm body

1 July 2020

Package information

1 Package summary

Terminal position code	B (bottom)
Package type descriptive code	LFBGA157
Package style descriptive code	LFBGA (low profile fine-pitch ball grid array)
Mounting method type	S (surface mount)
Issue date	12-06-2017
Manufacturer package code	98ASA01073D

Table 1. Package summary

Parameter	Min	Nom	Max	Unit
package length	7.85	8	8.15	mm
package width	7.85	8	8.15	mm
package height	1.24	1.25	1.26	mm
nominal pitch	-	0.5	-	mm
actual quantity of termination	-	157	-	



LFBGA157, low profile, fine-pitch ball grid array package, 157 terminals, 0.5 mm pitch, 8 mm x 8 mm x 1.25 mm body

2 Package outline




Figure 1. Package outline LFBGA157 (SOT1919-1)

LFBGA157, low profile, fine-pitch ball grid array package, 157 terminals, 0.5 mm pitch, 8 mm x 8 mm x 1.25 mm body

NOTES:

1. ALL DIMENSIONS IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
3. MAXIMUM SOLDER BALL DIAMETER MEASURED PARALLEL TO DATUM A.
4. PARALLELISM MEASUREMENT SHALL EXCLUDE ANY EFFECT OF MARK ON TOP SURFACE OF PACKAGE.
5. MAXIMUM SOLDER BUMP SHAPE MEASURED PARALLEL TO DATUM A.
6. ALL DIMENSIONS ARE SYMMETRIC ACROSS THE PACKAGE CENTER LINES, UNLESS DIMENSIONED OTHERWISE.

© NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE
TITLE: FCPBGA, MOLDED ARRAY, 8 X 8 X 1.25 PKG, 0.5 MM PITCH, 157 I/O	DOCUMENT NO: 98ASA01073D	REV: A
	STANDARD: NON-JEDEC	
	SOT1919-1	12 JUN 2017

Figure 2. Package outline note LFBGA157 (SOT1919-1)

3 Legal information

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

LFBGA157, low profile, fine-pitch ball grid array package, 157 terminals, 0.5 mm pitch, 8 mm x 8 mm x 1.25 mm body

Contents

1 Package summary1
2 Package outline2
3 Legal information4