



Information Brief



Freescale Semiconductor, Inc.
 ARCHIVED BY FREESCALE SEMICONDUCTOR, INC. 2005

First Fully Monolithic RF Cascode IC Amplifiers

Off-chip matching maximizes flexibility

The MRFIC0915 and MRFIC0916 are cost-effective, high isolation cascode amplifiers that operate at frequencies ranging from 100 MHz to 2.5 GHz. These unique silicon monolithic ICs are available in the industry standard SOT-143 miniature surface mount package, saving significant printed circuit board space in a wide variety of applications. Both devices have on-chip bias circuitry that sets the bias point, while off-chip matching maximizes design flexibility and efficiency.

The MRFIC0915 is a lower bias current (2.5 mA) version of the MRFIC0916, which has a bias current of 5.6 mA at a supply voltage of 2.7 V. The higher current MRFIC0916 offers improved specifications for Small Signal Gain, Reverse Isolation, and Output Power. These integrated cascode amplifiers are ideal for Voltage Controlled Oscillators (VCOs), buffer amplifiers, Low Noise Amplifiers (LNAs), mixers, and IF amplifiers in RF end products.

**For More Information On This Product,
 Go to: www.freescale.com**

FEATURES

COMMON SPECIFICATIONS

- Usable frequency range of 100 MHz to 2.5 GHz
- On-chip bias circuitry sets bias point
- Supply voltage from 2.7 to 5.0 V
- Noise figure of 1.9 dB at 850 MHz

SPECIFICATION DIFFERENCES

	MRFIC0915	MRFIC0916
• Bias Current ($V_{CC} = 2.7\text{ V}$)	2.5 mA	5.6 mA
• Small Signal Gain ($V_{CC} = 2.7\text{ V}$; $f = 850\text{ MHz}$)	16.2 dB	18.5 dB
• P_{out} @ 1 dB Gain Comp. ($V_{CC} = 2.7\text{ V}$; $f = 850\text{ MHz}$)	-4.6 dBm	2.3 dBm
• Reverse Isolation ($f = 850\text{ MHz}$)	38 dB	44 dB

TYPES OF APPLICATIONS

These integrated cascode amplifiers are ideal for use in any RF product that operates between 100 MHz and 2.5 GHz, and may be applied in:

- Voltage Controlled Oscillators (VCOs)
- Buffer Amplifiers
- Low Noise Amplifiers (LNAs)
- Mixers
- IF Amplifiers

BENEFITS TO YOU

- Higher circuit and system density with miniature surface mount package.
- Inherent excellent RF signal isolation with 38 to 44 dB of Reverse Isolation at 850 MHz.
- Simplified design with an integrated cascode amplifier in a single package.
- Lower system cost and manufacturing costs due to integrated, on-chip bias circuitry.
- Can be used in three-cell battery-powered applications with a power supply voltage as low as 2.7 V.
- Maximized design flexibility and efficiency with off-chip matching.
- Smaller battery for portable applications with 2.7 V operation.

A SOLUTION FOR THESE QUESTIONS

- Do you need to use one or more cascode amplifiers in your design to enhance the RF signal isolation in your wireless or RF product?
- Do you want to reduce the pc board area for your portable RF product?
- Do you need more isolation between your VCO and mixer?
- Does your design require that the battery size be reduced with a supply voltage as low as 2.7 V?
- Do you want to reduce the parts count and lower your manufacturing costs by using an integrated cascode amplifier with on-chip bias circuitry?
- Would you like to improve your design flexibility by customizing the matching for your cascode amplifier in VCO, buffer amplifier, LNA, IF amplifier and/or mixer designs?

LITERATURE


Complete data sheets containing full specifications, characteristic curves, S-parameters, typical noise parameters, and application circuit configurations are available through Motorola's LDC as MRFIC0915/D and MRFIC0916/D. Alternately, call Mfax at 602/244-6609 and key-in MRFIC0915 and/or MRFIC0916.

ORDERING INFORMATION

Device	Operating	
	Temperature Range	Package
MRFIC0915T1	T _C = -35°C to +100°C	SOT-143
MRFIC0916T1		Tape and Reel*

*(3,000 units per 8 mm, 7 inch reel)



Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters can and do vary in different applications. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights nor the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part. Motorola and  are registered trademarks of Motorola, Inc. Motorola, Inc. is an Equal Opportunity/Affirmative Action Employer.

How to reach us:

USA/EUROPE/Locations Unlisted: Motorola Literature Distribution;
 P.O. Box 5405; Denver, CO. 80217 or call 1-800-441-2447

JAPAN: Nippon Motorola Ltd.: SPD, Strategic Planning Office 4-32-1,
 Nishi-Gotanda, Shinagawa-ku, Tokyo 141, Japan. 81-3-5487-8488

Customer Focus Center: 1-800-521-6274

ASIA/PACIFIC: Motorola Semiconductors H.K. Ltd.;
 8B Tai Ping Industrial Park, 51 Ting Kok Road, Tai Po, N.T.,
 Hong Kong. 852-26629298

Mfax™: RMFAX0@email.sps.mot.com – TOUCHTONE 1-602-244-6609
 Motorola Fax Back System US & Canada Only 1-800-774-1848
<http://sps.motorola.com/mfax/>

Mfax is a trademark of Motorola, Inc.

Home Page: <http://motorola.com/sps/>
Wireless Page: motorola.com/wireless-semi