

Building on more than 11 years of innovation leadership, the LPC microcontroller portfolio has expanded to more than 400 32-bit devices covering every application class, from entry-level designs to high-end systems that run Linux® OS. This selection guide is a starting point for choosing a specific device. For the latest product information, visit www.nxp.com/LPC.

LPC Series MCUs

Series	CPU	Memory	Key Features		Applications
LPC800 Entry-level, 8-bit alternate	Arm® Cortex® -M0+ Up to 30 MHz	16-64 KB Flash 1-16 KB RAM	SCTimer/PWM Switch matrix Pattern match engine		Sensor gateways Battery-powered devices 8/16-bit replacements
LPC1100 Integrated connectivity	Cortex-M0/M0+ 50 MHz	4-256 KB Flash 1-36 KB RAM	USB CAN EEPROM		Gaming and PC peripherals Remote sensors System supervisors Alarm/lighting systems
LPC51U68 High-Performance and Power-Efficient	Cortex-M0+ 100MHz	256 KB flash Up to 96 KB total SRAM	Crystal-less FS USB combined with 8 Flexcomm interfaces Supports SMBus (System Management Bus) Power-efficient 5.0 Msps, 12-bit ADC: full-spec performance (1.62 to 3.6V, -40 to 105 °C) 12/48/96 MHz FRO, 100 kHz-1.5MHz WDOG OSC, 32 Xtal OSC, external clock input Basic & advanced timers including SCTimer/PWM		High performance gaming keyboard/mice Industrial grade USB to serial port bridge E-meter Fingerprint recognition USB audio device Sensor hub with USB interface Entry-level mobile POS
LPC54000 Mainstream, power efficiency	Cortex-M4* 100 MHz 180 MHz 220 MHz *Dual-core options available	128-512 KB Flash Up to 200 KB RAM	USB Digital mic interface CAN/CAN-FD LCD controller	Ethernet FlexComm Security	Smart home and building automation Auto-aftermarket w/ CAN FD Industrial control Gaming accessories
LPC1200 Noise immunity	Cortex-M0 50 MHz	32-128 KB Flash 4-8 KB RAM	8 kV protection IEC 60730 Class B certified		White goods Industrial control UPS/power conversion
LPC1300 Entry-level upgrade	Cortex-M3 72 MHz	8-64 KB Flash 4-12 KB RAM	USB		Consumer peripherals and toys Home automation
LPC1500 Motion control	Cortex-M3 72 MHz	64-256 KB Flash 12-36 KB RAM	USB CAN QEI		Motor control Digital power supplies Solar inverters
LPC1700 Scalable, mainstream	Cortex-M3 Up to 120 MHz	32-512 KB Flash 8-96 KB RAM	USB CAN Ethernet	LCD QEI	Smart energy Data collectors Auto-aftermarket Industrial controls and networking Medical diagnostics
LPC1800 Performance and integration	Cortex-M3 180 MHz	Up to 1024 KB Flash* 104-200 KB RAM *Flashless option available	Dual HS USB CAN Ethernet	LCD Security	Secure industrial gateways Data collectors Portable medical equipment Consumer audio applications
LPC4000 Scalable, mainstream	Cortex-M4 120 MHz	64-512 KB Flash 24-96 KB RAM	USB CAN	Ethernet LCD	Rich display HMI Medical diagnostics HVAC and building control
LPC4300 High performance and integration	Cortex-M4* 204 MHz *Multi-core options available	Up to 1024 KB Flash* 104-282 KB RAM *Flashless option available	Dual HS USB CAN Ethernet	LCD SGPIO Security	High-fidelity embedded audio Secure communication hubs Data collectors Scanners and printers



Discover the difference

MCUXpresso Software and Tools

NXP's MCUXpresso software and tools offer comprehensive development solutions designed to optimize, ease and accelerate embedded system development of applications based on Arm® Cortex®-M core devices, including Kinetis and LPC microcontrollers.



MCUXpresso SDK

An open-source software development kit (SDK) built specifically for your processor and evaluation board selections.



MCUXpresso IDE

An easy-to-use integrated development environment (IDE) for creating, building, debugging, and optimizing your application.



MCUXpresso Config Tools

A comprehensive suite of system configuration tools, including pins, clocks, SDK builder and more.

Learn more www.nxp.com/MCUXpresso.

Other device drivers and example code include:

- ▶ **LPCOpen**—an extensive set of RTOS-agnostic libraries with common APIs that include chip- and board-level device drivers, protocol stacks for TCP/IP (LwIP), USB devices and hosts, CAN bus, and SEGGER emWin graphics libraries. Project files for Arm Keil®, IAR® and MCUXpresso IDE tools are provided and other toolchains can also be used if desired. LPCOpen is available for these device series: LPC1100, LPC1300, LPC1500, LPC1700, LPC1800, LPC4000, LPC4300. Learn more at www.nxp.com/LPCOpen
- ▶ **Code Bundles**—very simple and easy to used peripheral libraries with accompanying examples intended for users of the LPC800 series device to easily migrate to 32-bit Arm MCUs from legacy 8- and 16- bit processors. Code bundles are available from product information page each LPC800 series device on www.nxp.com.
- ▶ **Amazon FreeRTOS**—an operating system for MCUs that makes small, low-power edge devices easy to program, deploy, secure, connect, and manage. It is based on the FreeRTOS kernel, a popular open source operating system for MCUs, and extends it with software libraries that make it easy to securely connect your small, low-power devices to AWS cloud services like AWS IoT Core or to more powerful edge devices running AWS Greengrass.



LPCXpresso Development Boards

LPCXpresso boards are a low cost, easy to use development platform; a concept pioneered by NXP. All boards incorporate an on-board debug probe with option for an external probe. The boards work seamlessly with MCUXpresso IDE and all partner tool-chains that support CMSIS-DAP or J-link protocols. Flexible expansion options include Arduino UNO and PMod. Most LPCXpresso boards also support SWO trace and profiling, and several also include on-board power measurement. Learn more about LPCXpresso boards at www.nxp.com/LPCXpresso-BOARDS.

A whole universe of third-party tools and software

NXP brings together world-class development platforms, tools, boards, and software from NXP and partners to get you started developing on NXP LPC microcontrollers in just minutes. With advanced yet low-cost ways to evaluate, develop, and debug with LPC MCUs and a choice of toolchains that support the entire Cortex-M portfolio, the LPC developer ecosystem gives you a familiar set of tools no matter which LPC MCU you choose. NXP works closely with the best software product providers in the industry to facilitate the highest quality middleware for LPC MCUs. For more information about LPC partner resources, visit: www.nxp.com/microcontrollers/ecosystem.



The 10-year promise: the NXP Product Longevity program

The NXP Product Longevity program ensures a stable supply of microcontrollers for your design. Longevity products are available for a minimum of ten years after product launch, and are supported by our standard end-of-life notification policy. Most products in the Cortex-M and Arm9 categories are covered by the program. Longevity products remain in the program even if the manufacturing site changes. We manufacture through a number of resources, including our own factories and qualified outside vendors. If we transfer a longevity product to another facility, we re-qualify the product to maintain its status in the longevity program. For a complete, up-to-date list of longevity products, visit <http://www.nxp.com/LPC-ProductLongevity>.

LPC800 Series | Entry-level offering, 8-bit simplicity | Cortex-M0+ core

Available in low-pin-count packages, these 30 MHz MCUs offer exceptional power efficiency, 32-bit control, and basic connectivity.

Part no.	Max. clock speed (MHz)	Memory		Serial interfaces			Analog				GPIO	Supply voltage (V)	Temperature range (°C)	Package	Common features	Other features
		Flash (KB)	RAM (KB)	UART	I ² C	SPI	12-bit ADC Channels	Sample rate	Comparator	NFC Tag						
LPC802	15	16	2	2	1	1	12	480 Ksps	1		Up to 17	1.71 – 3.6	-40 to +105	TSSOP16, TSSOP20, HVQFN33, WLCSP16	Switch matrix, reduced-power modes, brownout detection, power-on reset	Level shifter option
LPC804	15	32	4	2	2	1	12	480 Ksps	1		Up to 30	1.71 – 3.6	-40 to +105	TSSOP20, TSSOP24, HVQFN33		10-bit DAC, Programmable Logic Unit, Capacitive touch, Level shifter option
LPC811	30	8	2	2	1	1			1		14	1.8–3.6	-40 to +105	TSSOP16		
LPC812	30	16	4	3	1	2			1		18	1.8–3.6	-40 to +105	SO20, TSSOP16/20, XSON16		
LPC822	30	16	4	3	4	2	12	1.2 Msps	1		29	1.8–3.6	-40 to +105	TSSOP20, HVQFN33		Pattern-match engine
LPC824	30	32	8	3	4	2	12	1.2 Msps	1		29	1.8–3.6	-40 to +105	TSSOP20, HVQFN33		Pattern-match engine
LPC832	30	16	4	1	1	2	5	1.2 Msps			16	1.8–3.6	-40 to +85	TSSOP20		Pattern-match engine
LPC834	30	32	4	1	1	2	12	1.2 Msps			29	1.8–3.6	-40 to +85	HVQFN33		Pattern-match engine
LPC844	30	64	8	2	2	2	12	1.2 Msps	1		54	1.8–3.6	-40 to +105	LQFP48/64, HVQFN33/48		Pattern-match engine, fast initialization memory (FAIM)
LPC845	30	64	16	5	4	2	12	1.2 Msps	1		54	1.8–3.6	-40 to +105	LQFP48/64, HVQFN33/48		Pattern-match engine, fast initialization memory (FAIM), capacitive touch interface
LPC8N04	8	32	8		1	1				Yes	Up to 12	1.72–3.6	-40 to +85	HVQFN24		Built-in temperature sensor with +/- 1.5°C accuracy

LPC1100 Series | Low power, broad selection, and industry-standard connectivity | Cortex-M0+ and Cortex-M0 cores

These Cortex-M0+ and Cortex-M0 MCUs deliver exceptional power efficiency for longer battery life, and performance headroom for product enhancements. They provide an upgrade path for the Cortex-M0+ LPC800 Series.

Part no.	Max. clock speed (MHz)	Memory				Timers			Serial interfaces					Analog			GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes		
		Flash (KB)	Flash page (b)	RAM (KB)	EEPROM (KB)	Standard timers ¹	PWM channels ²	State-configurable timer (SCTimer/PWM) ³	UART	I ² C	SPI	I ² S	USB device ⁴	CAN	ADC channels/resolution	Sample rate						DAC	Comparator
LPC11xx: Low pin count, low-power Arm® Cortex®-M0																							
LPC1102	50	32	256	8		6	7		1	1	1				5-ch./10-bit	400 ksps			11	1.8–3.6	-40 to +85	WLCSP16	ROM power profiles, 5V-tolerant I/O
LPC1104	50	32	256	8		6	8		1	1	1				5-ch./10-bit	400 ksps			13	1.8–3.6	-40 to +85	WLCSP16	ROM power profiles, 5V-tolerant I/O
LPC1110	50	4	256	1		6	8		1	1	1				5-ch./10-bit	400 ksps			16	1.8–3.6	-40 to +85	SO20	On-chip PMU, ROM power profiles
LPC1111	50	8	256	2/4		6	8/11		1	1	1				5/6/8-ch./10-bit	400 ksps			Up to 28	1.8–3.6	-40 to +85	TSSOP20, HVQFN33	On-chip PMU, ROM power profiles, 5V-tolerant I/O
LPC1112	50	16	256	2/4		6	8/11		1	1	1				5/6/8-ch./10-bit	400 ksps			Up to 28	1.8–3.6	-40 to +85	SO20, TSSOP20/28, HVQFN24/33	On-chip PMU, ROM power profiles, 5V-tolerant I/O
LPC1113	50	24	256	4/8		6	11		1	1	1-2				8-ch./10-bit	400 ksps			28/42	1.8–3.6	-40 to +85	HVQFN33, LQFP48	ROM power profiles, 5V-tolerant I/O
LPC1114	50	32	256	4/8		6	10/11		1	1	1-2				6/8-ch./10-bit	400 ksps			Up to 42	1.8–3.6	-40 to +85	TSSOP28, HVQFN33, LQFP48	On-chip PMU, ROM power profiles, 5V-tolerant I/O
LPC1115	50	64	256	8		6	11		1	1	2				8-ch./10-bit	400 ksps			42	1.8–3.6	-40 to +105	LQFP48, TFBGA48	ROM power profiles, 5V-tolerant I/O
LPC1124	50	32	256	8		6	11		3	1	2				8-ch./12-bit	2 Msps			38	1.8–3.6	-40 to +105	LQFP48	ROM EEPROM drivers and power profiles
LPC1125	50	64	256	8		6	11		3	1	2				8-ch./12-bit	2 Msps			38	1.8–3.6	-40 to +105	LQFP48	ROM EEPROM drivers and power profiles
LPC11xxLV: 1.8 V Cortex-M0																							
LPC1101LV	50	32	256	2		6	10		1	1	1				6-ch./8-bit	400 ksps			21	1.65–1.95	-40 to +85	WLCSP25	Tiny package, unique ID
LPC1102LV	50	32	256	8		6	10		1	1	1				6-ch./8-bit	400 ksps			21	1.65–1.95	-40 to +85	WLCSP25	Tiny package, unique ID
LPC1112LV	50	16	256	2/4		6	9/11		1	1	1				6-ch./8-bit or 6-ch./10-bit	400 ksps			20/27	1.65–1.95	-40 to +85	HVQFN24/33	Unique ID
LPC1114LV	50	32	256	4/8		6	11		1	1	1				6-ch./8-bit or 6-ch./10-bit	400 ksps			20/27	1.65–1.95	-40 to +85	HVQFN24/33	Unique ID

LPC1100 Series (continued)

Part no.	Max. clock speed (MHz)	Memory				Timers			Serial interfaces					Analog				RTC	GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes	
		Flash (KB)	Flash page (b)	RAM (KB)	EEPROM (KB)	Standard timers ¹	PWM channels ²	State-configurable timer (SCTimer/PWM) ³	UART	I ² C	SPI	I ² S	USB device ⁴	CAN	ADC channels/resolution	Sample rate	DAC							Comparator
LPC11Axx: Analog Cortex-M0																								
LPC11A02	50	16	256	4	2	6	10		1	1	1				8-ch./10-bit	400 ksp/s	10 b	1		18	1.8–3.6	-40 to +85	WLCSP20	V _{REF} UVLO protection
LPC11A04	50	32	256	8	4	6	10		1	1	1				8-ch./10-bit	400 ksp/s	10 b	1		18	1.8–3.6	-40 to +85	WLCSP20	V _{REF} UVLO protection
LPC11A11	50	8	256	2	512 b	6	12		1	1	2				8-ch./10-bit	400 ksp/s	10 b	1		28	1.8–3.6	-40 to +85	HVQFN33	V _{REF} UVLO protection
LPC11A12	50	16	256	4	1	6	12		1	1	2				8-ch./10-bit	400 ksp/s	10 b	1		28/42	1.8–3.6	-40 to +85	HVQFN33, LQFP48	V _{REF} UVLO protection
LPC11A13	50	24	256	6	2	6	12		1	1	2				8-ch./10-bit	400 ksp/s	10 b	1		28	1.8–3.6	-40 to +85	HVQFN33	V _{REF} UVLO protection
LPC11A14	50	32	256	8	4	6	12		1	1	2				8-ch./10-bit	400 ksp/s	10 b	1		28/42	1.8–3.6	-40 to +85	HVQFN33, LQFP48	V _{REF} UVLO protection
LPC11Cxx: CAN Cortex-M0																								
LPC11C12	50	16	256	8		6	11		1	1	2			1	8-ch./10-bit	400 ksp/s				42	1.8–3.6	-40 to +85	LQFP48	C_CAN, USART, SmartCard, ROM EEPROM drivers and power profiles
LPC11C14	50	32	256	8		6	11		1	1	2			1	8-ch./10-bit	400 ksp/s				42	1.8–3.6	-40 to +85	LQFP48	C_CAN, USART, SmartCard, ROM EEPROM drivers and power profiles
LPC11C22	50	16	256	8		6	10		1	1	2			1	8-ch./10-bit	400 ksp/s				36	1.8–3.6	-40 to +85	LQFP48	C_CAN and CAN txcvr, USART, SmartCard, ROM EEPROM drivers and power profiles
LPC11C24	50	32	256	8		6	10		1	1	2			1	8-ch./10-bit	400 ksp/s				36	1.8–3.6	-40 to +85	LQFP48	C_CAN and CAN txcvr, USART, SmartCard, ROM EEPROM drivers and power profiles
LPC11Dxx: Cortex-M0 with LCD driver																								
LPC11D14	50	32	256	8		6	11		1	1	2				8-ch./10-bit	400 ksp/s				42	1.8–3.6	-40 to +85	LQFP100	LPC1114 with integrated 40 x 4 segment LCD driver
LPC11Exx: EEPROM Cortex-M0																								
LPC11E11	50	8	256	4	512 b	6	11		1	1	2				8-ch./10-bit	400 ksp/s				28	1.8–3.6	-40 to +85	HVQFN33	ROM EEPROM drivers and power profiles, 32-bit divide libraries
LPC11E12	50	16	256	6	1	6	11		1	1	2				8-ch./10-bit	400 ksp/s				40	1.8–3.6	-40 to +85	LQFP48	ROM EEPROM drivers and power profiles, 32-bit divide libraries
LPC11E13	50	24	256	8	2	6	11		1	1	2				8-ch./10-bit	400 ksp/s				40	1.8–3.6	-40 to +85	LQFP48	ROM EEPROM drivers and power profiles, 32-bit divide libraries
LPC11E14	50	32	256	10	4	6	11		1	1	2				8-ch./10-bit	400 ksp/s				28/40/54	1.8–3.6	-40 to +85	LQFP48/64, HVQFN33	ROM EEPROM drivers and power profiles, 32-bit divide libraries
LPC11E36	50	96	256	12	4	6	11		1	1	2				8-ch./10-bit	400 ksp/s				28/54	1.8–3.6	-40 to +85	LQFP64, HVQFN33	ROM EEPROM drivers and power profiles, 32-bit divide libraries
LPC11E37	50	128	256	12	4	6	11		1	1	2				8-ch./10-bit	400 ksp/s				40/54	1.8–3.6	-40 to +85	LQFP48/64	ROM EEPROM drivers and power profiles, 32-bit divide libraries
LPC11E37H	50	128	256	12	4	6	11		2 ⁵	2	2	1 ⁶			8-ch./10-bit	400 ksp/s				40/54	1.8–3.6	-40 to +85	LQFP64	LPC11E37 with I/O handler for enhanced PS/UART functionality and DMA transfers
LPC11E66	50	64	256	12	4	6	14	2	4	2	2				8-ch./12-bit	2 Msps			1	36	1.8–3.6	-40 to +105	LQFP48	ROM EEPROM drivers and power profiles
LPC11E67	50	128	256	20	4	6	19	2	5	2	2				12-ch./12-bit	2 Msps			1	36/50/80	1.8–3.6	-40 to +105	LQFP48, LQFP64, LQFP100	ROM EEPROM drivers and power profiles
LPC11E68	50	256	256	36	4	6	19	2	5	2	2				12-ch./12-bit	2 Msps			1	36/50/80	1.8–3.6	-40 to +105	LQFP48, LQFP64, LQFP100	ROM EEPROM drivers and power profiles

LPC1100 Series (continued)

Part no.	Max. clock speed (MHz)	Memory				Timers			Serial interfaces					Analog			RTC	GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes
		Flash (KB)	Flash page (b)	RAM (KB)	EEPROM (KB)	Standard timers ¹	PWM channels ²	State-configurable timer (SCTimer/PWM) ³	UART	I ² C	SPI	I ² S	USB device ⁴	CAN	ADC channels/resolution	Sample rate						
LPC11Uxx: USB Cortex-M0																						
LPC11U12	50	16	256	6		6	11		1	1	2	1 x FS		8-ch./10-bit	400 ksp/s			26/40	1.8–3.6	-40 to +85	LQFP48, HVQFN33	ROM USB drivers and power profiles, 32-bit divide libraries, 5V-tolerant I/O
LPC11U13	50	24	256	6		6	11		1	1	2	1 x FS		8-ch./10-bit	400 ksp/s			40	1.8–3.6	-40 to +85	LQFP48	ROM USB drivers and power profiles, 32-bit divide libraries, 5V-tolerant I/O
LPC11U14	50	32	256	6		6	11		1	1	2	1 x FS		8-ch./10-bit	400 ksp/s			26/40	1.8–3.6	-40 to +85	HVQFN33, LQFP48, TFBGA48	ROM USB drivers and power profiles, 32-bit divide libraries, 5V-tolerant I/O
LPC11U23	50	24	256	8	1	6	11		1	1	2	1 x FS		8-ch./10-bit	400 ksp/s			40	1.8–3.6	-40 to +85	LQFP48	ROM USB drivers and power profiles, 32-bit divide libraries, 5V-tolerant I/O
LPC11U24	50	32	256	6/8	2/4	6	11		1	1	2	1 x FS		8-ch./10-bit	400 ksp/s			26/40/54	1.8–3.6	-40 to +85	HVQFN33, TFBGA48, LQFP48/64	ROM USB drivers and power profiles, 32-bit divide libraries, 5V-tolerant I/O
LPC11U34	50	40/48	256	8/10	4	6	11		1	1	2	1 x FS		8-ch./10-bit	400 ksp/s			26/40	1.8–3.6	-40 to +85	LQFP48, HVQFN33	ROM USB drivers and power profiles, 32-bit divide libraries, 5V-tolerant I/O
LPC11U35	50	64	256	10/12	4	6	11		1	1	2	1 x FS		8-ch./10-bit	400 ksp/s			40/54	1.8–3.6	-40 to +85	LQFP48/64, HVQFN33, TFBGA48	ROM USB drivers and power profiles, 32-bit divide libraries, 5V-tolerant I/O
LPC11U36	50	96	256	10/12	4	6	11		1	1	2	1 x FS		8-ch./10-bit	400 ksp/s			40/54	1.8–3.6	-40 to +85	LQFP48/64	ROM USB drivers and power profiles, 32-bit divide libraries, 5V-tolerant I/O
LPC11U37	50	128	256	10/12	4	6	11		1	1	2	1 x FS		8-ch./10-bit	400 ksp/s			40/54	1.8–3.6	-40 to +85	LQFP48/64	ROM USB drivers and power profiles, 32-bit divide libraries, 5V-tolerant I/O
LPC11U37H	50	128	256	10/12	4	6	11		2 ⁵	2	2	1 ⁶	1 x FS	8-ch./10-bit	400 ksp/s			26/40	1.8–3.6	-40 to +85	LQFP64	LPC11U37 with I/O handler for enhanced SPI/UART functionality and DMA transfers
LPC11U66	50	64	256	12	4	11	14	2	3	2	2	1 x FS		8-ch./12-bit	2 Msps		1	34	2.4–3.6	-40 to +105	LQFP48	ROM USB drivers and power profiles, 32-bit divide, temp. sensor
LPC11U67	50	128	256	16	4	11 ⁷	14 ⁸	2	3	2	2	1 x FS		8-ch./12-bit	2 Msps		1	34	2.4–3.6	-40 to +105	LQFP48	ROM USB drivers and power profiles, 32-bit divide, temp. sensor
LPC11U68	50	256	256	32	4	11 ⁷	17/19 ⁸	2	5	2	2	1 x FS		10-ch./12-bit or 12-ch./12-bit	2 Msps		1	34/48/80	2.4–3.6	-40 to +105	LQFP48/64/100	ROM USB drivers and power profiles, 32-bit divide, temp. sensor

¹ Includes watchdog timer and SYSTICK timer

² Using timers 0-3

³ SCTimer/PWM peripheral can be configured as additional timers and/or PWM channels

⁴ FS = full speed

⁵ Includes I/O handler used as UART

⁶ Includes I/O handler used as I²S interface

⁷ Includes timers 0-3, SCTimer/PWMs configured as four 16-bit timers, one Watchdog timer, one real-time clock, and one SYSTICK timer

⁸ Includes timers 0-3 and SCTimer/PWMs as PWM (LPC11U68 configuration is package-dependent)

LPC51U68 MCUs | High-Performance and Power-Efficient | Cortex-M0+ core

100MHz Cortex-M0+ based MCU with crystal-less FS USB and ample memory resources

Part no.	Max. clock speed (MHz)	Memory			Timers ¹		Serial interfaces				Analog		GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes
		Flash (KB)	Flash page (b)	RAM (KB)	Standard timers	PWM channels ²	UART ³	I ² C ³	SPI ³	I ² S ³	12-bit ADC channels	Sample rate (Msps)					
LPC51U68	100	256	256	96	9	18	8	8	8	2	1xFS	12	Up to 48	1.62 to 3.6	-40 to +105	LQFP64, LQFP48	Low power ADC, Temperature Sensor

¹ Includes 32-bit general-purpose timers, watchdog timer, real-time alarm clock, systick timer, repetitive-interrupt timer and SCTimer/PWM configured as two 16-bit timers

² Using SCTimer/PWM and general purpose timer to generate PWM

³ Total numbers of UART, I²C, SPI, I²S is 8. In addition, the maximum number of I²S is 2.

LPC54000 Series | Scalable, power-efficient mainstream microcontrollers for the broad market | Cortex-M4 core

Representing the very latest microcontroller innovations, the LPC54000 series MCUs include single- and dual-core options with best-in-class power efficiency and scalability.

Part no.	Max. clock speed (MHz)	Cortex-M0+ coprocessor	Flash (KB)	RAM (KB)	Timers		Serial interfaces							Analog		Graphical LCD controller	GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes	
					Standard timers ¹	PWM channels ²	UART ³	I ² C ³	SPI ³	I ² S ³	CAN	USB device	USB Host/Device	Ethernet w/ 1588	12-bit ADC channels							Sample rate (MSPS)
LPC540xx family: flashless and flexible broad market MCUs with CAN FD and graphics																						
LPC54005	180			360	15	25	9	9	9	2			1xFS 1xHS		12	5		64	1.71 to 3.6	-40 to +105	TFBGA100, LQFP100	On-Chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC54016	180			360	15	28	10	10	10	2	Yes		1xFS 1xHS	Yes	12	5		Up to 171	1.71 to 3.7	-40 to +105	TFBGA180, LQFP208, LQFP100	On-Chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC54018	180			360	15	28	10	10	10	2	Yes		1xFS 1xHS	Yes	12	5	Yes	Up to 171	1.71 to 3.8	-40 to +105	TFBGA180, LQFP208	On-Chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC541xx family: streamlined features for always-on applications																						
LPC54101	100	0	256 512	104	15	18	4	3	2						12	5		37 50	1.62–3.6 V	-40 to +105	WLCSP49, LQFP64	Low-power ADC, small form factor
LPC54102	100	1	256 512	104	15	18	4	3	2						12	5		37 50	1.62–3.6 V	-40 to +105	WLCSP49, LQFP64	Ultra-low-power coprocessor for sensor listening, aggregation, fusion and communication, small form factor
LPC5411x family: power-efficient MCU with USB and digital microphone interface																						
LPC54113	100	0	128 256	up to 192	15	18	8	8	8	2		1xFS			12	5		37 50	1.62–3.6 V	-40 to +105	WLCSP49, LQFP64	On-chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC54114	100	1	256	192	15	18	8	8	8	2		1xFS			12	5		37 50	1.62–3.6 V	-40 to +105	WLCSP49, LQFP64	On-chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC546xx family: flexible broad market MCUs with CAN FD and graphics																						
LPC54605	180	-	256 512	136 200	15	28	10	10	10	2	0		1xFS 1xHS		12	5		145	1.71–3.6 V	-40 to +105	TFBGA180	On-Chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC54606	180	-	256 512	136 200	15	28	10	10	10	2	2		1xFS 1xHS	Yes	12	5		up to 171	1.71–3.6 V	-40 to +105	LQFP100/208, TFBGA100/180	On-Chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC54607	180	-	256 512	136 200	15	28	10	10	10	2	0		1xFS 1xHS		12	5	Yes	145 171	1.71–3.6 V	-40 to +105	TFBGA180, LQFP208	On-Chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC54608	180	-	512	200	15	28	10	10	10	2	2		1xFS 1xHS	Yes	12	5	Yes	145 171	1.71–3.6 V	-40 to +105	TFBGA180, LQFP208	On-Chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC54616	180	-	256 512	136 200	15	28	10	10	10	2	2*		1xFS 1xHS	Yes	12	5		up to 171	1.71–3.6 V	-40 to +105	LQFP100/208, TFBGA100/180	On-Chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC54618	180	-	512	200	15	28	10	10	10	2	2*		1xFS 1xHS	Yes	12	5	Yes	145 171	1.71–3.6 V	-40 to +105	TFBGA180, LQFP208	On-Chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC
LPC54628	220	-	512	200	15	28	10	10	10	2	2*		1xFS 1xHS	Yes	12	5	Yes	145	1.71–3.6 V	-40 to +105	TFBGA180	On-Chip voice-activation detection (VAD) engine, digital MIC subsystem, low-power ADC

¹Includes 32-bit general-purpose timers, watchdog timer, real-time alarm clock, repetitive-interrupt timer, SYSTICK timer, and SCTimer/PWM configured as two 16-bit timers

²Using SCTimer/PWM and general purpose timer to generate PWM

³For LPC5411x and LPC546xx MCU families, total numbers of UART, I²C, SPI, I²S is 8 and 10 respectively. In addition, the maximum number of I²S is 2.

*Support for CAN-FD mode

LPC1200 Series | Noise immunity for industrial applications | Cortex-M0 core

Delivering extra reliability in electrically challenging environments, these Cortex-M0 MCUs are optimized for industrial control and home appliances, and are available with an LCD driver.

Part no.	Max. clock speed (MHz)	Memory			Timers		Serial interfaces			Analog			RTC	GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes
		Flash (KB)	Flash sector (b)	RAM (KB)	Standard timers ¹	PWM channels ²	UART	I ² C	SPI	ADC channels/ resolution	Sample rate	Comparator						
LPC1224	30	32/48	256	4	7	10	2	1	1	8-ch./10-bit	400 ksps	2	1	39/55	3.2-3.6	-40 to +85	LQFP48/64	Additional DMA, CRC, RS-485
LPC1225	30	64/80	256	8	7	10	2	1	1	8-ch./10-bit	400 ksps	2	1	39/55	3.2-3.6	-40 to +85	LQFP48/64	Additional DMA, CRC, RS-485
LPC1226	30	96	256	8	7	10	2	1	1	8-ch./10-bit	400 ksps	2	1	39/55	3.2-3.6	-40 to +85	LQFP48/64	Additional DMA, CRC, RS-485
LPC1227	30	128	256	8	7	10	2	1	1	8-ch./10-bit	400 ksps	2	1	39/55	3.2-3.6	-40 to +85	LQFP48/64	Additional DMA, CRC, RS-485
LPC12D27	50	128	256	8	7	10	2	1	1	8-ch./10-bit	400 ksps	2	1	39	3.2-3.6	-40 to +85	LQFP100	LPC1227 with integrated 40 x 4 segment LCD driver

¹ Includes watchdog timer, SYSTICK timer, and real-time clock

² Using timers 0-3

LPC1300 Series | Performance and basic connectivity, LPC1100 upgrade | Cortex-M3 core

Operating at clock speeds up to 72 MHz and available with a full-speed USB controller, these Cortex-M3 MCUs provide a performance upgrade path for LPC1100 and LPC11U00 devices.

Part no.	Max. clock speed (MHz)	Memory			Timers		Serial interfaces				Analog		GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes
		Flash (KB)	RAM (KB)	EEPROM (KB)	Standard timers ¹	PWM channels ²	UART	I ² C	SPI	USB device ³	ADC channels/ resolution	Sample Rate					
LPC131x																	
LPC1311	72	8	4		6	11	1	1	1		8-ch./10-bit	400 ksps	28	2.0-3.6	-40 to +85	HVQFN33	ROM EEPROM drivers and power profiles, USART, SmartCard
LPC1313	72	32	8		6	11	1	1	1		8-ch./10-bit	400 ksps	28/42	2.0-3.6	-40 to +85	LQFP48, HVQFN33	ROM EEPROM drivers and power profiles, USART, SmartCard
LPC1315	72	32	8	2	7	11	1	1	2		8-ch./12-bit	500 ksps	28/51	2.0-3.6	-40 to +85	LQFP48/64, HVQFN33	ROM EEPROM drivers and power profiles, USART, SmartCard
LPC1316	72	48	8	4	7	11	1	1	2		8-ch./12-bit	500 ksps	28/51	2.0-3.6	-40 to +85	LQFP48/64, HVQFN33	ROM EEPROM drivers and power profiles, USART, SmartCard
LPC1317	72	64	10	4	7	11	1	1	2		8-ch./12-bit	500 ksps	28/51	2.0-3.6	-40 to +85	LQFP48/64, HVQFN33	ROM EEPROM drivers and power profiles, USART, SmartCard
LPC134x: USB																	
LPC1342	72	16	4		6	11	1	1	1	1 x FS	8-ch./10-bit	400 ksps	28	2.0-3.6	-40 to +85	LQFP48, HVQFN33	USB device-only controller, ROM USB and EEPROM drivers and power profiles
LPC1343	72	32	8		6	11	1	1	1	1 x FS	8-ch./10-bit	400 ksps	28/42	2.0-3.6	-40 to +85	LQFP48, HVQFN33	USB device-only controller, ROM USB and EEPROM drivers and power profiles
LPC1345	72	32	10	2	7	11	1	1	2	1 x FS	8-ch./12-bit	500 ksps	28/51	2.0-3.6	-40 to +85	LQFP48/64, HVQFN33	USB device-only controller, ROM USB and EEPROM drivers and power profiles in ROM, USART, SmartCard
LPC1346	72	48	10	4	7	11	1	1	2	1 x FS	8-ch./12-bit	500 ksps	28/51	2.0-3.6	-40 to +85	LQFP48/64, HVQFN33	USB device-only controller, ROM USB and EEPROM drivers and power profiles in ROM, USART, SmartCard
LPC1347	72	64	12	4	7	11	1	1	2	1 x FS	8-ch./12-bit	500 ksps	28/51	2.0-3.6	-40 to +85	LQFP48/64, HVQFN33	USB device-only controller, ROM USB and EEPROM drivers and power profiles in ROM, USART, SmartCard

¹ Includes watchdog timer and SYSTICK timer; LPC13x5, LPC13x6, and LPC 13x7 add repetitive-interrupt timer

² Using timers 0-3

³ FS = full speed

LPC1500 Series | High-precision motion control | Cortex-M3 core

Optimized for motor control, these low-power Cortex-M3 MCUs provide a long list of peripherals, including full-speed USB, a CAN controller, an advanced PWM/timer subsystem, and two high-speed 12-bit ADCs.

Part no.	Max. clock speed (MHz)	Memory			Timers			Serial interfaces					Analog				RTC	GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes
		Flash (KB)	RAM (KB)	EEPROM (KB)	Standard timers ¹	PWM channels ²	State-configurable timer (SCTimer/PWM) ³	UART	I ² C	SPI	USB device	CAN	ADC channels/resolution	Sample rate	DAC	Comparator						
LPC1517	72	64	12	4	13	28	4	3	1	2		1	2 x 12-ch./12-bit	2 Msps	12-bit	4	1	32/46	2.4-3.6	-40 to +105	LQFP48/64	Switch matrix, QEI
LPC1518	72	128	20	4	13	28	4	3	1	2		1	2 x 12-ch./12-bit	2 Msps	12-bit	4	1	46/78	2.4-3.6	-40 to +105	LQFP64/100	Switch matrix, QEI
LPC1519	72	256	36	4	13	28	4	3	1	2		1	2 x 12-ch./12-bit	2 Msps	12-bit	4	1	46/78	2.4-3.6	-40 to +105	LQFP64/100	Switch matrix, QEI
LPC1547	72	64	12	4	13	28	4	3	1	2	1 x FS	1	2 x 12-ch./12-bit	2 Msps	12-bit	4	1	30/44	2.4-3.6	-40 to +105	LQFP48/64	USB device-only controller, switch matrix, QEI
LPC1548	72	128	20	4	13	28	4	3	1	2	1 x FS	1	2 x 12-ch./12-bit	2 Msps	12-bit	4	1	44/76	2.4-3.6	-40 to +105	LQFP64/100	USB device-only controller, switch matrix, QEI
LPC1549	72	256	36	4	13	28	4	3	1	2	1 x FS	1	2 x 8/12-ch./12-bit	2 Msps	12-bit	4	1	30/76	2.4-3.6	-40 to +105	LQFP48/64/100	USB device-only controller, switch matrix, QEI

¹ Includes multi-rate timer, repetitive-interrupt timer, windowed watchdog timer, SYSTICK timer, real-time clock, and each SCTimer/PWM configured as two 16-bit timers

² Includes use of SCTimer/PWMs as PWM (maximum number depends on package)

³ SCTimer/PWM peripheral can be configured as additional timers and/or PWM channels

LPC1700 Series | High performance, multi-connectivity, advanced peripherals | Cortex-M3 core

With a range of advanced connectivity and display options, these Cortex-M3 MCUs provide an upgrade path for the Arm® Arm7™ LPC2300.

Part no.	Max clock speed (MHz)	Memory			Timers			Serial interfaces						Analog			RTC	LCD controller	SD/MMC	External bus interface (bits)	GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes
		Flash (KB)	RAM (KB)	EEPROM (KB)	Standard timers ¹	PWM channels ²	UART	I ² C	SPI	I ² S	USB device/host/OTG ³	CAN	Ethernet	ADC channels/resolution	Sample rate	DAC									
LPC1751	100	32	8		10	12	4	3	2		1 x FS	1	6-ch./12-bit	400 ksps		1				52	2.4-3.6	-40 to +85	LQFP80	QEI, motor-control PWM	
LPC1752	100	64	16		10	12	4	3	2		1 x FS	1	6-ch./12-bit	400 ksps		1				52	2.4-3.6	-40 to +85	LQFP80	QEI, motor-control PWM	
LPC1754	100	128	32		10	12	4	3	2		1 x FS	1	6-ch./12-bit	400 ksps	10-bit	1				52	2.4-3.6	-40 to +85	LQFP80	QEI, motor-control PWM	
LPC1756	100	256	32		10	12	4	3	2	1	1 x FS	2	6-ch./12-bit	400 ksps	10-bit	1				52	2.4-3.6	-40 to +85	LQFP80	QEI, motor-control PWM	
LPC1758	100	512	64		10	12	4	3	2	1	1 x FS	2	6-ch./12-bit	400 ksps	10-bit	1				52	2.4-3.6	-40 to +85	LQFP80	QEI, motor-control PWM	
LPC1759	100	512	64		10	12	4	3	2	1	1 x FS	2	6-ch./12-bit	400 ksps	10-bit	1				52	2.4-3.6	-40 to +85	LQFP80	QEI, motor-control PWM	
LPC1763	100	256	64		10	12	4	3	2	1			8-ch./12-bit	400 ksps	10-bit	1				70	2.4-3.6	-40 to +85	LQFP100	QEI, motor-control PWM	
LPC1764	100	128	32		10	12	4	3	2		1 x FS	2	8-ch./12-bit	400 ksps		1				70	2.4-3.6	-40 to +85	LQFP100	QEI, motor-control PWM	
LPC1765	100	256	64		10	12	4	3	2	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1				70	2.4-3.6	-40 to +85	LQFP100, TFBGA100	QEI, motor-control PWM	
LPC1766	100	256	64		10	12	4	3	2	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1				70	2.4-3.6	-40 to +85	LQFP100	QEI, motor-control PWM	
LPC1767	100	512	64		10	12	4	3	2	1		1	8-ch./12-bit	400 ksps	10-bit	1				70	2.4-3.6	-40 to +85	LQFP100	QEI, motor-control PWM	
LPC1768	100	512	64		10	12	4	3	2	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1				70	2.4-3.6	-40 to +85	LQFP100, TFBGA100	QEI, motor-control PWM	
LPC1769	120	512	64		10	12	4	3	2	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1				70	2.4-3.6	-40 to +85	LQFP100	QEI, motor-control PWM	
LPC1774	120	128	40	2	9	18	4	3	3	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1		8/32	109/165			-40 to +85	LQFP144/208	QEI, motor-control PWM	
LPC1776	120	256	80	4	9	18	5	3	3	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1	1	16/32	141/165			-40 to +85	LQFP208, TFBGA180	QEI, motor-control PWM	
LPC1777	120	512	96	4	9	18	5	3	3	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1	1	32	165			-40 to +85	LQFP208	QEI, motor-control PWM	
LPC1778	120	512	96	4	9	18	5	3	3	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1	1	8/16/32	109/165			-40 to +85	LQFP144/208, TFBGA180/208	QEI, motor-control PWM	
LPC1785	120	256	80	4	9	18	5	3	3	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1	1	32	165			-40 to +85	LQFP208	Motor-control PWM	
LPC1786	120	256	80	4	9	18	5	3	3	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1	1	32	165			-40 to +85	LQFP208	QEI, motor-control PWM	
LPC1787	120	512	96	4	9	18	5	3	3	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1	1	32	165			-40 to +85	LQFP208	QEI, motor-control PWM	
LPC1788	120	512	96	4	9	18	5	3	3	1	1 x FS	2	8-ch./12-bit	400 ksps	10-bit	1	1	8/16/32	109/165			-40 to +85	LQFP144/208, TFBGA180/208	QEI, motor-control PWM	

¹ Includes watchdog timer, SYSTICK timer, motor-control timer, PWM timer, and real-time clock; LPC177x/8x adds a repetitive-interrupt timer ³ FS = full speed

² Using motor-control PWM and one (LPC175x/6x) or two (LPC177x/8x) general-purpose PWMs

LPC1800 Series | Best M3 performance, multi-high-speed connectivity, advanced peripherals | Cortex-M3 core

These feature-packed devices combine the industry's highest-performance Cortex-M3 (up to 180 MHz) with a wide range of advanced connectivity.

Part no.	Max. clock speed (MHz)	Memory			Timers		Serial interfaces					Analog			Security			RTC	LCD controller	Quad SPI flash interface (SPIFI) ⁶	SDIO	External bus interface (bits)	GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes		
		Flash (KB)	RAM (KB)	EEPROM (KB)	Standard timers ¹	PWM channels ²	State-configurable timer (SCTimer/PWM) ³	UART	I ² C	SPI	I ² S	USB device/host ⁴	CAN	Ethernet	ADC channels/resolution	Sample rate	DAC											AES engine	OTP key storage ⁵
LPC18xx: High-performance Arm Cortex-M3																													
LPC1810	180		136		10	22	1	4	2	3	2		2	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	8/16	Up to 64	2.2-3.6	-40 to +85	LQFP144, TFBGA100	Flashless		
LPC1812	180	512	104	16	10	22	1	4	2	3	2		2	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	8/16	Up to 64	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Single-bank flash		
LPC1813	180	512	104	16	10	22	1	4	2	3	2		2	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	8/16	Up to 64	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash		
LPC1815	180	768	136	16	10	22	1	4	2	3	2		2	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	8/16	Up to 64	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash		
LPC1817	180	1024	136	16	10	22	1	4	2	3	2		2	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	8/16	Up to 64	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash		
LPC1820	180		168		10	22	1	4	2	3	2	1 x HS	2	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	8/16	Up to 64	2.2-3.6	-40 to +85	LQFP144, TFBGA100	Flashless, on-chip HS USB PHY with OTG		
LPC1822	180	512	104	16	10	22	1	4	2	3	2	1 x HS	2	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	8/16	Up to 64	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Single-bank flash, on-chip HS USB PHY with OTG		
LPC1823	180	512	104	16	10	22	1	4	2	3	2	1 x HS	2	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	8/16	Up to 64	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash, on-chip HS USB PHY with OTG		
LPC1825	180	768	136	16	10	22	1	4	2	3	2	1 x HS	2	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	8/16	Up to 64	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash, on-chip HS USB PHY with OTG		
LPC1827	180	1024	136	16	10	22	1	4	2	3	2	1 x HS	2	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	8/16	Up to 64	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash, on-chip HS USB PHY with OTG		
LPC1830	180		200		10	22	1	4	2	3	2	2x HS ⁴	2	1	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	16/32	Up to 64	2.2-3.6	-40 to +85	LQFP144, TFBGA100/180, LBGA256	Flashless, on-chip HS USB PHY with OTG	
LPC1833	180	512	136	16	10	22	1	4	2	3	2	2x HS ⁴	2	1	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	16/32	164	2.2-3.6	-40 to +105	LQFP100/144, LBGA256	Dual-bank flash, on-chip HS USB PHY with OTG	
LPC1837	180	1024	136	16	10	22	1	4	2	3	2	2x HS ⁴	2	1	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	16/32	164	2.2-3.6	-40 to +105	LQFP100/144, LBGA256	Dual-bank flash, on-chip HS USB PHY with OTG	
LPC1850	180		200		10	22	1	4	2	3	2	2x HS ⁴	2	1	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	16/32	164	2.2-3.6	-40 to +85	TFBGA180, LBGA256	Flashless, on-chip HS USB PHY with OTG, 1024 x 768 color LCD controller	
LPC1853	180	512	136	16	10	22	1	4	2	3	2	2x HS ⁴	2	1	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	16/32	164	2.2-3.6	-40 to +105	LQFP208, LBGA256	Dual-bank flash, on-chip HS USB PHY with OTG, 1024 x 768 color LCD controller	
LPC1857	180	1024	136	16	10	22	1	4	2	3	2	2x HS ⁴	2	1	2x 8-ch./10-bit	400 ksp/s	10-bit			1	1	1	16/32	164	2.2-3.6	-40 to +105	LQFP208, LBGA256	Dual-bank flash, on-chip HS USB PHY with OTG, 1024 x 768 color LCD controller	
LPC185xx: High-performance Cortex-M3 with security features for protecting code and data																													
LPC18510	180		136		10	22	1	4	2	3	2		2	2x 8-ch./10-bit	400 ksp/s	10-bit	•	•	•	1	1	1	8/16	Up to 64	2.2-3.6	-40 to +85	LQFP144, BGA100, BGA180	Flashless	
LPC18530	180		200		10	22	1	4	2	3	2	2x HS ⁴	2	1	2x 8-ch./10-bit	400 ksp/s	10-bit	•	•	•	1	1	1	16/32	Up to 64	2.2-3.6	-40 to +85	LQFP144, BGA100, BGA256	Flashless, on-chip HS USB PHY with OTG
LPC18537	180	1024	136	16	10	22	1	4	2	3	2	2x HS ⁴	2	1	2x 8-ch./10-bit	400 ksp/s	10-bit	•	•	•	1	1	1	16/32	164	2.2-3.6	-40 to +105	LQFP144, BGA100	Dual-bank flash, on-chip HS USB PHY with OTG
LPC18550	180		200		10	22	1	4	2	3	2	2x HS ⁴	2	1	2x 8-ch./10-bit	400 ksp/s	10-bit	•	•	•	1	1	1	16/32	164	2.2-3.6	-40 to +85	BGA180, BGA256	Flashless, on-chip HS USB PHY with OTG
LPC18557	180	1024	136	16	10	22	1	4	2	3	2	2x HS ⁴	2	1	2x 8-ch./10-bit	400 ksp/s	10-bit	•	•	•	1	1	1	16/32	164	2.2-3.6	-40 to +105	LQFP208, BGA256	Dual-bank flash, on-chip HS USB PHY with OTG

¹ Includes watchdog timer, real-time alarm clock, repetitive-interrupt timer, SYSTICK timer, and SCTimer/PWM configured as two 16-bit timers

² Using motor-control PWM and SCTimer/PWM as PWM

³ SCTimer/PWM peripheral can be configured as additional timers and/or PWM channels

⁴ HS = high speed

⁵ OTP can store two 128-bit keys

⁶ SPIFI peripheral enables use of large, low-cost Quad SPI Flash

⁷ USB0 = integrated HS PHY, USB1 = integrated FS PHY or ULPI

LPC4000 Series | High performance, DSP options, multi-connectivity, advanced peripherals | Cortex-M4 core

These Cortex-M4 MCUs provide an upgrade path for the Cortex-M3 LPC177x/8x families.

Part no.	Max. clock speed (MHz)	Floating-point unit (FPU)	Memory			Timers		Serial interfaces					Analog			Comparator	RTC	LCD controller	Quad SPI flash interface (SPIFI) ⁴	SD/MMC	External bus interface (bits)	GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes
			Flash (KB)	RAM (KB)	EEPROM (KB)	Standard timers ¹	PWM channels ²	UART	I ² C	SPI	I ² S	USB device/host/OTG ³	CAN	Ethernet	ADC channels/resolution											
LPC4072	120		64	24	2	9	18	4	3	3	1	1 x FS	2		8-ch./12-bit	400 ksp/s	10-bit	1	1		53	2.4-3.6	-40 to +85	LQFP80, TFBGA80	Low-power Harvard architecture	
LPC4074	120		128	40	2	9	18	4	3	3	1	1 x FS	2		8-ch./12-bit	400 ksp/s	10-bit	1	1		53/109	2.4-3.6	-40 to +85	LQFP144, TFBGA80	Low-power Harvard architecture	
LPC4076	120	1	256	80	4	9	18	5	3	3	1	1 x FS	2	1	8-ch./12-bit	400 ksp/s	10-bit	2	1	1	8/16	109/140	2.4-3.6	-40 to +85	LQFP144, TFBGA180	Low-power Harvard architecture, QEI, floating-point unit
LPC4078	120	1	512	96	4	9	18	5	3	3	1	1 x FS	2	1	8-ch./12-bit	400 ksp/s	10-bit	2	1	1	8/16/32	53/165	2.4-3.6	-40 to +85	LQFP80/100/144/208, TFBGA180/208	Low-power Harvard architecture, QEI, floating-point unit
LPC4088	120	1	512	96	4	9	18	5	3	3	1	1 x FS	2	1	8-ch./12-bit	400 ksp/s	10-bit	2	1	1	8/16/32	109/165	2.4-3.6	-40 to +85	LQFP144/208, TFBGA180/208	Low-power Harvard architecture, QEI, floating-point unit

¹ Includes watchdog timer, SYSTICK timer, motor-control timer, PWM timer, and real-time clock

² Using motor-control PWM and two general-purpose PWMs

³ FS = full-speed

⁴ SPIFI peripheral enables use of large, low-cost Quad SPI Flash

LPC4300 Series | Best performance, DSP functionality, options for multi-core, multi-high-speed connectivity, advanced peripherals | Cortex-M4 core

These multi-core devices combine the Cortex-M4 DSP capabilities with the Cortex-M0 power efficiency enabling application partition across cores for higher performance.

Part no.	Max. clock speed (MHz)	Core		Memory			Timers			Serial interfaces					Analog		Security			RTC	LCD controller	Quad SPI flash interface (SPIFI) ⁷	SDIO	External bus interface (bits)	GPIO	Supply voltage (V)	Temperature range (°C)	Package	Notes		
		Cortex-M0 coprocessor	Flash (KB)	RAM (KB)	EEPROM (KB)	Standard timers ¹	PWM channels ²	State-configurable timer (SCTimer) ³ /PWM ³	UART	I ² C	SPI	I ² S	SGPIO ⁴	USB device/host ⁵	CAN	Ethernet	ADC channels/resolution	Sample rate	DAC											AES engine	OTP key storage ⁶
LPC43xxx: Multi-core Arm Cortex-M4/M0																															
LPC4310	204	1		168	12	22	1	4	2	3	2	1		2	2 x 4/6-ch./10-bit	400 ksps	10-bit					1	1	1	8/16	Up to 83	2.2-3.6	-40 to +85	LQFP144, TFBGA100	Flashless	
LPC4312	204	1	512	104	16	12	22	1	4	2	3	2	1	2	2 x 4/6-ch./10-bit	400 ksps	10-bit					1	1	1	8/16	Up to 83	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Single-bank flash	
LPC4313	204	1	512	104	16	12	22	1	4	2	3	2	1	2	2 x 4/6-ch./10-bit	400 ksps	10-bit					1	1	1	8/16	Up to 83	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash	
LPC4315	204	1	768	136	16	12	22	1	4	2	3	2	1	2	2 x 4/6-ch./10-bit	400 ksps	10-bit					1	1	1	8/16	Up to 83	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash	
LPC4317	204	1	1024	136	16	12	22	1	4	2	3	2	1	2	2 x 4/6-ch./10-bit	400 ksps	10-bit					1	1	1	8/16	Up to 83	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash	
LPC4320	204	1		200	12	22	1	4	2	3	2	1	1 x HS	2	2 x 4/6-ch./10-bit	400 ksps	10-bit					1	1	1	8/16	Up to 83	2.2-3.6	-40 to +85	LQFP144, TFBGA100	Flashless, on-chip USB HS PHY	
LPC4322	204	1	512	104	16	12	22	1	4	2	3	2	1	1 x HS	2	2 x 4/6-ch./10-bit	400 ksps	10-bit				1	1	1	8/16	Up to 83	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Single-bank flash, on-chip USB HS PHY	
LPC4323	204	1	512	104	16	12	22	1	4	2	3	2	1	1 x HS	2	2 x 4/6-ch./10-bit	400 ksps	10-bit				1	1	1	8/16	Up to 83	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash, on-chip USB HS PHY	
LPC4325	204	1	768	136	16	12	22	1	4	2	3	2	1	1 x HS	2	2 x 4/6-ch./10-bit	400 ksps	10-bit				1	1	1	8/16	Up to 83	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash, on-chip USB HS PHY	
LPC4327	204	1	1024	136	16	12	22	1	4	2	3	2	1	1 x HS	2	2 x 4/6-ch./10-bit	400 ksps	10-bit				1	1	1	8/16	Up to 83	2.2-3.6	-40 to +105	LQFP144, TFBGA100	Dual-bank flash, on-chip USB HS PHY	
LPC4330	204	1		264	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit				1	1	1	16/32	Up to 164	2.2-3.6	-40 to +85	LQFP144, TFBGA180/100, LBG256	Flashless, on-chip USB HS PHY with OTG	
LPC4333	204	1	512	136	16	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit			1	1	1	16/32	Up to 164	2.2-3.6	-40 to +105	LQFP144, TFBGA100, LBG256	Dual-bank flash, on-chip USB HS PHY	
LPC4337	204	1	1024	136	16	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit			1	1	1	16/32	Up to 164	2.2-3.6	-40 to +105	LQFP144, TFBGA100, LBG256	Dual-bank flash, on-chip USB HS PHY with OTG	
LPC4350	204	1		264	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit				1	1	1	16/32	Up to 164	2.2-3.6	-40 to +85	LQFP208, LBG256, TFBGA180	Flashless, on-chip HS USB PHY, 1024x768 color LCD controller	
LPC4353	204	1	512	136	16	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit			1	1	1	16/32	Up to 164	2.2-3.6	-40 to +105	LQFP208, LBG256	Dual-bank flash, on-chip HS USB PHY, 1024 x 768 color LCD controller	
LPC4357	204	1	1024	136	16	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit			1	1	1	16/32	Up to 164	2.2-3.6	-40 to +105	LQFP208, LBG256	Dual-bank flash, on-chip HS USB PHY, 1024 x 768 color LCD controller	
LPC4367	204	2	1024	154	16	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit			1	1	1	16/32	Up to 164	2.2-3.6	-40 to +85	TFBGA100, LQFP208, LBG256	IO subsystem, dual-bank flash, on-chip HS USB PHY, 1024 x 768 color LCD controller	
LPC4370	204	2		282	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	1 x 6-ch./12-bit 2 x 8-ch./10-bit ⁹	80 Msps 400 ksps	10-bit				1	1	1	1	8/32	Up to 164	2.2-3.6	-40 to +85	LBGA256, TFBGA100	6-ch. 80 Msps ADC, on-chip USB PHY, 1024 x 768 color LCD controller
LPC435xx: Multi-core Arm Cortex-M4/M0 with security features for protecting code and data																															
LPC43520	204	1		200	12	22	1	4	2	3	2	1	1 x HS	2	2 x 4/6-ch./10-bit	400 ksps	10-bit	•	•	•	1	1	1	1	8/16	Up to 83	2.2-3.6	-40 to +85	LQFP144, BGA180	Flashless, on-chip USB HS PHY	
LPC43530	204	1		264	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit	•	•	•	1	1	1	16/32	Up to 164	2.2-3.6	-40 to +85	LQFP144, BGA100, BGA256	Flashless, on-chip USB HS PHY with OTG	
LPC43537	204	1	1024	136	16	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit	•	•	•	1	1	1	16/32	Up to 164	2.2-3.6	-40 to +105	LQFP144, BGA100	Dual-bank flash, on-chip USB HS PHY with OTG
LPC43550	204	1		264	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit	•	•	•	1	1	1	16/32	Up to 164	2.2-3.6	-40 to +105	BGA180, BGA256	Flashless, on-chip USB HS PHY 1024 x 768 color LCD controller	
LPC43567	204	2	1024	154	16	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit	•	•	•	1	1	1	16/32	Up to 164	2.2-3.6	-40 to +85	TFBGA100, LQFP208, LBG256	IO subsystem, dual-bank flash, on-chip HS USB PHY, 1024 x 768 color LCD controller
LPC43557	204	1	1024	136	16	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	2 x 8-ch./10-bit	400 ksps	10-bit	•	•	•	1	1	1	16/32	Up to 164	2.2-3.6	-40 to +85	LQFP208, LBG256	Dual-bank flash, on-chip USB HS PHY 1024 x 768 color LCD controller
LPC43570	204	2		282	12	22	1	4	2	3	2	1	2 x HS ⁸	2	1	1 x 6-ch./12-bit 2 x 8-ch./10-bit ⁹	80 Msps 400 ksps	10-bit	•	•	•	1	1	1	1	16/32	Up to 164	2.2-3.6	-40 to +85	BGA100, BGA256	6-ch. 80 Msps ADC, on-chip USB PHY, 1024 x 768 color LCD controller

¹ Includes watchdog timer, real-time alarm clock, repetitive-interrupt timer, SYSTICK timer, and SCTimer/PWM configured as two 16-bit timers

² Using motor-control PWM and SCTimer/PWM as PWM

³ SCTimer/PWM peripheral can be configured as additional timers and/or PWM channels

⁴ SGPIO peripheral can be configured as additional PWM, I²C, I²S, SSI/SSP, and/or UART channels

⁵ HS = high speed

⁶ OTP can store two 128-bit keys

⁷ SPIFI peripheral enables use of large, low-cost Quad SPI Flash

⁸ USB0 = integrated HS PHY, USB1 = integrated FS PHY or ULP1

⁹ LBG256 package only

