

DSP56F80xx in Power Line Modem Applications


Overview

A power line modem, increasingly used for communication between several appliances and an integral component of the smart kitchen, once required both a microcontroller for general control and a specialized application-specific integrated

circuit (ASIC) for coding/decoding and sending/receiving functions. Today, both the microcontroller and ASIC in a power line modem are replaced by a digital signal processor (DSP).

Key Benefits

- > Interfaces low voltage to high voltage power grid
- > Transmits the data using the existing power transmission lines
- > Supports networking and independent addressing of end devices
- > Supports stand-alone operation in small applications
- > Requires a small power stage for signal delivery
- > Out-of-the-box software components designed to expedite time-to-market and reduce development costs



ARCHIVED BY FREESCALE SEMICONDUCTOR

Freescale Ordering Information

Part Number	Product Highlights	Additional Information
DSP56F801	80 MHz, 40 MIPS, SCI, SPI, ADC, PWM, Quad Timer and > 8K Program Flash > 1K Program RAM > 2K Data Flash > 1K Data RAM	MCU-friendly instruction set, OnCE for debug, on-chip relaxation oscillator, 2K BootFLASH and up to 11 GPIO available in a 48-pin LQFP.
DSP56F802	80 MHz, 40 MIPS, SCI, SPI, ADC, PWM, Quad Timer and > 8K Program Flash > 1K Program RAM > 2K Data Flash > 1K Data RAM	MCU-friendly instruction set, OnCE for debug, on-chip relaxation oscillator, 2K BootFLASH and up to 4 GPIO available in a 32-pin LQFP.
DSP56F803	80 MHz, 40 MIPS, CAN, SCI, SPI, ADC, PWMs, Quadrature Decoder, Quad Timer and > 31.5K Program Flash > 512K Program RAM > 4K Data Flash > 2K Data RAM	MCU-friendly instruction set, OnCE for debug, on-chip relaxation oscillator, 2K BootFLASH, external memory expansion, and up to 16 GPIO available in a 100-pin LQFP.
DSP56F805	80 MHz, 40 MIPS, CAN, SCIs, SPI, ADC, PWMs, Quadrature Decoder, Quad Timer and > 31.5K Program Flash > 512K Program RAM > 4K Data Flash > 2K Data RAM	MCU-friendly instruction set, OnCE for debug, on-chip relaxation oscillator, 2K BootFLASH, external memory expansion, and up to 32 GPIO available in a 144-pin LQFP.
DSP56F807	80 MHz, 40 MIPS, CAN, SCIs, SPI, ADCs, PWMs, Quadrature Decoder, Quad Timer and > 60K Program Flash > 2K Program RAM > 8K Data Flash > 4K Data RAM	MCU-friendly instruction set, OnCE for debug, on-chip relaxation oscillator, 2K BootFLASH, external memory expansion, and up to 32 GPIO available in both a 160-pin LQFP and 160 MAPBGA.
DSP56F827	80 MHz, 40 MIPS, SCI, SPI, SSI, TOD, ADC, Quad Timer and > 64K Program Flash > 1K Program RAM > 4K Data Flash > 4K Data RAM	MCU-friendly instruction set, OnCE for debug, external memory expansion, and up to 52 GPIO available in 128-pin LQFP.

Design Challenges

A power line modem transmits and receives data through a power line, or mains. Its use in home applications requires a duplex-mode power line modem that transmits and receives data at approximately 10 kbit/s.

The figure on page 1 shows a simple block diagram of a power line modem. An incoming signal is coupled to the receiving component of the modem that decodes the data and delivers it to the application through an interface. The application returns data to the modem, where it's coded. The transmitter then generates an amplified signal that is coupled into the power line.

Factors to consider in power line communications are:

- > Easy signal coupling into and out of the power line.
- > Efficient transmission through the power line and ongoing separation between the communication signal and the power line frequency.

- > Resistance to noise and interference such as electromagnetic interference (EMI) and electromagnetic compatibility (EMC).

The regulations for power line communication in America, Europe, and Asia differ greatly. A common standard does not exist. In Europe, for example, several frequency bands and frequencies ranging from 3 kHz to 148.5 kHz have been defined for power line communications. The frequency range of 95 kHz to 148.5 kHz is open for home interconnectivity applications, with the modulation frequency band, 125 kHz to 140 kHz, defined as carrier sense multiple access (CSMA).

The modulation band selected for power line communications must meet the required data rate while maximizing resistance to noise and interference with the signal. In any power line, there are several sources of noise and

interference, each with individual characteristics:

- > Multiples of the main frequency; i.e., 50 Hz, 100 Hz, 150 Hz
- > High-voltage transients from flashes or switches
- > High-frequency noise of power factor corrections (PFCs), motors, and inverters

Every modulation band has advantages and disadvantages. Commonly used schemes for modulation include binary phase shift keying (BPSK), frequency shift keying (FSK), and several spread spectrum techniques. In all applications, a modulation scheme should support networking and independent addressing of the end devices. The physical interface should provide for coupling the signal from the transmitter to the power line and from the power line to the receiver.


Freescal Semiconductor Solution

A coupling transformer with high pass characteristic is a reliable solution, providing necessary galvanic isolation of the power line from the main voltage. In a one-phase operation, the transformer

should be connected in parallel between one phase and neutral for 220 V and between two of the three phases for a three-phase operation. A serial connection of the coupling transformer is not recommended, because it results in

a high current through the transformer that causes a magnetic saturation of the transformer core. The figure below shows a basic schematic often used for a coupler.

BASIC SCHEMATIC OF A DATA COUPLER FOR A POWER LINE MODEM



In the above figure, values of R, C and the ratio of the transformer depend on the actual data rate and power and frequency of the signal. For use in frequencies ranging from 95 kHz to 148.5 kHz, the coupled signal voltage can reach up to 116 dBµV, equating 631 mV.

Freescal Semiconductor's DSP56F8xx offers a superior solution in a power line modem. The DSP56F8xx's small form factor, internal clock generator, and microcontroller functions make this device ideal in a stand-alone operation in small applications. The 12-bit analog-to-


digital converter (ADC) has sufficient resolution to detect information signals, and a 15-bit pulse width modulation (PWM) generates clear transmissions. The on-chip flash memory and calculating power code and decode data is transmitted to the application by the integrated serial communications interface (SCI). Only a small power stage is required to deliver the signal to the coupling transformer.

As shown in the figure on page 4, a power line modem may be added to an existing application using a DSP56F8xx. The combination and interaction

between the algorithms used for the power line modem and the motor drive of the gate opener mean an influence of the motor power stage to the power line communication can be avoided.

A special reference design can demonstrate the benefits of including the DSP56F8xx in a power line modem. After successfully proving the functionality via the reference design, the software for power line communication may be integrated into the embedded Software Development Kit (SDK).

POWER LINE MODEM AS AN ADD-ON IN A GATE OPENER



Development Tools

Tool Type	Product Name	Vendor	Description
Software	MSW3SDK000AA	Freescale Semiconductor	Software infrastructure that allows development of efficient, high level software applications that are fully portable and reusable across all DSP56800/DSP56800E family of processors.
Software	CWDSP56800	Freescale Semiconductor	CodeWarrior™ Software Development Tools for DSP56800 (Metrowerks)
Hardware	DSP56F801EVM	Freescale Semiconductor	Evaluation Modules for the 56F801 and 56F802
Hardware	DSP56F803EVM	Freescale Semiconductor	Evaluation Module For the 56F803
Hardware	DSP56F805EVM	Freescale Semiconductor	Evaluation Module For the 56F805
Hardware	DSP56F807EVM	Freescale Semiconductor	Evaluation Module For the 56F807
Hardware	DSP56F827EVM	Freescale Semiconductor	Evaluation Module For the 56F827
Development Kit	DSPOSRT00	Freescale Semiconductor	Emulation Support for 56F8xx Processors (Requires Ethernet Network)

Disclaimer

This document may not include all the details necessary to completely develop this design. It is provided as a reference only and is intended to demonstrate the variety of applications for the device.

Learn More: Contact the Technical Information Center at +1-800-521-6247 or +1-480-768-2130. For more information about Freescale products, please visit www.freescale.com.